



NEUTRIK



[Products](#) > [Industrial](#) > [Circular connectors](#) > [nanoCON](#) > NSC3M

[print](#)

NSC3M

3 pole male cable connector, chuck type strain relief and solder contacts

The nanoCON is the smallest lockable 3 pole connector in the world. It offers a robust metal housing, a metal locking device, gold plated contacts and excellent cable retention.

Features & Benefits

- World's smallest circular lockable multipole connector
- Robust metal housing with gold plated contacts
- Reliable and versatile in applications like medical equipment, control systems, sensors or audio applications such as miniature and wireless microphones and portable mixers
- Pre-mating contact 1



Downloads

-  [Assembly Instruction - nanoCON cable connectors](#)
-  [Product Guide 2013, 07 Circular Connectors](#)
-  [Drawing NSC3M](#)
-  [Drawing NSC3M](#)

Technical Information [hide](#)

Product	
Title	NSC3M
Connection Type	nanoCON
Gender	male
Electrical	
Contact resistance	≤ 12 mΩ (inner)
Dielectric strength	1 kVdc
Insulation resistance	> 1 GΩ (after damp heat test IEC 68-2-30)
Rated current per contact	2 A
Rated voltage	50 V
Mechanical	
Cable O.D.	max. 3.4 mm
Cable retention	> 20 N

Insertion force	< 15 N
Lifetime	500 mating cycles
Wiresize	0.2 mm² / 0.14 mm² (solid / stranded wire)
Wiresize	24 AWG / 26 AWG
Wiring	Solder contacts
Locking device	Latch lock

Material	
Contact plating	0.5 µm Au
Contacts	Brass (CuZn35Pb2)
Insert	PETP
Shell	CuSn4Pb4Zn4
Strain relief	Polyacetal (POM)

Environmental	
Flammability	UL 94 V-0
Protection class	IP 40
Solderability	Complies with IEC 68-2-20
Temperature range	-30 °C to +80 °C

