









- 1 SHELLS: BRASS; CONTACTS: PHOSPHOR BRONZE; HOUSING: POLYESTER, UL 94V-0 RATED, BLACK.
- 2 0.76 μ m [.000030] MIN GOLD ON MATING END FOR A LENGTH OF 1.37[.054] MIN ON INSIDE, 2.54 μ m [.000100] MIN TIN-LEAD FOR A LENGTH OF 3.30[.130] MIN FROM OPPOSITE END, ALL OVER 1.27 μ m [.000050] MIN NICKEL.
- 3 0.38 μ m [.000015] MIN GOLD ON MATING END FOR A LENGTH OF 1.37[.054] MIN ON INSIDE, 2.54 μ m [.000100] MIN TIN-LEAD FOR A LENGTH OF 3.30[.130] MIN FROM OPPOSITE END, ALL OVER 1.27 μ m [.000050] MIN NICKEL.
- 4 2.54 μ m [.000100] MIN TIN-LEAD OVER 1.27 μ m [.000050] MIN NICKEL.
- 5 GOLD PLATING PER MIL-G-45204, TIN PLATING PER MIL-T-10727, NICKEL PLATING PER QQ-N-290, COPPER PLATING PER MIL-C-14550.
- 6 RECEPTACLE ASSEMBLY MATES WITH 6 PIN, 8.99±0.10[.354±.004] DIAMETER PLUG.
- 7 3.81 μ m [.000150] MIN TIN-LEAD OVER 2.54 μ m [.000100] MIN COPPER.

LOC	DIST	P	F	ZONE	LTR	REVISIONS		
						DESCRIPTION	DATE	APPD
BD	26					RLSE PER NPR 3410	4-1-91	-
					0	WAS 91-4264-2-1 & -2		
					A	REVISED PER ECN BD5094	08/21/91	-
					B	REVISED PER ECN BD5035	09/20/91	RW
					C	REVISED PER ECN BD5992	02/28/92	JS
					D	OBS -1 PER EC 0020-1537-93	03/31/94	RB

OBSOLETE		750730-2
		750730-1
	CONTACT FINISH	PART NUMBER

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± 0.13 [.005] 3 PLC DEC ± - ANGLES ± -		DR 4-1-91 H MOLL CHK 4-4-91 R. STONE APPD 4-5-91 R. WHYNE APPD 4-5-91 J. FULPONI PRODUCT SPEC -		 AMP INCORPORATED Harrisburg, Pa. 17105			
MATERIAL 							
FINISH  CONTACTS: SEE TABLE INNER SHELL:  OUTER SHELL: 		APPLICATION SPEC -		SIZE D	CAGE CODE 00779	DRAWING NO 750730	
		WEIGHT -		SCALE 10:1	SHEET 1 OF 1		