

PJA100F

PJ

A

100

F

-

-

①


②

③

④

⑤

⑥



Example recommended EMI/EMC filter
NAC-04-472



High voltage pulse noise type : NAP series
Low leakage current type : NAM series
* A higher current rating EMI/EMC filter
may be recommended in view of the
other devices that could be connected
in parallel with the power supply.

- ① Series name
② Single output
③ Output wattage
④ Universal input
⑤ Output voltage
⑥ Optional *6
C : with Coating
R : Remote on/off
(Required external
power source)
J : Connector interface
T : Vertical terminal block
N2 : with DIN rail

See 5.1 in Instruction Manual.

*Make sure necessary tests will be carried out on your end equipment with the power supply installed in accordance with any required EMC/EMI regulations.

SPECIFICATIONS

* Please consider "PBA100F-5-N" about 5V output with case cover.

	MODEL		PJA100F-12	PJA100F-15	PJA100F-24	PJA100F-36	PJA100F-48
INPUT	VOLTAGE[V]		AC85 - 264 1 φ (Output derating is required at AC85V - 115V. See 1.1 and 3.2 in Instruction Manual)				
	CURRENT[A]	ACIN 100V	1.2typ (Io=90%)				
		ACIN 115V	1.1typ (Io=100%)				
		ACIN 230V	0.6typ (Io=100%)				
	FREQUENCY[Hz]		50 / 60 (47 - 63)				
	EFFICIENCY[%]	ACIN 100V	82typ (Io=90%)	83typ (Io=90%)	85typ (Io=90%)	86typ (Io=90%)	86typ (Io=90%)
		ACIN 115V	82typ (Io=100%)	83typ (Io=100%)	85typ (Io=100%)	86typ (Io=100%)	86typ (Io=100%)
		ACIN 230V	85typ (Io=100%)	86typ (Io=100%)	88typ (Io=100%)	89typ (Io=100%)	89typ (Io=100%)
	POWER FACTOR	ACIN 100V	0.98typ (Io=90%)				
		ACIN 115V	0.98typ (Io=100%)				
ACIN 230V		0.90typ (Io=100%) * Power factor correction is stopped at AC250V or more.					
INRUSH CURRENT[A]	ACIN 100V	16typ (Io=90%) Ta=25℃ at cold start					
	ACIN 115V	16typ (Io=100%) Ta=25℃ at cold start					
	ACIN 230V	32typ (Io=100%) Ta=25℃ at cold start					
LEAKAGE CURRENT[ma]		0.75max (ACIN 240V, 60Hz, Io=100%, According to IEC62368-1 and DEN-AN)					
OUTPUT	VOLTAGE[V]		12	15	24	36	48
	CURRENT[A]	ACIN 85-115V	Output derating is required at ACIN 115V or less (refer to instruction manual 3.2)				
		ACIN 115V-264V	8.4	6.7	4.3	2.8	2.1
	WATTAGE[W]	ACIN 85-115V	Output derating is required at ACIN 115V or less (refer to instruction manual 3.2)				
		ACIN 115V-264V	100.8	100.5	103.2	100.8	100.8
	LINE REGULATION[mV] *3		48max	60max	96max	144max	192max
	LOAD REGULATION [mV] *3	Io=30 to 100%	100max	120max	150max	150max	300max
		Io=0 to 30%	Burst operation (Please contact us about detail)				
	RIPPLE[mVp-p] *1	0 to +40℃	120max	120max	120max	150max	150max
		-10 to 0℃	160max	160max	160max	200max	400max
		Io: load factor	Io=0 to 30%	500max	500max	500max	500max
	RIPPLE NOISE[mVp-p] *1	0 to +40℃	150max	150max	150max	200max	200max
		-10 to 0℃	180max	180max	180max	240max	500max
		Io: load factor	Io=0 to 30%	600max	600max	600max	600max
	TEMPERATURE REGULATION[mV]	0 to +40℃	120max	150max	240max	360max	480max
		-10 to +40℃	180max	180max	290max	440max	600max
	DRIFT[mV] *2		48max	60max	96max	144max	192max
START-UP TIME[ms]		500typ (ACIN 115V, Io=100%) Ta=25℃					
HOLD-UP TIME[ms]		20typ (ACIN 115V, Io=100%)					
OUTPUT VOLTAGE ADJUSTMENT RANGE[V]		10.80 to 13.20	13.50 to 16.50	21.60 to 26.40	32.40 to 39.60	43.20 to 52.80	
OUTPUT VOLTAGE SETTING[V]		12.00 to 12.48	15.00 to 15.60	24.00 to 24.96	36.00 to 37.44	48.00 to 49.92	
PROTECTION CIRCUIT AND OTHERS	OVERCURRENT PROTECTION		Works over 105% of rating and recovers automatically				
	OVERVOLTAGE PROTECTION[V]		13.80 to 16.80	17.25 to 21.00	27.60 to 33.60	41.40 to 50.40	54.00 to 67.20
	OPERATING INDICATION		LED (Green)				
	REMOTE SENSING		Not provided				
	REMOTE ON/OFF		Optional (Required external power source. Option -R)				
ISOLATION	INPUT-OUTPUT • RC *8		AC3,000V 1minute, Cutoff current = 10mA, DC500V 50MΩ min (At room temperature)				
	INPUT-FG		AC2,000V 1minute, Cutoff current = 10mA, DC500V 50MΩ min (At room temperature)				
	OUTPUT • RC-FG *8		AC500V 1minute, Cutoff current = 100mA, DC500V 50MΩ min (At room temperature)				
	OUTPUT-RC *8		AC500V 1minute, Cutoff current = 100mA, DC500V 50MΩ min (At room temperature)				
ENVIRONMENT	OPERATING TEMP.,HUMID.AND.ALTITUDE *4		-20 to +70℃ (Output derating is required), 20 - 90%RH (Non condensing), 3,000m (10,000 feet) max				
	STORAGE TEMP.,HUMID.AND.ALTITUDE		-20 to +75℃, 20 - 90%RH (Non condensing), 9,000m (30,000 feet) max				
	VIBRATION		10 - 55Hz, 19.6m/s² (2G), 3minutes period, 60minutes each along X, Y and Z axes				
	IMPACT		196.1m/s² (20G), 11ms, once each X, Y and Z axes				
SAFETY AND NOISE REGULATIONS	AGENCY APPROVALS		UL62368-1, C-UL (CSA62368-1), EN62368-1, UL508 (Except option -J) Complies with DEN-AN				
	CONDUCTED NOISE		Complies with FCC-B, VCCI-B, CISPR22-B, EN55011-B, EN55022-B				
	HARMONIC ATTENUATOR *7		Complies with IEC61000-3-2 class A				

SPECIFICATIONS


OTHERS	CASE SIZE/WEIGHT	41 X 97 X 109mm [1.61 X 3.82 X 4.29 inches] (Excluding terminal block and screw) (W X H X D) / 500g max
	COOLING METHOD	Convection
WARRANTY	WARRANTY	5 years (subject to the operating conditions)

- | | | | |
|----|--|---|--|
| *1 | This is the result of measurement of the testing board with capacitors of 22 μ F and 0.1 μ F placed at 150 mm from the output terminals by a 20 MHz oscilloscope or a ripple-noise meter equivalent to Keisoku-Giken RM103.
See 1.6 of Instruction Manual for more details.
When the load factor is 0 - 30%, the switching power loss is reduced by burst operation, which will cause ripple and ripple noise to go beyond the specifications. | hour warm-up at 25°C.
*3 Consult us about dynamic load and input response. Measure the output voltage by using the average mode of the tester to deal with the burst operation at 30% load or less.
*4 Output power derating is required. See 3.2 in Instruction Manual.
*5 See 3.3 in Instruction Manual for more details.
*6 Consult us about safety agency approvals for the models with optional functions.
*7 Consult us about other classes.
*8 The RC terminal is added to option -R models. The RC terminal is isolated | from input, output, and FG.
* Do not use the power supply in overcurrent conditions or in unspecified input voltage ranges. Otherwise the internal components may be damaged.
* Parallel operation is not possible with this mode.
* Sound noise may be heard from the power supply when used for pulse load. |
| *2 | Drift is the change in DC output for an eight hour period after a half- | | |

Features


- Compact design (Depth: 109mm 4.29inches)
- High efficiency (88%typ PJA100F-24, AC230Vin, 100% load)
- Low power consumption (1.5W typ AC240Vin, no load at standard model)
- UL508 approved (Except option -J), and complies with SEMI F47 (see instruction manual 1.1)
- Various connection interface options (vertical terminal [-T], AMP connector [-J])

Block diagram



External view

The external size of -R option, -J option, -N2 option and -T option models is different from the standard model. See "5. Options and Others" in Instruction Manual for more details.



- ※ Tolerance : ± 1 [± 0.04]
- ※ Weight : 500g max
- ※ PCB Material/thickness : FR-4 / 1.6mm [0.06 inches]
- ※ Chassis material : Aluminum
- ※ Cover material : Electric galvanizing steel board
- ※ Dimensions in mm, []=inches
- ※ Mounting torque : $0.49\text{N} \cdot \text{m}$ max
- ※ Screw tightening torque : $M3.5\ 1.0\text{N} \cdot \text{m}$ max
- ※ Connect the input FG to safety earth ground.

PJA150F

PJ

A

150

F

-

-

①

②

③

④

⑤

⑥



Example recommended EMI/EMC filter
NAC-04-472



High voltage pulse noise type : NAP series
Low leakage current type : NAM series
* A higher current rating EMI/EMC filter
may be recommended in view of the
other devices that could be connected
in parallel with the power supply.

- ① Series name
② Single output
③ Output wattage
④ Universal input
⑤ Output voltage
⑥ Optional *
C : with Coating
R : Remote on/off
(Required external
power source)
J : Connector interface
T : Vertical terminal block
N2 : with DIN rail

See 5.1 in Instruction Manual.

*Make sure necessary tests will be carried out on your end equipment with the power supply installed in accordance with any required EMC/EMI regulations.

SPECIFICATIONS

* Please consider "PBA150F-5-N" about 5V output with case cover.

	MODEL		PJA150F-12	PJA150F-15	PJA150F-24	PJA150F-36	PJA150F-48
INPUT	VOLTAGE[V]		AC85 - 264 1 φ (Output derating is required at AC85V - 115V. See 1.1 and 3.2 in Instruction Manual)				
	CURRENT[A]	ACIN 100V	1.7typ (Io=90%)				
		ACIN 115V	1.6typ (Io=100%)				
		ACIN 230V	0.8typ (Io=100%)				
	FREQUENCY[Hz]		50 / 60 (47 - 63)				
	EFFICIENCY[%]	ACIN 100V	84typ (Io=90%)	84typ (Io=90%)	87typ (Io=90%)	87typ (Io=90%)	87typ (Io=90%)
		ACIN 115V	84typ (Io=100%)	84typ (Io=100%)	87typ (Io=100%)	87typ (Io=100%)	87typ (Io=100%)
		ACIN 230V	87typ (Io=100%)	87typ (Io=100%)	90typ (Io=100%)	90typ (Io=100%)	90typ (Io=100%)
	POWER FACTOR	ACIN 100V	0.98typ (Io=90%)				
		ACIN 115V	0.98typ (Io=100%)				
ACIN 230V		0.93typ (Io=100%) * Power factor correction is stopped at AC250V or more.					
INRUSH CURRENT[A]	ACIN 100V	16typ (Io=90%) Ta=25℃ at cold start					
	ACIN 115V	16typ (Io=100%) Ta=25℃ at cold start					
	ACIN 230V	32typ (Io=100%) Ta=25℃ at cold start					
LEAKAGE CURRENT[ma]		0.75max (ACIN 240V, 60Hz, Io=100%, According to IEC62368-1 and DEN-AN)					
OUTPUT	VOLTAGE[V]		12	15	24	36	48
	CURRENT[A]	ACIN 85-115V	Output derating is required at ACIN 115V or less (refer to instruction manual 3.2)				
		ACIN 115V-264V	12.5	10	6.4	4.2	3.2
	WATTAGE[W]	ACIN 85-115V	Output derating is required at ACIN 115V or less (refer to instruction manual 3.2)				
		ACIN 115V-264V	150.0	150.0	153.6	151.2	153.6
	LINE REGULATION[mV] *3		48max	60max	96max	144max	192max
	LOAD REGULATION [mV] *3	Io=30 to 100%	100max	120max	150max	150max	300max
		Io=0 to 30%	Burst operation (Please contact us about detail)				
	RIPPLE[mVp-p] *1	0 to +40℃	120max	120max	120max	150max	150max
		-10 to 0℃	160max	160max	160max	200max	400max
		Io: load factor	500max	500max	500max	500max	500max
	RIPPLE NOISE[mVp-p] *1	0 to +40℃	150max	150max	150max	200max	200max
		-10 to 0℃	180max	180max	180max	240max	500max
		Io: load factor	600max	600max	600max	600max	600max
	TEMPERATURE REGULATION[mV]	0 to +40℃	120max	150max	240max	360max	480max
		-10 to +40℃	180max	180max	290max	440max	600max
	DRIFT[mV] *2		48max	60max	96max	144max	192max
START-UP TIME[ms]		500typ (ACIN 115V, Io=100%) Ta=25℃					
HOLD-UP TIME[ms]		20typ (ACIN 115V, Io=100%)					
OUTPUT VOLTAGE ADJUSTMENT RANGE[V]		10.80 to 13.20	13.50 to 16.50	21.60 to 26.40	32.40 to 39.60	43.20 to 52.80	
OUTPUT VOLTAGE SETTING[V]		12.00 to 12.48	15.00 to 15.60	24.00 to 24.96	36.00 to 37.44	48.00 to 49.92	
PROTECTION CIRCUIT AND OTHERS	OVERCURRENT PROTECTION		Works over 105% of rating and recovers automatically				
	OVERVOLTAGE PROTECTION[V]		13.80 to 16.80	17.25 to 21.00	27.60 to 33.60	41.40 to 50.40	54.00 to 67.20
	OPERATING INDICATION		LED (Green)				
	REMOTE SENSING		Not provided				
	REMOTE ON/OFF		Optional (Required external power source. Option -R)				
ISOLATION	INPUT-OUTPUT • RC *8		AC3,000V 1minute, Cutoff current = 10mA, DC500V 50MΩ min (At room temperature)				
	INPUT-FG		AC2,000V 1minute, Cutoff current = 10mA, DC500V 50MΩ min (At room temperature)				
	OUTPUT • RC-FG *8		AC500V 1minute, Cutoff current = 100mA, DC500V 50MΩ min (At room temperature)				
	OUTPUT-RC *8		AC500V 1minute, Cutoff current = 100mA, DC500V 50MΩ min (At room temperature)				
ENVIRONMENT	OPERATING TEMP., HUMID. AND ALTITUDE *4		-20 to +70℃ (Output derating is required), 20 - 90%RH (Non condensing), 3,000m (10,000 feet) max				
	STORAGE TEMP., HUMID. AND ALTITUDE		-20 to +75℃, 20 - 90%RH (Non condensing), 9,000m (30,000 feet) max				
	VIBRATION		10 - 55Hz, 19.6m/s² (2G), 3minutes period, 60minutes each along X, Y and Z axes				
	IMPACT		196.1m/s² (20G), 11ms, once each X, Y and Z axes				
SAFETY AND NOISE REGULATIONS	AGENCY APPROVALS		UL62368-1, C-UL (CSA62368-1), EN62368-1, UL508 (Except option -J) Complies with DEN-AN				
	CONDUCTED NOISE		Complies with FCC-B, VCCI-B, CISPR22-B, EN55011-B, EN55022-B				
	HARMONIC ATTENUATOR *7		Complies with IEC61000-3-2 class A				

SPECIFICATIONS


OTHERS	CASE SIZE/WEIGHT	41 X 97 X 129mm [1.61 X 3.82 X 5.08 inches] (Excluding terminal block and screw) (W X H X D) / 600g max
	COOLING METHOD	Convection
WARRANTY	WARRANTY	*5 5 years (subject to the operating conditions)

- | | | |
|--|---|--|
| <p>*1 This is the result of measurement of the testing board with capacitors of 22 μF and 0.1 μF placed at 150 mm from the output terminals by a 20 MHz oscilloscope or a ripple-noise meter equivalent to Keisoku-Giken RM103.</p> <p>See 1.6 of Instruction Manual for more details.</p> <p>When the load factor is 0 - 30%, the switching power loss is reduced by burst operation, which will cause ripple and ripple noise to go beyond the specifications.</p> | <p>hour warm-up at 25°C.</p> <p>*3 Consult us about dynamic load and input response. Measure the output voltage by using the average mode of the tester to deal with the burst operation at 30% load or less.</p> <p>*4 Output power derating is required. See 3.2 in Instruction Manual.</p> <p>*5 See 3.3 in Instruction Manual for more details.</p> <p>*6 Consult us about safety agency approvals for the models with optional functions.</p> <p>*7 Consult us about other classes.</p> <p>*8 The RC terminal is added to option -R models. The RC terminal is</p> | <p>isolated from input, output, and FG.</p> <p>* Do not use the power supply in overcurrent conditions or in unspecified input voltage ranges. Otherwise the internal components may be damaged.</p> <p>* Parallel operation is not possible with this mode.</p> <p>* Sound noise may be heard from the power supply when used for pulse load.</p> |
| <p>*2 Drift is the change in DC output for an eight hour period after a half-</p> | | |

Features


- Compact design (Depth: 129mm 5.08inches)
- High efficiency (90%typ PJA150F-24, AC230Vin, 100% load)
- Low power consumption (1.5W typ AC240Vin, no load at standard model)
- UL508 approved (Except option -J), and complies with SEMI F47 (see instruction manual 1.1)
- Various connection interface options (vertical terminal [-T], AMP connector [-JJ])


Block diagram



External view

The external size of -R option, -J option, -N2 option and -T option models is different from the standard model. See “5. Options and Others” in Instruction Manual for more details.





Example recommended EMI/EMC filter
NAC-06-472



High voltage pulse noise type : NAP series
Low leakage current type : NAM series
* A higher current rating EMI/EMC filter may be recommended in view of the other devices that could be connected in parallel with the power supply.

- ① Series name
- ② Single output
- ③ Output wattage
- ④ Universal input
- ⑤ Output voltage
- ⑥ Optional *6
- C : with Coating
- G : Low leakage current
- V : External potentiometer for output voltage adjustment
- R : Remote on/off (Required external power source)
- F4: Low speed fan

See 5.1 in Instruction Manual.

*Make sure necessary tests will be carried out on your end equipment with the power supply installed in accordance with any required EMC/EMI regulations.

SPECIFICATIONS

	MODEL	PJA300F-5	PJA300F-12	PJA300F-15	PJA300F-24	PJA300F-36	PJA300F-48
INPUT	VOLTAGE[V]	AC85 - 264 1 φ (Output derating is required at AC85V - 100V. See 1.1 and 3.2 in Instruction Manual)					
	CURRENT[A]	ACIN 100V	3.5typ (Io=100%)	3.9typ (Io=100%)			
		ACIN 115V	3.0typ (Io=100%)	3.3typ (Io=100%)			
		ACIN 230V	1.5typ (Io=100%)	1.7typ (Io=100%)			
	FREQUENCY[Hz]	50 / 60 (47 - 63)					
	EFFICIENCY[%]	ACIN 100V	73typ (Io=100%)	79typ (Io=100%)	81typ (Io=100%)	82typ (Io=100%)	83typ (Io=100%)
		ACIN 115V	74typ (Io=100%)	80typ (Io=100%)	82typ (Io=100%)	83typ (Io=100%)	83typ (Io=100%)
		ACIN 230V	77typ (Io=100%)	82typ (Io=100%)	84typ (Io=100%)	86typ (Io=100%)	86typ (Io=100%)
	POWER FACTOR	ACIN 100V	0.99typ (Io=100%)				
		ACIN 115V	0.98typ (Io=100%)				
		ACIN 230V	0.95typ (Io=100%)				
OUTPUT	INRUSH CURRENT[A]	ACIN 100V	20typ (Io=100%) Ta=25°C at cold start				
		ACIN 115V	20typ (Io=100%) Ta=25°C at cold start				
		ACIN 230V	40typ (Io=100%) Ta=25°C at cold start				
	LEAKAGE CURRENT[ma]	0.75max (ACIN 240V, 60Hz, Io=100%, According to IEC62368-1 and DEN-AN)					
	VOLTAGE[V]	5	12	15	24	36	48
	CURRENT[A]	ACIN 85-100V	Output derating is required at ACIN 100V or less (refer to instruction manual 3.2)				
		ACIN 100V-264V	50	25	20	12.5	8.4
	WATTAGE[W]	ACIN 85-100V	Output derating is required at ACIN 100V or less (refer to instruction manual 3.2)				
		ACIN 100V-264V	250	300	300	300	302.4
	LINE REGULATION[mV] *3	20max	48max	60max	96max	144max	192max
PROTECTION CIRCUIT AND OTHERS	LOAD REGULATION[mV] *3	40max	100max	120max	150max	150max	300max
	RIPPLE[mVp-p] *1	0 to +50°C	80max	120max	120max	120max	150max
		-10 to 0°C	140max	160max	160max	160max	400max
	RIPPLE NOISE[mVp-p] *1	0 to +50°C	120max	150max	150max	150max	200max
		-10 to 0°C	160max	180max	180max	180max	240max
	TEMPERATURE REGULATION[mV]	0 to +50°C	50max	120max	150max	240max	360max
		-10 to +50°C	75max	180max	180max	290max	440max
	DRIFT[mV] *2	20max	48max	60max	96max	144max	192max
	START-UP TIME[ms]	300typ (ACIN 100V, Io=100%)					
	HOLD-UP TIME[ms]	20typ (ACIN 100V, Io=100%)					
ISOLATION	OUTPUT VOLTAGE ADJUSTMENT RANGE[V]	4.50 to 5.50	10.80 to 13.20	13.50 to 16.50	21.60 to 26.40	32.40 to 39.60	43.20 to 52.80
	OUTPUT VOLTAGE SETTING[V]	5.00 to 5.15	12.00 to 12.48	15.00 to 15.60	24.00 to 24.96	36.00 to 37.44	48.00 to 49.92
	OVERCURRENT PROTECTION	Works over 105% of rating and recovers automatically					
	OVERVOLTAGE PROTECTION[V]	5.75 to 7.00	13.80 to 16.80	17.25 to 21.00	27.60 to 33.60	41.40 to 50.40	55.20 to 67.20
	OPERATING INDICATION	LED (Green)					
	REMOTE SENSING	Not provided					
	REMOTE ON/OFF	Optional (Required external power source. Option -R)					
	INPUT-OUTPUT · RC *9	AC3,000V 1minute, Cutoff current = 10mA, DC500V 50MΩ min (At room temperature)					
	INPUT-FG	AC2,000V 1minute, Cutoff current = 10mA, DC500V 50MΩ min (At room temperature)					
	OUTPUT · RC-FG *9	AC500V 1minute, Cutoff current = 100mA, DC500V 50MΩ min (At room temperature)					
ENVIRONMENT	OUTPUT-RC *9	AC500V 1minute, Cutoff current = 100mA, DC500V 50MΩ min (At room temperature)					
	OPERATING TEMP., HUMID. AND ALTITUDE *4	-20 to +70°C (Output derating is required), 20 - 90%RH (Non condensing), 3,000m (10,000 feet) max					
	STORAGE TEMP., HUMID. AND ALTITUDE	-20 to +75°C, 20 - 90%RH (Non condensing), 9,000m (30,000 feet) max					
	VIBRATION	10 - 55Hz, 19.6m/s² (2G), 3minutes period, 60minutes each along X, Y and Z axes					
	IMPACT	196.1m/s² (20G), 11ms, once each X, Y and Z axes					
SAFETY AND NOISE REGULATIONS	AGENCY APPROVALS	UL62368-1, C-UL (CSA62368-1), EN62368-1 Complies with DEN-AN					
	CONDUCTED NOISE	Complies with FCC-B, VCCI-B, CISPR22-B, EN55011-B, EN55022-B					
	HARMONIC ATTENUATOR *8	Complies with IEC61000-3-2 class A					

SPECIFICATIONS

OTHERS	CASE SIZE/WEIGHT	102×41×190mm [4.02×1.61×7.48 inches] (Excluding terminal block and screw) (W×H×D) / 1.0kg max
	COOLING METHOD	*7 Forced cooling (internal fan)
WARRANTY	WARRANTY	*5 5 years (subject to the operating conditions)

*1 This is the result of measurement of the testing board with capacitors of 22 μ F and 0.1 μ F placed at 150 mm from the output terminals by a 20 MHz oscilloscope or a ripple-noise meter equivalent to Keisoku-Giken RM103.

See 1.6 of Instruction Manual for more details.

*2 Drift is the change in DC output for an eight hour period after a half-hour warm-up at 25°C.

*3 Consult us about dynamic load and input response.

*4 Output power derating is required. See 3.2 in Instruction Manual.

*5 See 3.3 in Instruction Manual for more details.

*6 Consult us about safety agency approvals for the models with optional functions.

*7 The fan speed slows down at no load.

*8 Consult us about other classes.

*9 The RC terminal is added to option -R models. The RC terminal is

isolated from input, output, and FG.

* Do not use the power supply in overcurrent conditions or in unspecified input voltage ranges. Otherwise the internal components may be damaged.


* Parallel operation is not possible with this mode.

* Sound noise may be heard from the power supply when used for pulse load.

Features


- Cost-effective
- Longer life (see Instruction Manual)
- Low profile (meets 1U height = 41 mm or 1.61 inches)
- Wide operating temperature range (-20°C to +70°C see instruction manual)
- Slow fan speed at no load
- Complies with SEMI F-47
- Many optional functions

Block diagram



External view

The external size of -V option and -R option models is different from the standard model. See "5. Options and Others" in Instruction Manual for more details.



PJA600F

PJ

A

600

F

-

-

①

②

③

④

⑤

⑥

Example recommended EMI/EMC filter
NAC-16-472

High voltage pulse noise type : NAP series
Low leakage current type : NAM series
* A higher current rating EMI/EMC filter may be recommended in view of the other devices that could be connected in parallel with the power supply.

- ① Series name
② Single output
③ Output wattage
④ Universal input
⑤ Output voltage
⑥ Optional *6
C : with Coating
G : Low leakage current
V : External potentiometer for output voltage adjustment
W: Parallel operation, LV alarm Remote sensing
R : Remote on/off (Required external power source)
F4: Low speed fan

See 5.1 in Instruction Manual.

*Make sure necessary tests will be carried out on your end equipment with the power supply installed in accordance with any required EMC/EMI regulations.

SPECIFICATIONS

	MODEL		PJA600F-5	PJA600F-12	PJA600F-15	PJA600F-24	PJA600F-36	PJA600F-48
INPUT	VOLTAGE[V]		AC85 - 264 1 φ (Output derating is required at AC85V - 100V. See 1.1 and 3.2 in Instruction Manual)					
	CURRENT[A]	ACIN 100V	6.7typ (Io=100%)	7.5typ (Io=100%)				
		ACIN 115V	5.7typ (Io=100%)	6.5typ (Io=100%)				
		ACIN 230V	2.8typ (Io=100%)	3.2typ (Io=100%)				
	FREQUENCY[Hz]		50 / 60 (47 - 63)					
	EFFICIENCY[%]	ACIN 100V	76typ (Io=100%)	81typ (Io=100%)	82typ (Io=100%)	84typ (Io=100%)	85typ (Io=100%)	85typ (Io=100%)
		ACIN 115V	77typ (Io=100%)	82typ (Io=100%)	82typ (Io=100%)	85typ (Io=100%)	86typ (Io=100%)	85typ (Io=100%)
		ACIN 230V	79typ (Io=100%)	84typ (Io=100%)	85typ (Io=100%)	88typ (Io=100%)	88typ (Io=100%)	88typ (Io=100%)
	POWER FACTOR	ACIN 100V	0.99typ (Io=100%)					
		ACIN 115V	0.98typ (Io=100%)					
		ACIN 230V	0.95typ (Io=100%)					
INRUSH CURRENT[A]	ACIN 100V	20/40typ (Io=100%) (Primary inrush current /Secondary inrush current) (More than 3sec to re-start)						
	ACIN 115V	20/40typ (Io=100%) (Primary inrush current /Secondary inrush current) (More than 3sec to re-start)						
	ACIN 230V	40/40typ (Io=100%) (Primary inrush current /Secondary inrush current) (More than 3sec to re-start)						
LEAKAGE CURRENT[ma]		1.5max (ACIN 240V, 60Hz, Io=100%, According to IEC62368-1 and DEN-AN)						
OUTPUT	VOLTAGE[V]		5	12	15	24	36	48
	CURRENT[A]	ACIN 85-100V	Output derating is required at ACIN 100V or less (refer to instruction manual 3.2)					
		ACIN 100V-264V	100	50	40	25	16.7	12.5
	WATTAGE[W]	ACIN 85-100V	Output derating is required at ACIN 100V or less (refer to instruction manual 3.2)					
		ACIN 100V-264V	500	600	600	600	601.2	600
	LINE REGULATION[mV]		*7 20max	48max	60max	96max	144max	192max
	LOAD REGULATION[mV]		*7 40max	100max	120max	150max	150max	300max
	RIPPLE[mVp-p]	*1 0 to +50℃	80max	120max	120max	120max	150max	150max
		*1 -20 to 0℃	140max	160max	160max	160max	160max	400max
	RIPPLE NOISE[mVp-p]	*1 0 to +50℃	120max	150max	150max	150max	200max	200max
		*1 -20 to 0℃	160max	180max	180max	180max	240max	500max
	TEMPERATURE REGULATION[mV]	0 to +50℃	50max	120max	150max	240max	360max	480max
		-20 to +50℃	75max	180max	180max	290max	440max	600max
	DRIFT[mV]		*2 20max	48max	60max	96max	144max	192max
	START-UP TIME[ms]		300typ (ACIN 100V, Io=100%)					
	HOLD-UP TIME[ms]		20typ (ACIN 100V, Io=100%)					
	OUTPUT VOLTAGE ADJUSTMENT RANGE[V]		4.50 to 5.50	10.80 to 13.20	13.50 to 16.50	21.60 to 26.40	32.40 to 39.60	43.20 to 52.80
OUTPUT VOLTAGE SETTING[V]		5.00 to 5.15	12.00 to 12.48	15.00 to 15.60	24.00 to 24.96	36.00 to 37.44	48.00 to 49.92	
PROTECTION CIRCUIT AND OTHERS	OVERCURRENT PROTECTION		Works over 105% of rating and recovers automatically					
	OVERVOLTAGE PROTECTION[V]		5.75 to 7.00	13.80 to 16.80	17.25 to 21.00	27.60 to 33.60	41.40 to 50.40	55.20 to 67.20
	OPERATING INDICATION		LED (Green)					
	REMOTE SENSING		Optional (Option -W)					
	REMOTE ON/OFF		Optional (Required external power source. Option -R)					
ISOLATION	INPUT-OUTPUT • RC	*3	AC3,000V 1minute, Cutoff current = 10mA, DC500V 50MΩ min (At room temperature)					
	INPUT-FG		AC2,000V 1minute, Cutoff current = 10mA, DC500V 50MΩ min (At room temperature)					
	OUTPUT • RC-FG	*3	AC500V 1minute, Cutoff current = 100mA, DC500V 50MΩ min (At room temperature)					
	OUTPUT-RC	*3	AC500V 1minute, Cutoff current = 100mA, DC500V 50MΩ min (At room temperature)					
ENVIRONMENT	OPERATING TEMP., HUMID.AND ALTITUDE		*4 -20 to +70℃ (Output derating is required), 20 - 90%RH (Non condensing), 3,000m (10,000 feet) max					
	STORAGE TEMP., HUMID.AND ALTITUDE		-20 to +75℃, 20 - 90%RH (Non condensing), 9,000m (30,000 feet) max					
	VIBRATION		10 - 55Hz, 19.6m/s ² (2G), 3minutes period, 60minutes each along X, Y and Z axes					
	IMPACT		196.1m/s ² (20G), 11ms, once each X, Y and Z axes					
SAFETY AND NOISE REGULATIONS	AGENCY APPROVALS		UL62368-1, C-UL (CSA62368-1), EN62368-1 Complies with DEN-AN					
	CONDUCTED NOISE		Complies with FCC-B, VCCI-B, CISPR22-B, EN55011-B, EN55022-B					
	HARMONIC ATTENUATOR		*9 Complies with IEC61000-3-2 class A					

SPECIFICATIONS

OTHERS	CASE SIZE/WEIGHT	120×61×215mm [4.72×2.40×8.46 inches] (Excluding terminal block and screw) (W×H×D) / 2.0kg max
	COOLING METHOD	*8 Forced cooling (internal fan)
WARRANTY	WARRANTY	*5 5 years (subject to the operating conditions)

*1 This is the result of measurement of the testing board with capacitors of 22 μ F and 0.1 μ F placed at 150 mm from the output terminals by a 20 MHz oscilloscope or a ripple-noise meter equivalent to Keisoku-Giken RM103.
See 1.6 of Instruction Manual for more details.

*2 Drift is the change in DC output for an eight hour period after a half-hour warm-up at 25°C.

*3 The RC terminal is added to option -R models. The RC terminal is isolated from input, output, and FG.

*4 Output power derating is required. See 3.2 in Instruction Manual.

*5 See 3.3 in Instruction Manual for more details.

*6 Consult us about safety agency approvals for the models with optional functions.

*7 Consult us about dynamic load and input response.

*8 The fan speed slows down at no load.

*9 Consult us about other classes.

* Do not use the power supply in overcurrent conditions or in unspecified input voltage ranges. Otherwise the internal components may be damaged.


* Parallel operation is allowed for PLA600FA models with the -W option only.

* Sound noise may be heard from the power supply when used for pulse load.

Features


- Cost-effective
- Longer life (see Instruction Manual)
- Low profile (meets 2U height = 61 mm or 2.40 inches)
- Wide operating temperature range (-20°C to +70°C see instruction manual)
- Slow fan speed at no load
- Complies with SEMI F-47
- Many optional functions

Block diagram



External view

The external size of -V option, -W option and -R option models is different from the standard model. See "5. Options and Others" in Instruction Manual for more details.



PJA1000F

PJ

A

1000

F

-


①

②

③

④

⑤



Example recommended EMI/EMC filter
NAC-20-472



High voltage pulse noise type : NAP series
Low leakage current type : NAM series

- ① Series name
② Single output
③ Output wattage
④ Universal input
⑤ Output voltage

*Make sure necessary tests will be carried out on your end equipment with the power supply installed in accordance with any required EMC/EMI regulations.

SPECIFICATIONS

	MODEL	PJA1000F-24	PJA1000F-48
INPUT	VOLTAGE[V]	AC85 - 264 1 ϕ (Output derating is required at AC85V - 115V. See 1.1 and 3.2 in Instruction Manual)	
	CURRENT[A]	ACIN 100V	12.5typ (Io=90%)
		ACIN 115V	11.0typ (Io=100%)
		ACIN 230V	5.5typ (Io=100%)
	FREQUENCY[Hz]	50 / 60 (47 - 63)	
	EFFICIENCY[%]	ACIN 100V	84typ (Io=90%)
		ACIN 115V	85typ (Io=100%)
		ACIN 230V	88typ (Io=100%)
OUTPUT	POWER FACTOR	ACIN 100V	0.98typ (Io=90%)
		ACIN 115V	0.98typ (Io=100%)
		ACIN 230V	0.95typ (Io=100%)
	INRUSH CURRENT[A]	ACIN 100V	15/30typ (Io=90%) (Primary inrush current /Secondary inrush current) (More than 10sec to re-start)
		ACIN 115V	15/30typ (Io=100%) (Primary inrush current /Secondary inrush current) (More than 10sec to re-start)
		ACIN 230V	30/30typ (Io=100%) (Primary inrush current /Secondary inrush current) (More than 10sec to re-start)
	LEAKAGE CURRENT[ma]	1.5max (ACIN 240V, 60Hz, Io=100%, According to IEC62368-1 and DEN-AN)	
	VOLTAGE[V]	24	48
PROTECTION CIRCUIT AND OTHERS	CURRENT[A]	ACIN 85-115V	Output derating is required at ACIN 115V or less (refer to instruction manual 3.2)
		ACIN 115V-264V	42
	WATTAGE[W]	ACIN 85-115V	Output derating is required at ACIN 115V or less (refer to instruction manual 3.2)
		ACIN 115V-264V	1008
	LINE REGULATION[mV]	*2	96max
	LOAD REGULATION[mV]	*2	150max
	RIPPLE[mVp-p]	0 to +50°C	120max
		-20 to 0°C	160max
	RIPPLE NOISE[mVp-p]	0 to +50°C	150max
		-20 to 0°C	180max
	TEMPERATURE REGULATION[mV]	0 to +50°C	240max
		-20 to +50°C	290max
	DRIFT[mV]	*3	96max
	START-UP TIME[ms]	800typ (ACIN 115V, Io=100%)	
ISOLATION	HOLD-UP TIME[ms]	20typ (ACIN 115V, Io=100%)	
	OUTPUT VOLTAGE ADJUSTMENT RANGE[V]	20.40 to 28.50	40.80 to 55.20
	OUTPUT VOLTAGE SETTING[V]	24.00 to 24.96	48.00 to 49.92
	OVERCURRENT PROTECTION	Works over 105% of rating and recovers automatically	
ENVIRONMENT	OVERVOLTAGE PROTECTION[V]	28.80 to 34.80	57.00 to 67.20
	OPERATING INDICATION	LED (Green)	
	INPUT-OUTPUT	AC3,000V 1minute, Cutoff current = 25mA, DC500V 50M Ω min (At room temperature)	
	INPUT-FG	AC2,000V 1minute, Cutoff current = 25mA, DC500V 50M Ω min (At room temperature)	
SAFETY AND NOISE REGULATIONS	OUTPUT-FG	AC500V 1minute, Cutoff current = 100mA, DC500V 50M Ω min (At room temperature)	
	OPERATING TEMP., HUMID. AND ALTITUDE *4	-20 to +70°C (Output derating is required), 20 - 90%RH (Non condensing), 3,000m (10,000 feet) max	
	STORAGE TEMP., HUMID. AND ALTITUDE	-20 to +75°C, 20 - 90%RH (Non condensing), 9,000m (30,000 feet) max	
	VIBRATION	10 - 55Hz, 19.6m/s ² (2G), 3minutes period, 60minutes each along X, Y and Z axes	
HARMONIC ATTENUATOR *5	IMPACT	196.1m/s ² (20G), 11ms, once each X, Y and Z axes	
	AGENCY APPROVALS	UL62368-1, C-UL (CSA62368-1), EN62368-1 Complies with DEN-AN	
	CONDUCTED NOISE	Complies with FCC-B, VCCI-B, CISPR22-B, EN55011-B, EN55022-B	

SPECIFICATIONS

OTHERS	CASE SIZE/WEIGHT	150×61×240mm [5.91×2.40×9.45 inches] (Excluding terminal block and screw) (W×H×D) / 2.8kg max
	COOLING METHOD	*6 Forced cooling (internal fan)
WARRANTY	WARRANTY	*7 5 years (subject to the operating conditions)

*1 This is the result of measurement of the testing board with capacitors of 22 μ F and 0.1 μ F placed at 150 mm from the output terminals by a 20 MHz oscilloscope or a ripple-noise meter equivalent to Keisoku-Giken RM103.
See 1.6 of Instruction Manual for more details.

*2 Consult us about dynamic load and input response.

*3 Drift is the change in DC output for an eight hour period after a half-hour warm-up at 25°C.

*4 Output power derating is required. See 3.2 in Instruction Manual.

*5 Consult us about other classes.

*6 The fan speed slows down or stops at no load.

*7 See 3.3 in Instruction Manual for more details.

* Do not use the power supply in overcurrent conditions or in unspecified input voltage ranges. Otherwise the internal components may be damaged.


* Parallel operation is not possible with this mode.

* Sound noise may be heard from the power supply when used for pulse load.


Features

- Cost-effective
- Longer life (see Instruction Manual)
- Low profile (meets 2U height = 61 mm or 2.4 inches)
- Wide operating temperature range (-20°C to +70°C see instruction manual)
- Stop or slow fan speed at no load

Block diagram



External view



- ※ Tolerance : ± 1 [± 0.04]
 ※ Weight : 2.8kg max
 ※ PCB Material/thickness : FR-4 / 1.6mm [0.06inches]
 ※ Chassis material : Electric galvanizing steel board
 ※ Case material : Electric galvanizing steel board
 ※ Dimensions in mm, [] = inches
 ※ Mounting torque : 1.5N · m max
 ※ Screw tightening torque : 1.6N · m max
 ※ Output terminal M4 tightening torque : 1.2N · m max
 ※ Connect the input FG to safety earth ground.

PJA1500F

PJ

A

1500

F

-

①

②

③

④

⑤



Example recommended EMI/EMC filter
NAC-20-472



High voltage pulse noise type : NAP series
Low leakage current type : NAM series

- ① Series name
② Single output
③ Output wattage
④ Universal input
⑤ Output voltage

*Make sure necessary tests will be carried out on your end equipment with the power supply installed in accordance with any required EMC/EMI regulations.

SPECIFICATIONS

	MODEL	PJA1500F-24	PJA1500F-48
INPUT	VOLTAGE[V]	AC85 - 264 1 ϕ (Output derating is required at AC85V - 115V. See 1.1 and 3.2 in Instruction Manual)	
	CURRENT[A]	ACIN 100V	18typ (Io=90%)
		ACIN 115V	16typ (Io=100%)
		ACIN 230V	8typ (Io=100%)
	FREQUENCY[Hz]	50 / 60 (47 - 63)	
	EFFICIENCY[%]	ACIN 100V	84typ (Io=90%)
		ACIN 115V	85typ (Io=100%)
		ACIN 230V	88typ (Io=100%)
	POWER FACTOR	ACIN 100V	0.98typ (Io=90%)
		ACIN 115V	0.98typ (Io=100%)
		ACIN 230V	0.95typ (Io=100%)
	INRUSH CURRENT[A]	ACIN 100V	15/30typ (Io=90%) (Primary inrush current /Secondary inrush current) (More than 10sec to re-start)
		ACIN 115V	15/30typ (Io=100%) (Primary inrush current /Secondary inrush current) (More than 10sec to re-start)
		ACIN 230V	30/30typ (Io=100%) (Primary inrush current /Secondary inrush current) (More than 10sec to re-start)
	LEAKAGE CURRENT[ma]	1.5max (ACIN 240V, 60Hz, Io=100%, According to IEC62368-1 and DEN-AN)	
OUTPUT	VOLTAGE[V]	24	48
	CURRENT[A]	ACIN 85-115V	Output derating is required at ACIN 115V or less (refer to instruction manual 3.2)
		ACIN 115V-264V	64
	WATTAGE[W]	ACIN 85-115V	Output derating is required at ACIN 115V or less (refer to instruction manual 3.2)
		ACIN 115V-264V	1536
	LINE REGULATION[mV]	*2	96max
	LOAD REGULATION[mV]	*2	150max
	RIPPLE[mVp-p]	0 to +50°C	120max
		*1 -20 to 0°C	160max
	RIPPLE NOISE[mVp-p]	0 to +50°C	150max
		*1 -20 to 0°C	270max
	TEMPERATURE REGULATION[mV]	0 to +50°C	240max
		-20 to +50°C	290max
	DRIFT[mV]	*3	96max
	START-UP TIME[ms]	800typ (ACIN 115V, Io=100%)	
	HOLD-UP TIME[ms]	20typ (ACIN 115V, Io=100%)	
PROTECTION CIRCUIT AND OTHERS	OVERCURRENT PROTECTION	Works over 105% of rating and recovers automatically	
	OVERVOLTAGE PROTECTION[V]	28.80 to 34.80	57.00 to 67.20
	OPERATING INDICATION	LED (Green)	
ISOLATION	INPUT-OUTPUT	AC3,000V 1minute, Cutoff current = 25mA, DC500V 50M Ω min (At room temperature)	
	INPUT-FG	AC2,000V 1minute, Cutoff current = 25mA, DC500V 50M Ω min (At room temperature)	
	OUTPUT-FG	AC500V 1minute, Cutoff current = 100mA, DC500V 50M Ω min (At room temperature)	
ENVIRONMENT	OPERATING TEMP., HUMID. AND ALTITUDE *4	-20 to +70°C (Output derating is required), 20 - 90%RH (Non condensing), 3,000m (10,000 feet) max	
	STORAGE TEMP., HUMID. AND ALTITUDE	-20 to +75°C, 20 - 90%RH (Non condensing), 9,000m (30,000 feet) max	
	VIBRATION	10 - 55Hz, 19.6m/s ² (2G), 3minutes period, 60minutes each along X, Y and Z axes	
	IMPACT	196.1m/s ² (20G), 11ms, once each X, Y and Z axes	
SAFETY AND NOISE REGULATIONS	AGENCY APPROVALS	UL62368-1, C-UL (CSA62368-1), EN62368-1, Complies with DEN-AN	
	CONDUCTED NOISE	Complies with FCC-A, VCCI-A, CISPR22-A, EN55011-A, EN55022-A, additional EMI/EMC Filter required for meeting class B	
	HARMONIC ATTENUATOR *5	Complies with IEC61000-3-2 class A	

SPECIFICATIONS

OTHERS	CASE SIZE/WEIGHT	178×61×268mm [7.01×2.40×10.55 inches] (Excluding terminal block and screw) (W×H×D) / 3.5kg max
	COOLING METHOD	*6 Forced cooling (internal fan)
WARRANTY	WARRANTY	*7 5 years (subject to the operating conditions)

*1 This is the result of measurement of the testing board with capacitors of 22 μ F and 0.1 μ F placed at 150 mm from the output terminals by a 20 MHz oscilloscope or a ripple-noise meter equivalent to Keisoku-Giken RM103.
See 1.6 of Instruction Manual for more details.

*2 Consult us about dynamic load and input response.

*3 Drift is the change in DC output for an eight hour period after a half-hour warm-up at 25°C.

*4 Output power derating is required. See 3.2 in Instruction Manual.

*5 Consult us about other classes.

*6 The fan speed slows down or stops at no load.

*7 See 3.3 in Instruction Manual for more details.

* Do not use the power supply in overcurrent conditions or in unspecified input voltage ranges. Otherwise the internal components may be damaged.


* Parallel operation is not possible with this mode.

* Sound noise may be heard from the power supply when used for pulse load.

Features

- Cost-effective
- Longer life (see Instruction Manual)
- Low profile (meets 2U height = 61 mm or 2.4 inches)
- Wide operating temperature range (-20°C to +70°C see instruction manual)
- Stop or slow fan speed at no load

Block diagram



External view

