


Tous droits strictement réservés. Reproduction ou communication à des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire.
Propriété de F C I b.v.



All rights strictly reserved.
 Whatever is not permitted
 Property of F C I b.v.



-
- Technical drawing of a plate with a grid of holes. The drawing shows a rectangular plate with a wavy left edge. A grid of 12 rows and 12 columns of holes is shown. The holes are labeled with diameters: 12 holes are labeled $\varnothing 0.10$ and 12 holes are labeled $\varnothing 0.10 +0.05 / 0$. Dimensions are given: 3 ± 0.15 , 6, 4, 2, 1, 4, 2, $2.05 +0.05 / 0$, $1.5 +0.1 / 0$, $0.6 +0.2 / -0.1$, and 3 ± 0.15 . A note "SEE NOTE 4." is present.




mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		 www.fciconnect.com																										
<table border="1"> <tr> <td>l</td><td>tr</td><td>ecn</td><td>no</td><td>date</td></tr> <tr> <td>K</td><td></td><td>DG04-094</td><td>CLu</td><td>04/21/21</td></tr> <tr> <td>L</td><td></td><td>DG06-0477</td><td>Cen</td><td>11/20/06</td></tr> <tr> <td>M</td><td></td><td>DG07-0168</td><td>Cen</td><td>05/08/07</td></tr> <tr> <td>N</td><td></td><td>DG09-0168</td><td>Cen</td><td>06/06/09</td></tr> </table>				l	tr	ecn	no	date	K		DG04-094	CLu	04/21/21	L		DG06-0477	Cen	11/20/06	M		DG07-0168	Cen	05/08/07	N		DG09-0168	Cen	06/06/09	linear		projection		 RA FEMALE SIGNAL STB 48 mm VERSION	
l	tr	ecn	no	date																														
K		DG04-094	CLu	04/21/21																														
L		DG06-0477	Cen	11/20/06																														
M		DG07-0168	Cen	05/08/07																														
N		DG09-0168	Cen	06/06/09																														
				angles		 mm		product family METRAL(tm) size/dwg no																										
				engr H. Bouwknegt 940308		scale 5:1		code 213																										
				chr A van Zanten 000530		A2		70229																										
				app H van Woensel 900918				sheet 1 of 3																										
sheet revision index sheet				N N 1 2 3																														



All rights strictly reserved. Reproduction or issue in third parties is any form without written authority from the proprietor.
 Property of F C I b.v.
 © F C I b.v.

Tous droits strictement réservés. Reproduction ou communication à des tiers sans autorisation écrite du propriétaire.
 Propriété de F C I b.v.
 © F C I b.v.



[M]
D
17




NOTES:

- | | | | | | | | | | |
|----------------|-----|-------|------|---------------------------------------|--|---|--|--|--|
| mat'l. code | | | | tolerances unless otherwise specified | | CUSTOMER COPY | | 
***fciconnect.com | |
| ltr | ecn | ndcr | date | linear | | projection title | | RA FEMALE SIGNAL | |
| N | | | | | |  | | STB 48 mm VERSION | |
| | | | | angles | |  | | product family METRAL(tn) | |
| | | | | dir. I. de Bil 970529 | | size/wg no | | code 213 | |
| | | | | engr. P. Schalk 970529 | | scale A2 | | sheet 2 of 2 | |
| | | | | chr. P. Schalk 970529 | | | | | |
| | | | | app'd H. Coolmans 970529 | | | | | |
| sheet revision | | sheet | | | | | | | |
| index | | | | | | | | | |


PC BOARD VERSIONS		
PRODUCTNR:	PCB THICKNESS	DIM "A"
70229-X03/X03LF	1.6	2.90
70229-X13/X13LF	2.4	3.53



PLATING CONTACT AREA:	
PRODUCT NR:	PERFORMANCE LEVEL:
70229-1YZ/1YZLF	TELCORDIA CO
70229-2YZ/2YZLF	CUSTOMER SPECIAL
70229-3YZ/3YZLF	CUSTOMER SPECIAL




PRODUCT AFTER HOT RIVETTING.



NOTES:

- BODY MAT'L: LIQUID CRYSTAL POLYMER 30% GLASS
FLAME RETARDANT ACC. UL 94-V0
- TERMINAL MATERIAL: PHOSPHOR BRONZE.
- PLATING SOLDER TAILS 2-8 um SnPb 90-97 OR 2-8 um PURE Sn
- INDICATED HOLES ARE UNPLATED.
- PRODUCT MARKING: PART NUMBER & BATCH ID.
- THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER
COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- THE HOUSING WILL WITHSTAND EXPOSURE TO 260DEGREE PEAK
TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER
APPLICATION.
- DIAMOND LOCATION PEG ARE ONLY EXISTED ON THE
BOTH SIDES OF PRODUCT.



RECOMMENDED HOLE PATTERN,
COMPONENT SIDE.

mat'l. code		tolerances unless otherwise specified		CUSTOMER COPY		FCI	
l	tr	ec	n	dd	date	linear	projection
N							title
							RA FEMALE SIGNAL
							STB 48 mm VERSION
							product family METRAL(tm)
							size dwg no
							213
							sheet
							3 of-
sheet	revision						
index	sheet						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

FCI:

[70229-112LF](#) [70229-101](#) [70299-196LF](#) [70299-199LF](#) [70229-101LF](#) [70299-1101LF](#) [70299-1100LF](#)