

Aluminum Capacitors Little-Lytic Electrolytics



Fig.1 Component outlines

QUICK REFERENCE DATA


DESCRIPTION	VALUE
Operating temperature	- 40 °C to + 105 °C
Tolerance on C _R	G = + 75 %, - 10 % and F = + 50 %, - 10 %
Ripple current	10 Ω to 600 Ω max. at 120 Hz, depending upon capacitance
Life validation test 2000 hours at + 85 °C	After test, capacitance value shall not have changed by more than ± 20 %, the equivalent series resistance in ohms shall not have exceeded 150 % of initial requirement and the leakage current shall not have exceeded the initial requirement
DC leakage current	Maximum DC leakage current at + 25 °C for all capacitors is 15 µA, except units in case code DD, which is 15.8 µA
Shelf test 250 hours at + 85 °C, with no voltage applied	The capacitance and equivalent series resistance shall meet the initial requirements and the DC leakage current shall not exceed 300 % of the initial requirement

FEATURES

- Proven dependable performance in the industrial and electronic equipment with either transistor or modified electron-tube circuits
- All terminal connections welded, eliminating possibility of open or intermittent contacts occasionally found in pressure joints of conventional capacitors
- Superior in size, performance characteristics, shelf life, construction and reliability
- Metal-encased with clear plastic outer insulating sleeve
- Excellent circuit performance when used as coupling capacitors
- Minimum drain and long battery life when used in battery bypass applications
- Better performance under life test than most miniature aluminum electrolytic capacitors
- Axial lead




CAPACITANCE VS. TEMPERATURE



DIMENSIONS in inches [millimeters]

CASE CODE	D	L	CASE CODE	D	L
BA	0.260 [6.604]	0.536 [13.614]	DC	0.385 [9.779]	0.848 [21.539]
BB	0.260 [6.604]	0.723 [18.364]	DD	0.385 [9.779]	0.973 [24.714]
CB	0.322 [8.179]	0.723 [18.364]	DF	0.385 [9.779]	1.286 [32.664]
CC	0.322 [8.179]	0.848 [21.539]	DH	0.385 [9.779]	1.536 [39.014]
DB	0.385 [9.779]	0.723 [18.364]			

DIMENSIONS AND AVAILABLE FORMS



ORDERING EXAMPLE

Order by distribution part no. Example: TE1055

Note

For lead (Pb)-free/RoHS compliant products add the suffix “-E3” to the shortened Distribution part. no.

Example TE1055-E3

Note

For lead (Pb)-free/RoHS compliant products add the suffix “E3” to the standard OEM part no.

Example: 30D256G003BA2E3

STANDARD RATINGS			
CAPACITANCE (μF)	CASE CODE	DISTRIBUTOR DIVISION PART NUMBER	SPRAGUE O.E.M. PART NUMBER
0 - 3 WV_{DC}			
1.0	-	See 0 - 50 WV _{DC} listing	-
2.0	-	See 0 - 50 WV _{DC} listing	-
3.0	-	See 0 - 50 WV _{DC} listing	-
4.0	-	See 0 - 50 WV _{DC} listing	-
5.0	-	See 0 - 25 WV _{DC} listing	-
6.0	-	See 0 - 25 WV _{DC} listing	-
8.0	-	See 0 - 25 WV _{DC} listing	-
10.0	-	See 0 - 16 WV _{DC} listing	-
15.0	-	See 0 - 12 WV _{DC} listing	-
20.0	-	See 0 - 6 WV _{DC} listing	-
25.0	BA	TE1055	30D256G003BA2
50.0	-	See 0 - 6 WV _{DC} listing	-
75.0	-	See 0 - 6 WV _{DC} listing	-
100.0	CB	TE1059.5	30D107G003CB2
200.0	CC	TE1064	30D207G003CC2
300.0	DC	TE1066	30D307G003DC2
500.0	DF	TE1068	30D507G003DF2
0 - 6 WV_{DC}			
1.0	-	See 0 - 50 WV _{DC} listing	-
2.0	-	See 0 - 50 WV _{DC} listing	-
3.0	-	See 0 - 50 WV _{DC} listing	-
4.0	-	See 0 - 50 WV _{DC} listing	-
5.0	-	See 0 - 25 WV _{DC} listing	-
6.0	-	See 0 - 25 WV _{DC} listing	-
8.0	-	See 0 - 25 WV _{DC} listing	-
10.0	-	See 0 - 16 WV _{DC} listing	-
15.0	-	See 0 - 12 WV _{DC} listing	-
20.0	BA	TE1090	30D206G006BA2
25.0	-	See 0 - 16 WV _{DC} listing	-
35.0	BB	TE1093	30D356G006BB2
50.0	BB	TE1100	30D506G006BB2
75.0	CB	TE1101.5	30D756G006CB2
100.0	-	See 0 - 12 WV _{DC} listing	-
200.0	DC	TE1104	30D207G006DC2
250.0	DD	TE1105	30D257G006DD2
300.0	DD	TE1106	30D307G006DD2
400.0	DF	TE1107	30D407G006DF2
500.0	DH	TE1107.5	30D507G006DH2
600.0	DH	TE1108.5	30D607G006DH2

Aluminum Capacitors
Little-Lytic Electrolytics

Vishay Sprague

STANDARD RATINGS			
CAPACITANCE (μF)	CASE CODE	DISTRIBUTOR DIVISION PART NUMBER	SPRAGUE O.E.M. PART NUMBER
0 - 12 WV_{DC}			
1.0	-	See 0 - 50 WV_{DC} listing	-
2.0	-	See 0 - 50 WV_{DC} listing	-
3.0	-	See 0 - 50 WV_{DC} listing	-
4.0	-	See 0 - 50 WV_{DC} listing	-
5.0	-	See 0 - 25 WV_{DC} listing	-
6.0	-	See 0 - 25 WV_{DC} listing	-
8.0	-	See 0 - 25 WV_{DC} listing	-
10.0	-	See 0 - 16 WV_{DC} listing	-
15.0	BA	TE1129	30D156G012BA2
20.0	-	See 0 - 16 WV_{DC} listing	-
25.0	-	See 0 - 16 WV_{DC} listing	-
50.0	-	See 0 - 16 WV_{DC} listing	-
60.0	CB	TE1133.5	30D606G012CB2
75.0	-	See 0 - 16 WV_{DC} listing	-
100.0	CC	TE1135	30D107G012CC2
150.0	-	See 0 - 16 WV_{DC} listing	—
200.0	-	See 0 - 16 WV_{DC} listing	—
250.0	-	See 0 - 16 WV_{DC} listing	—
290.0	DF	TE1139	30D297G012DF2
0 - 16 WV_{DC}			
1.0	-	See 0 - 50 WV_{DC} listing	-
2.0	-	See 0 - 50 WV_{DC} listing	-
3.0	-	See 0 - 50 WV_{DC} listing	-
4.0	-	See 0 - 50 WV_{DC} listing	-
5.0	-	See 0 - 25 WV_{DC} listing	-
6.0	-	See 0 - 25 WV_{DC} listing	-
8.0	-	See 0 - 25 WV_{DC} listing	-
10.0	BA	TE1155	30D106G016BA2
15.0	-	See 0 - 25 WV_{DC} listing	-
20.0	BB	TE1157	30D206G016BB2
25.0	BB	TE1157.1	30D256G016BB2
30.0	-	See 0 - 25 WV_{DC} listing	-
35.0	-	See 0 - 25 WV_{DC} listing	-
50.0	CB	TE1160	30D506G016CB2
75.0	CC	TE1161	30D756G016CC2
100.0	DC	TE1162	30D107G016DC2
150.0	DD	TE1163	30D157G016DD2
200.0	DF	TE1164	30D207G016DF2
250.0	DF	TE1164.5	30D257G016DF2
300.0	DH	TE1165.5	30D307G016DH2
350.0	DH	TE1166	30D357G016DH2

STANDARD RATINGS

CAPACITANCE (μ F)	CASE CODE	DISTRIBUTOR DIVISION PART NUMBER	SPRAGUE O.E.M. PART NUMBER
0 - 25 WV_{DC}			
1.0	-	See 0 - 50 WV _{DC} listing	-
2.0	-	See 0 - 50 WV _{DC} listing	-
3.0	-	See 0 - 50 WV _{DC} listing	-
4.0	-	See 0 - 50 WV _{DC} listing	-
5.0	BA	TE1202	30D505G025BA2
6.0	BA	TE1203	30D605G025BA2
8.0	BA	TE1203.5	30D805G025BA2
10.0	BB	TE1204	30D106G025BB2
15.0	BB	TE1205	30D156G025BB2
20.0	CB	TE1206	30D206G025CB2
25.0	CB	TE1207	30D256G025CB2
30.0	CB	TE1207.5	30D306G025CB2
35.0	CB	TE1208	30D356G025CB2
50.0	CC	TE1209	30D506G025CC2
75.0	DC	TE1210	30D756G025DC2
100.0	DD	TE1211	30D107G025DD2
150.0	DF	TE1212	30D157G025DF2
200.0	DH	TE1213	30D207G025DH2
0 - 50 WV_{DC}			
1.0	BA	TE1300	30D105G050BA2
2.0	BA	TE1301	30D205G050BA2
3.0	BA	TE1302	30D305G050BA2
4.0	BA	TE1302.1	30D405G050BA2
5.0	BB	TE1303	30D505G050BB2
6.0	BB	TE1303.1	30D605G050BB2
8.0	BB	TE1303.3	30D805G050BB2
10.0	CB	TE1304	30D106G050CB2
15.0	CB	TE1304.2	30D156G050CB2
20.0	CC	TE1305	30D206G050CC2
25.0	CC	TE1305.5	30D256G050CC2
35.0	DC	TE1306	30D356G050DC2
50.0	DD	TE1307	30D506G050DD2
75.0	DF	TE1308	30D756G050DF2
100.0	DH	TE1309	30D107G050DH2
100 WV_{DC}			
1.0	BA	TE1400	30D105F100BA2
2.0	BB	TE1401	30D205F100BB2
3.0	CB	TE1402	30D305F100CB2
4.0	CB	TE1403	30D405F100CB2
5.0	CC	TE1404	30D505F100CC2
10.0	DC	TE1407	30D106F100DC2
15.0	DD	TE1408	30D156F100DD2
20.0	DF	TE1409	30D206F100DF2
25.0	DH	TE1410	30D256F100DH2
30.0	DH	TE1411	30D306F100DH2
150 WV_{DC}			
1.0	BA	TE1500	30D105F150BA2
2.0	BB	TE1501	30D205F150BB2
3.0	CB	TE1502	30D305F150CB2
4.0	CC	TE1503	30D405F150CC2
5.0	CC	TE1504	30D505F150CC2
8.0	DC	TE1506	30D805F150DC2
10.0	DD	TE1507	30D106F150DD2
15.0	DF	TE1508.1	30D156F150DF2
20.0	DH	TE1509	30D206F150DH2



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk and agree to fully indemnify and hold Vishay and its distributors harmless from and against any and all claims, liabilities, expenses and damages arising or resulting in connection with such use or sale, including attorneys fees, even if such claim alleges that Vishay or its distributor was negligent regarding the design or manufacture of the part. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.