


DESCRIPTION


- 897.5 MHz SAW bandpass filter with a 40 MHz typical 3dB bandwidth.
- 3 x 3 mm ceramic LCC package.
- RoHS compliant.

TYPICAL PERFORMANCE



Frequency Response



S11 (747.5-1047.5 MHz)



S22 (747.5-1047.5 MHz)



SPECIFICATION


Parameter	Min	Typ	Max	Units
Center Frequency (Fc) ¹	-	897.5	-	MHz
Insertion Loss (880 to 915 MHz)	-	2.1	3.0	dB
Amplitude Ripple (880 to 915 MHz)	-	1.0	2.0	dB p-p
Input VSWR (880 to 915 MHz)	-	2	2.6	:1
Output VSWR (880 to 915 MHz)	-	2	2.6	:1
Attenuation (1 to 860 MHz) ²	17	19	-	dB
Attenuation (925 to 935 MHz) ²	5	12.4	-	dB
Attenuation (935 to 960 MHz) ²	20	24	-	dB
Attenuation (980 to 2000 MHz) ²	20	22	-	dB
Source Impedance	50 ohms single-ended			
Load Impedance	50 ohms single ended			
Ambient Temperature	-	25	-	° C

Notes: 1. Fixed reference point.
2. Reference level from 0 dB.

MAXIMUM RATINGS


Parameter	Min	Max	Units
Storage Temperature Range	-40	85	°C
Operating Temperature Range	-20	75	°C
Input Power Level	-	5	dBm
DC Voltage	-	3	Volts

MATCHING CIRCUIT



Notes: Matching components are not required; 50 ohm single-ended system.

PACKAGE OUTLINE



Package Material:
 Body: Al_2O_3 ceramic
 Lid: Kovar, Ni plated
 Terminations: Au plating 1 μ m min,
 over a 1.3-8.9 μ m Ni plating


Units: mm

Typical tolerances are ± 0.15 mm
 except where indicated.


Pad Configuration:

Input: B
 Output: E
 Ground: A, C, D, F

SUGGESTED FOOTPRINT



MARKING



ISO 9001
Registered

All specifications are believed to be accurate and reliable. However, Spectrum Microwave reserves the right to make changes without notice.
© 2010 All rights reserved.

Spectrum Microwave
324 Clark Street, Worcester, MA 01606, USA • Phone 1-508-852-5400 • Fax 1-508-852-8456
www.SpectrumMicrowave.com

DSSF0898BA02546S Rev A 7-Apr-2010
ECN 36650 Page 4 of 4