

Low Power Bipolar Transistors





BC109 Series



Feature:

- NPN Silicon Planar Epitaxial Transistors


TO-18 Metal Can Package



Specification Table

Dimensions	Minimum	Maximum
A	5.24	5.84
B	4.52	4.97
C	4.31	5.33
D	0.4	0.53
E	-	0.76
F	-	1.27
G	-	2.97
H	0.91	1.17
J	0.71	1.21
K	12.7	-
L	45°	

Dimensions : Millimetres



Pin Configuration:

- Emitter
- Base
- Collector

Absolute Maximum Ratings

Description	Symbol	BC109	Unit
Collector - Emitter Voltage	V_{CEO}	25	V
Collector - Base Voltage	V_{CBO}	30	
Emitter-Base Voltage	V_{EBO}	5	
Collector Current Continuous	I_C	0.2	A



Low Power Bipolar Transistors



BC109 Series

Absolute Maximum Ratings

Description	Symbol	BC109	Unit
Power Dissipation at $T_a = 25^\circ\text{C}$ Derate above 25°C	P_D	0.6 2.28	W mW / $^\circ\text{C}$
Power Dissipation at $T_C = 25^\circ\text{C}$ Derate above 25°C		1 6.67	
Operating and Storage Junction Temperature Range	T_J, T_{stg}	-65 to +200	$^\circ\text{C}$
Thermal Resistance			
Junction to Case	$R_{th(j-c)}$	175	$^\circ\text{C} / \text{W}$

Electrical Characteristics ($T_a = 25^\circ\text{C}$ unless otherwise specified)

Description	Symbol	Test Condition	Minimum	Maximum	Unit
Collector - Emitter Voltage	V_{CEO}	$I_C = 2 \text{ mA}, I_B = 0$	25	-	V
Emitter Base Voltage	V_{EBO}	$I_E = 10 \mu\text{A}, I_C = 0$	5	-	
Collector Cut off Current	I_{CBO}	$V_{CB} = 25 \text{ V}, I_E = 0$ $T_{amb} = 125^\circ\text{C}$	-	15	nA
		$V_{CB} = 25 \text{ V}, I_E = 0$	-	4	μA
DC Current	h_{FE}	$I_C = 10 \mu\text{A}, V_{CE} = 5 \text{ V}$ B Group	40	-	-
		C Group	100		
		$I_C = 2 \text{ mA}, V_{CE} = 5 \text{ V}$ B Group	200	800	
		C Group	200 420	450 800	
Base Emitter Saturation Voltage	$V_{BE(Sat)}$	$I_C = 10 \text{ mA}, I_B = 0.5 \text{ mA}$ $I_C = 100 \text{ mA}, I_B = 5 \text{ mA}$	-	0.83 1.05	V
Collector Emitter Saturation Voltage	$V_{CE(Sat)}$		-	0.25 0.6	
Base Emitter On Voltage	$V_{BE(on)}$	$I_C = 2 \text{ mA}, V_{CE} = 5 \text{ V}$	0.55	0.7	
		$I_C = 10 \text{ mA}, V_{CE} = 5 \text{ V}$	-	0.77	
Collector Knee Voltage	$V_{CE(K)}$	$I_C = 10 \text{ mA}, I_B = \text{The value for which } I_C = 11 \text{ mA at } V_{CE} = 1 \text{ V}$	-	0.6	
Transition Frequency	f_t	$V_{CE} = 5 \text{ V}, I_C = 10 \text{ mA}, f = 100 \text{ MHz}$	150	-	MHz
Noise Figure	NF	$V_{CE} = 5 \text{ V}, I_C = 0.2 \text{ mA}$ $R_g = 2 \text{ k}\Omega$	-	4	dB
		$F = 30 \text{ Hz to } 15 \text{ KHz}$ $F = 1 \text{ KHz}, B = 200 \text{ Hz}$		4	dB
Output Capacitance	C_{obo}	$V_{CB} = 10 \text{ V}, f = 1 \text{ MHz}$	-	4.5	pF
Small Signal Current Gain	h_{fe}	ALL $f = 1 \text{ kHz}$ $I_C = 2 \text{ mA}, V_{CE} = 5 \text{ V}$	240	900	-
		B Group	240	500	
		C Group	450	900	

Low Power Bipolar Transistors

BC109 Series



Electrical Characteristics ($T_a = 25^\circ\text{C}$ unless otherwise specified)

Description	Symbol	Test Condition	Minimum	Maximum	Unit
Input Impedance	h_{ie}	$I_C = 2 \text{ mA}$, $V_{CE} = 5 \text{ V}$ B Group C Group	3.2 6	8.5 15	$K\Omega$ $K\Omega$
Output Admittance	h_{oe}	$I_C = 2 \text{ mA}$, $V_{CE} = 5 \text{ V}$ B Group C Group	-	60 110	$\mu\Omega$

Part Number Table

Package	Part Number
Transistor, NPN, TO-18	BC109
Transistor, NPN, TO-18	BC109B
Transistor, NPN, TO-18	BC109C

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.