

Standard Recovery Power Diodes



S2 Series




Features:

- For surface mounted application
- Glass passivated junction chip
- Low forward voltage drop
- Easy pick and place
- High surge current capability
- High temperature soldering : 250°C / 10 seconds at terminals

Mechanical Data


Cases	: Moulded plastic
Terminals	: Solder plated
Polarity	: Indicated by cathode band

SMB/DO-214AA



Dimensions : Inches (Millimetres)

Foot Print



Dimensions

Length	Depth	Width	X	Y	Z
5.28	2.61	3.73	3.3	2.21	8

Dimensions : Millimetres

Standard Recovery Power Diodes



S2 Series

Maximum Ratings and Electrical Characteristics

Rating at 25°C ambient temperature unless otherwise specified. Single phase, half wave, 60 Hz, resistive or inductive load. For capacitive load, derate current by 20%

Type Number	S2A	S2D	S2G	S2J	Unit
Maximum Recurrent Peak Reverse Voltage	50	200	400	600	V
Maximum RMS Voltage	35	140	280	420	
Maximum DC Blocking Voltage	50	200	400	600	
Maximum Average Forward Rectified Current at T _L = 100°C	2				A
Peak Forward Surge Current, 8.3 ms Single Half Sine-Wave Superimposed on Rated Load (JEDEC Method)	50				
Maximum Instantaneous Forward Voltage at 2 A	1.15				V
Maximum DC Reverse Current at T _A = 25°C at Rated DC Blocking Voltage at T _A = 125°C	5 125				μA
Maximum Reverse Recovery Time (Note 1)	2				μS
Typical Junction Capacitance (Note 2)	30				pF
Operating Temperature Range T _J	-55 to +150				°C
Storage Temperature Range T _{STG}					

- Notes :** 1. Reverse recovery test conditions : $I_F = 0.5\text{ A}$, $I_R = 1\text{ A}$, $I_{RR} = 0.25\text{ A}$
2. Measured at 1 MHz and applied $V_R = 4\text{ V}$

Ratings and Characteristic Curves

Figure 1 Maximum Forward Current Derating Curve





Figure 2 Maximum Forward Current Derating Curve



Standard Recovery Power Diodes



S2 Series

Figure 3 Typical Forward Characteristics




Figure 4 Typical Reverse Characteristics





Figure 5 Typical Junction Capacitance



Specification Table

V_{RRM} Maximum (V)	I_{AV} (A)	I_{FSM} (A)	V_F (V) at $I_F = 2\text{ A}$ at 25°C	Package	Part Number
50	2	50	1.15	DO-214AA (SMB)	S2A
200					S2D
400					S2G
600					S2J

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.