




Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.

MARKETING SALES DRAWING
DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []



MIN. CAP. pF	WORKING VOLTAGE		I.R. MIN. @ 100 (VDC.)	DWV (VDC)	CURRENT Idc.	MINIMUM NO LOAD INSERTION LOSS (dB) AT 25°C PER MIL-STD-220			
	85°C	125°C				10 MHz	100 MHz	1 GHz	10 GHz
3000	125	50	10 G Ω	250	15	7	50	65	60

X-2015 Rev-0	REVISION RECORD									
	Original Release	0								
	C.O.	2910								
	RND TO COMP FMT.									
	S.M. 07-13-00									
	20000717-5-07	1								
	ADDED DIM. .050, DWV & I.R.									
	DIM. .140 WAS .138, .092 WAS									
	.100 & .183 WAS .196.									
	S.M. 01-08-04									
20040108-2-01		2								

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tusonix:](#)

[4100-003LF](#)