




13		12		11		10		9		8		7		6		5		4		3		2		1	
CKT. SIZE	PART NUMBER	ENG. NUMBER SDA-70204-	DIM. "A"		DIM. "B"		DIM. "C"		CKT. SIZE	PART NUMBER	ENG. NUMBER SDA-70204-	DIM. "A"		DIM. "B"		DIM. "C"		3° MAX. ROTATION PERMISSIBLE  DETAIL "V" SCALE = 20:1  DETAIL "S"							
			MM	IN.	MM	IN.	MM	IN.				MM	IN.	MM	IN.	MM	IN.							MM	IN.
08	25-02-6008	0259	7,62	.300	17,78	.700	20,32	.800	42	25-02-6042	0276	50,80	2.000	60,96	2.400	63,50	2.500								
10	25-02-6010	0260	10,16	.400	20,32	.800	22,86	.900	44	25-02-6044	0277	53,34	2.100	63,50	2.500	66,04	2.600								
12	25-02-6012	0261	12,70	.500	22,86	.900	25,40	1.000	46	25-02-6046	0278	55,88	2.200	66,04	2.600	68,58	2.700								
14	25-02-6014	0262	15,24	.600	25,40	1.000	27,94	1.100	48	25-02-6048	0279	58,42	2.300	68,58	2.700	71,12	2.800								
16	25-02-6016	0263	17,78	.700	27,94	1.100	30,48	1.200	50	25-02-6050	0280	60,96	2.400	71,12	2.800	73,66	2.900								
18	25-02-6018	0264	20,32	.800	30,48	1.200	33,02	1.300	52	25-02-6052	0281	63,50	2.500	73,66	2.900	76,20	3.000								
20	25-02-6020	0265	22,86	.900	33,02	1.300	35,56	1.400	54	25-02-6054	0282	66,04	2.600	76,20	3.000	78,74	3.100								
22	25-02-6022	0266	25,40	1.000	35,56	1.400	38,10	1.500	56	25-02-6056	0283	68,58	2.700	78,74	3.100	81,28	3.200								
24	25-02-6024	0267	27,94	1.100	38,10	1.500	40,64	1.600	58	25-02-6058	0284	71,12	2.800	81,28	3.200	83,82	3.300								
26	25-02-6026	0268	30,48	1.200	40,64	1.600	43,10	1.700	60	25-02-6060	0285	73,66	2.900	83,82	3.300	86,36	3.400								
28	25-02-6028	0269	33,02	1.300	43,10	1.700	45,72	1.800	62	25-02-6062	0286	76,20	3.000	86,36	3.400	88,90	3.500								
30	25-02-6030	0270	35,56	1.400	45,72	1.800	48,26	1.900	64	25-02-6064	0287	78,74	3.100	88,90	3.500	91,44	3.600								
32	25-02-6032	0271	38,10	1.500	48,26	1.900	50,80	2.000	66	25-02-6066	0288	81,28	3.200	91,44	3.600	93,98	3.700								
34	25-02-6034	0272	40,64	1.600	50,80	2.000	53,34	2.100	68	25-02-6068	0289	83,82	3.300	93,98	3.700	96,52	3.800								
36	25-02-6036	0273	43,10	1.700	53,34	2.100	55,88	2.200	70	25-02-6070	0290	86,36	3.400	96,52	3.800	99,06	3.900								
38	25-02-6038	0274	45,72	1.800	55,88	2.200	58,42	2.300	72	25-02-6072	0291	88,90	3.500	99,06	3.900	101,60	4.000								
40	25-02-6040	0275	48,26	1.900	58,42	2.300	60,96	2.400																	



NOTES:

1. WAFER MATERIAL: GLASS FILLED NYLON; COLOR: BLACK
2. PIN MATERIAL: COPPER ALLOY
3. PIN PLATING:
 - TIP: 15 MICROINCHES MINIMUM GOLD IN SELECTED AREA
 - TAIL: 75 MICROINCHES MINIMUM TIN IN SELECTED AREA OVER NICKEL UNDERPLATE OVER-ALL
4. PINS MUST MEET SOLDERABILITY SPEC. NO. 152
5. PIN PUSH-OUT FORCE (1.81 KG)/4 LBS MINIMUM
6. REFER TO P.S. NO. 70204
7. STANDARD PACKAGING PER: PK-70873-0070

CORRECT DIMENSION	EC NO: UCP2011-3892	DRAWN BY: DRWINMS BARRA	CHKD: APPR: MILLER	DESCRIPTION	REV	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION			
							mm	INCH	MM/IN	DATE						
							4 PLACES	± .005	± .005	DRAWN BY: JAS						
							3 PLACES	± .005	± .010	CHECKED BY: EIK						
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	SIZE	MATERIAL NO.	DOCUMENT NO.	SHEET NO.	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	ANGULAR	± 1/2°		DATE		MOLEX	MOLEX INCORPORATED	SDA-70204-0257-0320			
							± .005		DATE							
							± .005		DATE							
							± .005		DATE							