



Microwave Coaxial Connectors

Microwave Coaxial Cable Connectors



MM4829-2702



(in mm)

Dimensions

MM5829-2700



(in mm)





Dimensions

Part Number	Rated Voltage (Vrms)	Frequency Rating (GHz)	Temperature Range	VSWR
MM4829-2702	30	to 6.0	-40 to +85°C	1.3 max. (DC to 3GHz)
MM5829-2700	30	to 12	-40 to +85°C	1.3 max. (DC to 3GHz)
MXHP32	30	to 6.0	-40 to +85°C	1.3 max. (DC to 3GHz)
MXJA01	30	to 12	-40 to +85°C	1.3 max. (DC to 3GHz)


Impedance: 50ohm

Microwave Coaxial Connectors


Microwave Coaxial Connectors with Switch




Measurement Probe for MM8030-2610/MM8130-2600/MM8430-2610
(P/N: MM126320)




Measurement Probe for MM8030-2610
(P/N: MXHQ87WJ3000)



Measurement Probe for MM8130-2600/MM8430-2610
(P/N: MXHS83QE3000)




Measurement Probe for MM8930-2600
(P/N: MM126515)



⚠Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

Continued from the preceding page.

Measurement Probe for MM8930-2600
(P/N: MXHQ87PA3000)



(in mm)

Part Number	Rated Voltage (Vrms)	Frequency Rating (GHz)	Temperature Range	VSWR
MM8030-2610	30	to 11	-40 to +85°C	1.2 max. (DC to 3GHz)
MM8130-2600	30	to 6	-40 to +85°C	1.2 max. (DC to 3GHz)
MM8430-2610	30	to 6	-40 to +85°C	1.2 max. (DC to 3GHz)
MM8930-2600	30	to 6	-40 to +85°C	1.2 max. (DC to 3GHz)

Impedance: 50ohm