

To our customers,

Old Company Name in Catalogs and Other Documents

On April 1st, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: <http://www.renesas.com>

April 1st, 2010
Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (<http://www.renesas.com>)

Send any inquiries to <http://www.renesas.com/inquiry>.

Notice

1. All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
2. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
7. Renesas Electronics products are classified according to the following three quality grades: "Standard", "High Quality", and "Specific". The recommended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as "Specific" without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics product for any application for which it is not intended without the prior written consent of Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as "Specific" or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is "Standard" unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.
 - "Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.
 - "High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; safety equipment; and medical equipment not specifically designed for life support.
 - "Specific": Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.

(Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.

(Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.

NPN SILICON GERMANIUM RF TRANSISTOR

NESG220033

NPN SiGe RF TRANSISTOR FOR UHF-BAND, LOW NOISE, LOW DISTORTION AMPLIFICATION 3-PIN MINIMOLD (33 PKG)

FEATURES

- The device is an ideal choice for low noise, low distortion amplification.
NF = 0.75 dB TYP. @ $V_{CE} = 5\text{ V}$, $I_C = 10\text{ mA}$, $f = 1\text{ GHz}$
- $P_{O(1\text{ dB})} = 21.5\text{ dBm}$ TYP. @ $V_{CE} = 5\text{ V}$, $I_{C(\text{set})} = 40\text{ mA}$, $f = 1\text{ GHz}$
- $OIP_3 = 35\text{ dBm}$ TYP. @ $V_{CE} = 5\text{ V}$, $I_{C(\text{set})} = 40\text{ mA}$, $f = 1\text{ GHz}$
- Maximum stable power gain: $MSG = 14.0\text{ dB}$ TYP. @ $V_{CE} = 5\text{ V}$, $I_C = 40\text{ mA}$, $f = 1\text{ GHz}$
- SiGe HBT technology (UHS2) : $f_T = 12.5\text{ GHz}$
- This product is improvement of ESD of NESG2xxx series.
- 3-pin minimold (33 PKG)

ORDERING INFORMATION

Part Number	Order Number	Package	Quantity	Supplying Form
NESG220033	NESG220033-A	3-pin minimold (33 PKG) (Pb-Free)	50 pcs (Non reel)	<ul style="list-style-type: none"> 8 mm wide embossed taping Pin 3 (Collector) face the perforation side of the tape
NESG220033-T1B	NESG220033-T1B-A		3 kpcs/reel	

Remark To order evaluation samples, please contact your nearby sales office.
Unit sample quantity is 50 pcs.

ABSOLUTE MAXIMUM RATINGS ($T_A = +25^\circ\text{C}$)

Parameter	Symbol	Ratings	Unit
Collector to Base Voltage	V_{CBO}	5.5	V
Collector to Emitter Voltage	V_{CES}	13	V
Collector to Emitter Voltage	V_{CEO}	5.5	V
Base Current ^{Note 1}	I_B	36	mA
Collector Current	I_C	200	mA
Total Power Dissipation	P_{tot} ^{Note 2}	480	mW
Junction Temperature	T_J	150	$^\circ\text{C}$
Storage Temperature	T_{stg}	-65 to +150	$^\circ\text{C}$

Notes 1. Depend on the ESD protect device.

2. Mounted on 3.8 cm × 9.0 cm × 0.8 mm (t) glass epoxy PWB

Caution Observe precautions when handling because these devices are sensitive to electrostatic discharge.

The information in this document is subject to change without notice. Before using this document, please confirm that this is the latest version.
Not all products and/or types are available in every country. Please check with an NEC Electronics sales representative for availability and additional information.

THERMAL RESISTANCE (T_A = +25°C)

Parameter	Symbol	Ratings	Unit
Thermal Resistance from Junction to Ambient ^{Note}	R _{thj-a}	260	°C/W

Note Mounted on 3.8 cm × 9.0 cm × 0.8 mm (t) glass epoxy PWB

RECOMMENDED OPERATING RANGE (T_A = +25°C)

Parameter	Symbol	MIN.	TYP.	MAX.	Unit
Collector Current	I _C	–	40	–	mA

<R>

ELECTRICAL CHARACTERISTICS (T_A = +25°C)

Parameter	Symbol	Test Conditions	MIN.	TYP.	MAX.	Unit
DC Characteristics						
Collector Cut-off Current	I _{CBO}	V _{CB} = 5 V, I _E = 0 mA	–	–	100	nA
Emitter Cut-off Current	I _{EBO}	V _{EB} = 0.4 V, I _C = 0 mA	–	–	100	nA
DC Current Gain	h _{FE} ^{Note 1}	V _{CE} = 5 V, I _C = 10 mA	140	180	260	–
RF Characteristics						
Gain Bandwidth Product	f _T	V _{CE} = 5 V, I _C = 40 mA, f = 1 GHz	–	12.5	–	GHz
Insertion Power Gain	S _{21e} ²	V _{CE} = 5 V, I _C = 40 mA, f = 1 GHz	11.0	13.0	–	dB
Noise Figure (1)	NF1	V _{CE} = 5 V, I _C = 10 mA, f = 1 GHz, Z _S = Z _{Sopt} , Z _L = 50 Ω	–	0.75	1.15	dB
Noise Figure (2)	NF2	V _{CE} = 5 V, I _C = 40 mA, f = 1 GHz, Z _S = Z _{Sopt} , Z _L = Z _{Lopt}	–	0.9	–	dB
Associated Gain (1)	G _{a1}	V _{CE} = 5 V, I _C = 10 mA, f = 1 GHz, Z _S = Z _{Sopt} , Z _L = 50 Ω	10.0	12.0	–	dB
Associated Gain (2)	G _{a2}	V _{CE} = 5 V, I _C = 40 mA, f = 1 GHz, Z _S = Z _{Sopt} , Z _L = Z _{Lopt}	–	13.5	–	dB
Reverse Transfer Capacitance	C _{re} ^{Note 2}	V _{CB} = 5 V, I _E = 0 mA, f = 1 MHz	–	0.7	0.9	pF
Maximum Stable Power Gain	MSG ^{Note 3}	V _{CE} = 5 V, I _C = 40 mA, f = 1 GHz	12.0	14.0	–	dB
Gain 1 dB Compression Output Power	P _O (1 dB)	V _{CE} = 5 V, I _C (set) = 40 mA, f = 1 GHz, Z _S = Z _{Sopt} , Z _L = Z _{Lopt}	–	21.5	–	dBm
Output 3rd Order Intercept Point	OIP ₃	V _{CE} = 5 V, I _C (set) = 40 mA, f = 1 GHz, Δf = 1 MHz, Z _S = Z _{Sopt} , Z _L = Z _{Lopt}	–	35	–	dBm

Notes 1. Pulse measurement: PW ≤ 350 μs, Duty Cycle ≤ 2%

2. Collector to base capacitance when the emitter grounded.


$$3. \text{MSG} = \left| \frac{S_{21}}{S_{12}} \right|$$

h_{FE} CLASSIFICATION


Rank	FB
Marking	R7B
h _{FE} Value	140 to 260

TYPICAL CHARACTERISTICS ($T_A = +25^\circ\text{C}$, unless otherwise specified)


**TOTAL POWER DISSIPATION
vs. AMBIENT TEMPERATURE**




**REVERSE TRANSFER CAPACITANCE
vs. COLLECTOR TO BASE VOLTAGE**




**COLLECTOR CURRENT vs.
BASE TO EMITTER VOLTAGE**



**COLLECTOR CURRENT vs.
BASE TO EMITTER VOLTAGE**




**COLLECTOR CURRENT vs.
COLLECTOR TO EMITTER VOLTAGE**




Remark The graphs indicate nominal characteristics.


DC CURRENT GAIN vs.
COLLECTOR CURRENT




DC CURRENT GAIN vs.
COLLECTOR CURRENT



GAIN BANDWIDTH PRODUCT
vs. COLLECTOR CURRENT




GAIN BANDWIDTH PRODUCT
vs. COLLECTOR CURRENT




Remark The graphs indicate nominal characteristics.


INSERTION POWER GAIN,
MAG, MSG vs. FREQUENCY




INSERTION POWER GAIN,
MAG, MSG vs. FREQUENCY




INSERTION POWER GAIN,
MAG, MSG vs. FREQUENCY




INSERTION POWER GAIN,
MAG, MSG vs. FREQUENCY



INSERTION POWER GAIN, MAG, MSG
vs. COLLECTOR CURRENT




INSERTION POWER GAIN, MAG, MSG
vs. COLLECTOR CURRENT




Remark The graphs indicate nominal characteristics.


NOISE FIGURE, ASSOCIATED GAIN
vs. COLLECTOR CURRENT




OUTPUT 3RD ORDER INTERCEPT POINT
vs. COLLECTOR CURRENT



OUTPUT POWER, LINEAR GAIN,
COLLECTOR CURRENT vs. INPUT POWER



EACH OUTPUT POWER, IM_3
vs. EACH INPUT POWER



Remark The graphs indicate nominal characteristics.

S-PARAMETERS

S-parameters and noise parameters are provided on our Web site in a format (S2P) that enables the direct import of the parameters to microwave circuit simulators without the need for keyboard inputs.

Click here to download S-parameters.

[RF and Microwave] → [Device Parameters]

URL <http://www.necel.com/microwave/en/>

3-PIN MINIMOLD (33 PKG) (UNIT: mm)



1. Emitter
2. Base
3. Collector

- The information in this document is current as of November, 2009. The information is subject to change without notice. For actual design-in, refer to the latest publications of NEC Electronics data sheets, etc., for the most up-to-date specifications of NEC Electronics products. Not all products and/or types are available in every country. Please check with an NEC Electronics sales representative for availability and additional information.
- No part of this document may be copied or reproduced in any form or by any means without the prior written consent of NEC Electronics. NEC Electronics assumes no responsibility for any errors that may appear in this document.
- NEC Electronics does not assume any liability for infringement of patents, copyrights or other intellectual property rights of third parties by or arising from the use of NEC Electronics products listed in this document or any other liability arising from the use of such products. No license, express, implied or otherwise, is granted under any patents, copyrights or other intellectual property rights of NEC Electronics or others.
- Descriptions of circuits, software and other related information in this document are provided for illustrative purposes in semiconductor product operation and application examples. The incorporation of these circuits, software and information in the design of a customer's equipment shall be done under the full responsibility of the customer. NEC Electronics assumes no responsibility for any losses incurred by customers or third parties arising from the use of these circuits, software and information.
- While NEC Electronics endeavors to enhance the quality and safety of NEC Electronics products, customers agree and acknowledge that the possibility of defects thereof cannot be eliminated entirely. In addition, NEC Electronics products are not taken measures to prevent radioactive rays in the product design. When customers use NEC Electronics products with their products, customers shall, on their own responsibility, incorporate sufficient safety measures such as redundancy, fire-containment and anti-failure features to their products in order to avoid risks of the damages to property (including public or social property) or injury (including death) to persons, as the result of defects of NEC Electronics products.
- NEC Electronics products are classified into the following three quality grades: "Standard", "Special" and "Specific".
 The "Specific" quality grade applies only to NEC Electronics products developed based on a customer-designated "quality assurance program" for a specific application. The recommended applications of an NEC Electronics product depend on its quality grade, as indicated below. Customers must check the quality grade of each NEC Electronics product before using it in a particular application.
 "Standard": Computers, office equipment, communications equipment, test and measurement equipment, audio and visual equipment, home electronic appliances, machine tools, personal electronic equipment and industrial robots.
 "Special": Transportation equipment (automobiles, trains, ships, etc.), traffic control systems, anti-disaster systems, anti-crime systems, safety equipment and medical equipment (not specifically designed for life support).
 "Specific": Aircraft, aerospace equipment, submersible repeaters, nuclear reactor control systems, life support systems and medical equipment for life support, etc.

The quality grade of NEC Electronics products is "Standard" unless otherwise expressly specified in NEC Electronics data sheets or data books, etc. If customers wish to use NEC Electronics products in applications not intended by NEC Electronics, they must contact an NEC Electronics sales representative in advance to determine NEC Electronics' willingness to support a given application.

(Note)

- (1) "NEC Electronics" as used in this statement means NEC Electronics Corporation and also includes its majority-owned subsidiaries.
- (2) "NEC Electronics products" means any product developed or manufactured by or for NEC Electronics (as defined above).