








P.C.B. LAYOUT



CIRCUIT: SPST



ISOMETRIC



NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REFERENCE ONLY.
4. CONTACT MATERIAL: GOLD
5. RATING: 50mA, @ 12VDC
- ▲ 6. OPERATING FORCE: 160±50 gms
7. TRAVEL: 0.25mm±0.1mm
8. CONTACT RESISTANCE: 100 mΩ MAX. (INITIAL)
9. ELECTRICAL LIFE: 100,000 CYCLES MIN.
10. ▲ DENOTES CRITICAL PARAMETER



A	20378	REVISED AND REDRAWN	1/3/12	BGL
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE TL1105XF160R				
SCALE 4:1	DATE 1/3/2012	DR BGL	DWG P020229	REV D