


Tous droits strictement reserves. Reproduction ou communication a des tiers
Interdite sous quelque forme que ce soit sans autorisation ecrite du proprietaire.
Propriete de c FCI. Droits de reproduction FCI.

All rights strictly reserved. Reproduction or issue to third parties in any
form whatever is not permitted without written authority from the proprietor.
Property of FCI. Copyright FCI.

FCI



FOR SELECT LOAD P/N:

PRODUCT NR:	ROW#	CONFIGURATION											
		1	2	3	4	5	6	7	8	9	10	11	12
10030896-X201	B	-	X	X	X	-	X	-	X	-	X	-	X
10030896-X201LF	C	X	-	X	-	X	-	X	-	X	-	X	-
	D	-	X	X	X	-	X	-	X	-	X	-	X
	A	X	-	X	-	X	-	X	-	X	-	X	-

"-" POSITION NOT LOADED
"X" POSITION LOADED

NOTE:
1. WHEN PART NUMBER WITH A "LF" SUFFIX, THEN THE LF CONTACTS MUST BE USED.
FOR EXAMPLE: PART NUMBER IS10030896-X201LF
CONTACT NUMBER SHOULD BE HM1CDD----LF

PERFORMANCE CHARACTERISTICS:

- VOLTAGE RATING : 250 VAC.
- CURRENT RATING : 1.0 A AT 70°C.
- INSULATION RESISTANCE : 10⁹ MΩ MIN.AFTER TEST.
- DIELECTRIC WITHSTANDING VOLTAGE : 1000 V.
- CONTACT RESISTANCE : 20 mΩ MAX. AFTER TEST.
- OPERATING T° : -55°C TO +125°C.
- INSERTION FORCE : 0.94 N MAX. PER CONTACT.
- WITHDRAWAL FORCE : 0.20 N MIN. PER CONTACT.

MATERIALS:

- TERMINAL BLOCK : GLASS REINFORCED THERMOPLASTIC UL94-V0.
- COVER : POLYAMIDE-NYLON.
- LOCKING KEY : POLYAMIDE-NYLON.
- CONTACTS : PHOSPHOR BRONZE.
- PLATING : X=1 : 0.75 μ AU MIN. OVER NI IN CONTACT AREA;
SNPB(60/40) ON IDC-TERMINAL OR PURE Sn FOR LF.

WIRE CHARACTERISTICS:


- INSULATION DIAMETER 0.75 MM MAX.

PART NUMBERS:




- 10030896-X101 CONNECTOR FOR WIRE SIZE AWG28,AWG30 WITHOUT RETENTION RIBS ON INSULATION PLATE AND HOOD
- 10030896-X121 CONNECTOR FOR WIRE SIZE AWG26 WITHOUT RETENTION RIBS ON INSULATION PLATE AND HOOD
- 10030896-X201 CONNECTOR FOR WIRE SIZE AWG28,AWG30 WITHOUT RETENTION RIBS ON INSULATION PLATE AND HOOD

PILLOW COMPRESSED.
PLASTIC EDGE STOPS
COMPRESSING THE PILLOW
AT POINT GIVES MAX
COMPRESSION 0.4mm.

CONNECTOR MARKING



PARTNUMBER	WIRE SIZE MARKING	LOADING
10030896-X101	AWG28/30	FULL
10030896-X101LF		
10030896-X121		
10030896-X121LF	AWG26	FULL
10030896-X201		
10030896-X201LF	AWG28/30	SELECT
10030896-X201LF		



mat'l. code				tolerances unless otherwise specified		
ltr	ecn no	dr	date	linear	.X ±0.2	
A	T03-0280	M W	07/09/03		.XX ±0.1	
B	T03-0336	M W	08/12/03		.XXX ±	
C	T03-0340	Jeff	10/26/03	angles	0° ±1°	
D	0604-0034	CLu	05/26/04	dr	MAGGIE WU	06/30/03
E	0605-0079	CLu	04/11/05	engr	JEFF.HSIEH	06/30/03
				chr	JEFF.HSIEH	06/30/03
				appd	JENN TSAO	06/30/03
sheet		revision		E		
index		sheet		1		

CONFIDENTIAL



www.fciconnect.com

PDM: Rev: E

STATUS Released
cage code 22520
Printed: Jul 29, 2010

ACAD