

SSF26

high temperature internal fitting



The SSF26 series is a vertically mounted device designed to achieve reliable switching at higher temperatures.

Capable of working at temperatures up to 200°C.

Mounting is in the top or bottom of the tank from the inside, so requires access to the inside of the tank.

They are manufactured in 316 grade Stainless Steel, and will work in liquids of SG 0.65 minimum.

The switch action may be reversed by removing the float, inverting it and then refitting it to the stem.

Typical application is in Deep Frying Oil Tanks.



- **Stainless steel**
- **Internal mounting**
- **Temperature range to 200°C**
- **User configurable N/O or N/C action**

Technical Specification

| | | | |
|-----------------------|-----------|----------------------------------|-----------------|
| Mounting style | Internal | Cable length - standard | 1000mm |
| Mounting thread | 3/8" BSP | Cable size | 17/0.10 - AWG22 |
| Float & Stem material | 316 grade | Cable conductor material | Tinned copper |
| Maximum Temperature | 200°C | Cable sheath material | XLPE |
| Maximum Pressure | 10 bar | Cable temperature rating | 200°C |
| Float SG | 0.55 | Sealing gasket | Not supplied |
| Minimum fluid SG | 0.65 | Tightening torque for fixing nut | 2.0kg/cm |

Electrical Specification

| | |
|---------------------------|------------|
| Contact Form | N/O or N/C |
| Switching Power Max. VA | 50 |
| Switching Current Max. A | 0.5 |
| Switching Voltage AC | 300 |
| Switching Voltage DC | 300 |
| Breakdown Voltage Min. DC | 600 |

All ratings are for resistive load only.

Standard Parts

SSF26X100

Leadouts

100cm XLPE wires

Mechanical Dimensions

All dimensions are in millimeters (inches)

USA

Cynergy3 Components
11125 Knott Avenue, Suite D
San Diego, CA 90630
Sales & Tech Support (866) 258-5057
Email: sales@cynergy3.com

EUROPE - UK

Cynergy3 Components Ltd.
7 Cobham Road
Ferndown Industrial Estate
Wimborne, Dorset BH21 7PE
Telephone +44 (0) 1202 897969
Fax +44 (0) 1202 891918
Email: sales@cynergy3.com

