

## NOTES:

1. MATERIALS AND FINISHES: (PLATING THICKNESS IN MICRO-INCHES)

BODY - ZINC DIECAST, NICKEL PLATING

CONTACT - PHOSPHOR BRONZE, GOLD PLATING

INSULATOR - PTFE

## 2. ELECTRICAL:

A. IMPEDANCE: 75 OHM

B. FREQUENCY RANGE: DC-4 GHz

C. VSWR(RETURN LOSS): 1.07+0.007 F(GHz).

D. DIELECTRIC WITHSTANDING VOLTAGE: 500 VRMS, MIN.

## 3. MECHANICAL:

A. DURABILITY: 500 CYCLES MIN.

B. TEMPERATURE RANGE: - 65°C to +165°C

B6252P2-NT3G-75

DRAWING NO.

THIRD ANGLE PROJ.

REV

A

DESCRIPTION

RELEASE TO MFG.




DATE

05/23/06

ECO

GEFFERY

APPR



GLOBAL P/N
31-70336

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE:  
 0.5 - 6mm 6 - 30mm 30 - 120mm ANGLES  
 $\pm 0.1\text{mm}$   $\pm 0.2\text{mm}$   $\pm 0.3\text{mm}$   $\pm 1^\circ$

NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol Corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. The furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights or permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.

MATERIAL	DRAWN GEFFERY	DATE 23-May-06	TITLE BNC JACK RECEPTACLE PCB MOUNT		Amphenol RF Danbury, CT, USA Tainan, Taiwan Shenzhen, China www.amphenolrf.com
REFERENCE	ENGINEER Geffery	DATE 23-May-06			
131-6400-00	APPROVED S. M.	DATE 7/26/06			
FINISH	CAD FILE F:\DWG\B\6252P2\75\NT3GSZ	CODE ID 74868	DWG SIZE B	DRAWING NO. B6252P2-NT3G-75	REV A
PART NO.					

## CUSTOMER OUTLINE DRAWING

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[31-70336](#)