


59112-001



spec ref -				dr w wcadmin 2010/10/31		projection 		MM 		size A3		scale 10:1							
tolerance std ISO 406 ISO 1101 TOLERANCES UNLESS OTHERWISE SPECIFIED				eng Guo-Min Sun 2013/12/12						ecn no ELX-N-16500-1									
				chr -															
				appr Rick Bian 2013/12/12		product family MINITEK				rel level Released									
surface  ISO 1302		linear		0.X		±0.5				title 2.00MM UNSHROUDED HEADER BOARD TO BOARD THRU-HOLE				dwg no 59112				rev N	
				0.XX		±0.25													
				0.XXX		±0.15													
		angular		0°		±3°		www.fci.com		cat. no. -		Product - Customer Drw				sheet 1 of 2			



Copyright FCI.

A

B

C

D

A

B

C

D

PRODUCT NUMBER
59112-001

PRODUCT NUMBER DESCRIPTION :
59112- X XX - XX - XXX XLF

PLATING
S = 0.38um GOLD
ON CONTACT AREA
0.38um GOLD ON TAIL

G = 0.76um GOLD
ON CONTACT AREA
0.76um GOLD ON TAIL

F = 0.20um GOLD
ON CONTACT AREA
0.20um GOLD ON TAIL

T = 0.76um GOLD ON CONTACT AREA
2.54um 100% MATTE TIN ON TAIL

K = 0.76um GXT ON CONTACT AREA
2.54um 100% MATTE TIN ON TAIL

R = 0.38um GXT ON CONTACT AREA
2.54um 100% MATTE TIN ON TAIL

LEAD FREE (SEE NOTE 11)
RETENTION (SEE NOTES 6 & 10)
R: RETENTIVE LEG
STACKER HEIGHT (SEE NOTE 7)
PACKAGING: - = BAGS
(SEE NOTE 5) U = TUBES
P = TUBE WITH PICK-UP CAP
A = TAPE & REEL WITH PICK-UP CAP
POSITIONS PER ROW = "N"
(02 TO 25)
OMIT FROM PRODUCT NUMBER FOR
LEAD FREE WITH RETENTIVE LEG PRODUCT

PIN STYLE	OAL
22	08.2
24	09.6
26	10.2
28	11.8
30	13.5
32	14.1
34	15.6
36	17.1
38	19.1
40	21.1

6. RETENTION LEG:
2.3kg MAX INSERTION FORCE AND 1 kg MIN RETENTION FORCE PER
RETENTIVE PIN USING 1.57 THICK CIRCUIT BOARD AND RECOMMENDED
HOLE PATTERN. RETENTIVE LOCATION AT THE
DISCRETION OF THE MANUFACTURER.RETENTION IS TWO PINS PER
PART ADJACENT TO ONE ANOTHER.

7. STACK HEIGHT IS DETERMINED BY CUSTOMER APPLICATION REQUIREMENTS.
SPECIFIED IN mm. EXAMPLE: 3.7mm STACK HEIGHT=59112-XXX-037X.

8. POST LENGTH IS DETERMINED BY: (OAL)-(2.50)-(STACK HGT.)=POST
LENGTH.MINIMUM MATING LENGTH TO BE 2.0mm

9. DIM 1.0 APPLIES TO MOLDED SIDE(S) ONLY.IF SIDE(S) ARE BROKEN,
DIM 1.5 MAX APPLIES.

10. OMIT FROM PRODUCT NUMBER IF FEATURE IS NOT APPLICABLE.

11. P/N:59112-XXXLF IS SAME AS P/N:59112-XXX. THE SUFFIX 'LF'
IS ADDED FOR EASY LEAD FREE IDENTIFICATION.

12. THE HOUSING WILL WITHSTAND EXPOSURE TO 255°C PEAK
TEMPERATURE FOR 10 SECONDS IN A CONVECTION, INFRA-RED
OR VAPOR PHASE REFLOW OVEN.

13. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK
TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER
APPLICATION WITH A 1.57MM MINIMUM THICK CIRCUIT BOARD.

14. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND
OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.

NOTES:
1. MATERIAL HOUSING: HIGH TEMPERATURE THERMOPLASTIC
UL 94V-0, COLOR BLACK
2. MATERIAL TERMINAL: COPPER ALLOY
3. TO DETERMINE DIMENSIONS:
N=NUMBER OF POSITIONS PER ROW
EX.: 10 POS., N x 2.00 = 20.00 TOTAL POSITIONS
4. 0.9kg MIN. PIN RETENTION IN EITHER DIRECTION.
5. PACKAGING;
(A) STANDARD PACKAGING: IN POLY BAGS.
(B) SPECIAL PACKAGING: IN TUBE OR TAPE AND REEL.
FOR TUBE AN OPTIONAL PICK-UP CAP IS PROVIDED AT
THE CENTER OF THE PRODUCT FOR PICK AND PLACE APPLICATIONS.
PICK-UP CAP IS STANDARD IN TAPE AND REEL.
FOR ALL SPECIAL PACKAGING,FCI MUST BE CONTACTED FOR
AVAILABILITY IN SIZE REQUESTED.

spec ref	-	dr	wcadmin	2010/10/31	projection	MM	size	A3	scale	5:1	
tolerance std	ISO 406 ISO 1101	eng	Guo-Min Sun	2013/12/12	chr	-	ecn no	ELX-N-16500-1			
		appr	Rick Bian	2013/12/12	product family	MINITEK		rel level	Released		
surface	linear	0.X	±0.5	FCI	2.00MM UNSHROUDED HEADER BOARD TO BOARD THRU-HOLE		dwg no	59112		rev	N
		0.XX	±0.25								
		0.XXX	±0.15								
ISO 1302	angular	0°	±3°	www.fci.com	cat. no.	-	Product - Customer Drw			sheet 2 of 2	