



CATALOG LISTING	KEYWAY POSITION		CENTER POSITION		OPPOSITE KEYWAY POSITION	
	C-NC	C-NO	C-NO	C-NC	C-NC	C-NO
64AT26-1	1 & 2	3 & 4	NONE	ALL	3 & 4	1 & 2
64AT26-3	1 & 2	3 & 4	NONE	NONE	3 & 4	1 & 2
64AT26-5	1 & 2*	3 & 4*	NONE	ALL	3 & 4	1 & 2
64AT26-7	1 & 2*	3 & 4*	NONE	ALL	3 & 4*	1 & 2*
64AT26-514	1 & 2	3 & 4	NONE	ALL	3 & 4*	1 & 2*

* ASTERISK DENOTES MOMENTARY POSITION



NOTES

- 1 - SWITCHES MARKED 1 & 3 HAVE 24K SOLID GOLD OVERLAY CONTACTS "23SX" TYPE BASIC SWITCH (MEETS REQUIREMENTS OF MIL-PRF-8805)
- 2 - SWITCHES MARKED 2 & 4 HAVE SOLID SILVER CONTACTS "21SX" TYPE BASIC SWITCH (MEETS REQUIREMENTS OF MIL-PRF-8805)
- 3 - SWITCHES DO NOT NECESSARILY OPERATE SIMULTANEOUSLY
- 4 - PLATED TERMINALS WILL ACCEPT AMPS INC ϕ .058 PIN RECEPTACLES
- 5 - DULL FINISH ON LEVER AND BUSHING
- 6 - SWITCH NUMBERS STAMPED ON END OF BASIC SWITCHES
- 7 - TERMINAL DESIGNATION STAMPED ON BOTH SIDES OF UNIT
- 8 - OPERATING FORCE 1-5 LB WHEN APPLIED $.125 \pm .030$ FROM TOP OF THE LEVER
- 9 - HARDWARE FURNISHED ASSEMBLED WITH SWITCH OR IN PACKET 15PA313-AT PER MIL-PRF-8805
- 10 - CONTACT HONEYWELL-MICRO SWITCH IF INFORMATION ON LOW ENERGY LOADS IS REQUIRED OR FOR HELP WITH SPECIFIC APPLICATIONS
- 11 - REPLACEMENT MOUNTING HARDWARE PACKET 15PA313-AT



SPECIFICATION DETAILS:		
STANDARD:		
CONSTRUCTION:		
ENCLOSURE DESIGN	UNSEALED	
CONTACT MATERIAL & CONFIGURATION	SW 1 & 3 24K GOLD OVERLAY CONTACTS 23SX CONSTRUCTION SW 2 & 4 SOLID SILVER CONTACTS 21SX CONSTRUCTION	
CIRCUIT CONFIGURATION		
TERMINATION	-H58	
WEIGHT	1 LB MAX	
EXPOSED METALS	CORROSION RESISTANT AS NOTED	
ELECTRICAL CHARACTERISTICS:		
CONTACT ARRANGEMENT	4X S.P.D.T.	
SWITCH NO. 1 AND 3 30 VOLTS DC RATING INDUCTIVE ----- SEA LEVEL ----- .5 AMP RESISTIVE ----- SEA LEVEL ----- 1 AMP MAX INRUSH ----- 2 AMP	SWITCH NO. 2 AND 4 28 VOLTS DC RATING INDUCTIVE ----- SEA LEVEL ----- 4 AMP RESISTIVE ----- SEA LEVEL ----- 2.5 AMP 115 VOLTS AC RATING AT SEA LEVEL INDUCTIVE AND RESISTIVE ----- 7 AMP	
DIELECTRIC STRENGTH & INSULATION RES (BASIC SWITCH)	DIELECTRIC STRENGTH (500 VDC ± 10%)	
-BETWEEN TERMINALS AND EXPOSED NON-CURRENT CARRYING METAL	1000 V Rms, 500 A (MAX LEAKAGE) 1000 Megohms MIN	
-BETWEEN TERMINALS OF MUTUALLY INSULATED CIRCUITS	1000 V Rms, 500 A (MAX LEAKAGE) 1000 Megohms MIN	
-BETWEEN ALL UNCONNECTED TERMINALS OF THE SAME POLE	1000 V Rms, 500 A (MAX LEAKAGE) 1000 Megohms MIN	
SWITCH RESISTANCE	N/A	
RECOMMENDATION OR USE IN APPL LESS THAN .5 amps AND/OR 12 volts	10	
MECHANICAL CHARACTERISTICS:		
ACTUATOR STRENGTH	25 LB	
MOUNTING STRENGTH	25 LB	
LIFE:		
MECHANICAL LIFE	50,000 MIN	
ELECTRICAL LIFE AT FULL RATED LOAD	25,000 MIN	
ENVIRONMENTAL:		
TEMPERATURE RANGE	-55° C TO +85° C	
ALTITUDE RANGE	SEA LEVEL TO 50,000 FT	
SHOCK	100 G	
VIBRATION	10-500 Hz	
MOISTURE RESISTANCE	UNSEALED	
THERMAL SHOCK	N/A	
SALT SPRAY	N/A	

NOTE: INDUCTIVE LOADS USE AN3179-6 INDUCTOR, 115 VAC AT 75% PF

THIRD ANGLE PROJECTION	
SCALE	FULL
DO NOT SCALE PRINT	
UNLESS OTHERWISE SPECIFIED	
TOLERANCES ARE	
ONE PLACE	(.0) ± .030
TWO PLACES	(.00) ± .015
THREE PLACES	(.000) ± .005
ANGLES	±
WEIGHT	.07 LB EST

CATALOG LISTING	KEYWAY POSITION		CENTER POSITION		OPPOSITE KEYWAY POSITION	
	C-NC	C-NO	C-NO	C-NC	C-NC	C-NO
64AT26-1	1 & 2	3 & 4	NONE	ALL	3 & 4	1 & 2
64AT26-3	1 & 2	3 & 4	NONE	NONE	3 & 4	1 & 2
64AT26-5	1 & 2*	3 & 4*	NONE	ALL	3 & 4	1 & 2
64AT26-7	1 & 2*	3 & 4*	NONE	ALL	3 & 4*	1 & 2*
64AT26-514	1 & 2	3 & 4	NONE	ALL	3 & 4*	1 & 2*

* ASTERISK DENOTES MOMENTARY POSITION



NOTES

- 1 - SWITCHES MARKED 1 & 3 HAVE 24K SOLID GOLD OVERLAY CONTACTS "23SX" TYPE BASIC SWITCH (MEETS REQUIREMENTS OF MIL-PRF-8805)
- 2 - SWITCHES MARKED 2 & 4 HAVE SOLID SILVER CONTACTS "21SX" TYPE BASIC SWITCH (MEETS REQUIREMENTS OF MIL-PRF-8805)
- 3 - SWITCHES DO NOT NECESSARILY OPERATE SIMULTANEOUSLY
- 4 - PLATED TERMINALS WILL ACCEPT AMPS INC ϕ .058 PIN RECEPTACLES
- 5 DULL FINISH ON LEVER AND BUSHING
- 6 SWITCH NUMBERS STAMPED ON END OF BASIC SWITCHES
- 7 TERMINAL DESIGNATION STAMPED ON BOTH SIDES OF UNIT
- 8 OPERATING FORCE 1-5 LB WHEN APPLIED $.125 \pm .030$ FROM TOP OF THE LEVER
- 9 HARDWARE FURNISHED ASSEMBLED WITH SWITCH OR IN PACKET 15PA313-AT PER MIL-PRF-8805
- 10 CONTACT HONEYWELL-MICRO SWITCH IF INFORMATION ON LOW ENERGY LOADS IS REQUIRED OR FOR HELP WITH SPECIFIC APPLICATIONS
- 11 - REPLACEMENT MOUNTING HARDWARE PACKET 15PA313-AT

SPECIFICATION DETAILS:		
STANDARD:		
CONSTRUCTION:		
ENCLOSURE DESIGN	UNSEALED	
CONTACT MATERIAL & CONFIGURATION	SW 1 & 3 24K GOLD OVERLAY CONTACTS 23SX CONSTRUCTION SW 2 & 4 SOLID SILVER CONTACTS 21SX CONSTRUCTION	
CIRCUIT CONFIGURATION		
TERMINATION	- H58	
WEIGHT	1 LB MAX	
EXPOSED METALS		CORROSION RESISTANT AS NOTED
ELECTRICAL CHARACTERISTICS:		
CONTACT ARRANGEMENT	4X S.P.D.T.	
SWITCH NO. 1 AND 3 30 VOLTS DC RATING INDUCTIVE ----- SEA LEVEL ----- .5 AMP RESISTIVE ----- SEA LEVEL ----- 1 AMP MAX INRUSH ----- 2 AMP	SWITCH NO. 2 AND 4 28 VOLTS DC RATING INDUCTIVE ----- SEA LEVEL ----- 4 AMP RESISTIVE ----- SEA LEVEL ----- 7 AMP 115 VOLTS AC RATING AT SEA LEVEL INDUCTIVE AND RESISTIVE ----- 7 AMP	
DIELECTRIC STRENGTH & INSULATION RES (BASIC SWITCH)	DIELECTRIC STRENGTH (\approx 60 Hz FOR 5 SECONDS)	INSULATION RESISTANCE (500 VDC \pm 10%)
-BETWEEN TERMINALS AND EXPOSED NON-CURRENT CARRYING METAL	1000 V Rms, 500 A (MAX LEAKAGE)	1000 Megohms MIN
-BETWEEN TERMINALS OF MUTUALLY INSULATED CIRCUITS	1000 V Rms, 500 A (MAX LEAKAGE)	1000 Megohms MIN
-BETWEEN ALL UNCONNECTED TERMINALS OF THE SAME POLE	1000 V Rms, 500 A (MAX LEAKAGE)	1000 Megohms MIN
SWITCH RESISTANCE	N/A	
RECOMMENDATION OR USE IN APPL LESS THAN .5 amps AND/OR 12 volts	10	
MECHANICAL CHARACTERISTICS:		
ACTUATOR STRENGTH	25 LB	
MOUNTING STRENGTH	25 LB	
LIFE:		
MECHANICAL LIFE	50,000 MIN	
ELECTRICAL LIFE AT FULL RATED LOAD	25,000 MIN	
ENVIRONMENTAL:		
TEMPERATURE RANGE	-55° C TO +85° C	
ALTITUDE RANGE	SEA LEVEL TO 50,000 FT	
SHOCK	100 G	
VIBRATION	10-500 Hz	
MOISTURE RESISTANCE	UNSEALED	
THERMAL SHOCK	N/A	
SALT SPRAY	N/A	

NOTE: INDUCTIVE LOADS USE AN3179-6 INDUCTOR, 115 VAC AT 75% PF

THIRD ANGLE PROJECTION
SCALE FULL
DO NOT SCALE PRINT
UNLESS OTHERWISE SPECIFIED TOLERANCES ARE
ONE PLACE (.0) \pm .030
TWO PLACES (.00) \pm .015
THREE PLACES (.000) \pm .005
ANGLES \pm
WEIGHT .07 LB EST

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[64AT26-1](#)