




N-Channel 20-V (D-S) 175°C MOSFET

PRODUCT SUMMARY

$V_{(BR)DSS}$ (V)	$r_{DS(on)}$ (Ω)	I_D (A) ^a
20	0.003 @ $V_{GS} = 4.5$ V	85
	0.0034 @ $V_{GS} = 2.5$ V	85
	0.0038 @ $V_{GS} = 1.8$ V	85

175°C Rated
Maximum Junction Temperature
TrenchFET®
Power MOSFETs

TO-220AB




Top View

DRAIN connected to TAB


Ordering Information:
SUP85N02-03—E3 (Lead Free)

TO-263



Top View

Ordering Information:
SUB85N02-03—E3 (Lead Free)



N-Channel MOSFET

ABSOLUTE MAXIMUM RATINGS ($T_C = 25^\circ\text{C}$ UNLESS OTHERWISE NOTED)

Parameter	Symbol	Limit	Unit
Drain-Source Voltage	V_{DS}	20	V
Gate-Source Voltage	V_{GS}	± 8	
Continuous Drain Current ($T_J = 175^\circ\text{C}$) ^a	I_D	85	A
		85	
Pulsed Drain Current	I_{DM}	240	
Avalanche Current	I_{AR}	30	
Repetitive Avalanche Energy ^b	E_{AR}	45	mJ
Power Dissipation ^a			
Operating Junction and Storage Temperature Range	T_J, T_{stg}	-55 to 175	$^\circ\text{C}$

THERMAL RESISTANCE RATINGS

Parameter	Symbol	Limit	Unit
Junction-to-Ambient	R_{thJA}	40	$^\circ\text{C/W}$
		62.5	
Junction-to-Case	R_{thJC}	0.6	







Notes:

- See SOA curve for voltage derating.
- Duty cycle $\leq 1\%$.
- When mounted on 1" square PCB (FR-4 material).





MOSFET SPECIFICATIONS (T _J =25 °C UNLESS OTHERWISE NOTED)						
Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
Static						
Drain-Source Breakdown Voltage	V _{(BR)DSS}	V _{GS} = 0 V, I _D = 2 mA	20			V
Gate Threshold Voltage	V _{GS(th)}	V _{DS} = V _{GS} , I _{DS} = 2 mA	0.45			
Gate-Body Leakage	I _{GSS}	V _{DS} = 0 V, V _{GS} = ± 8 V			± 100	nA
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} = 20 V, V _{GS} = 0 V			1	μA
		V _{DS} = 20 V, V _{GS} = 0 V, T _J = 125 °C			250	
On-State Drain Current ^a	I _{D(on)}	V _{DS} = 5 V, V _{GS} = 4.5 V	120			A
Drain-Source On-State Resistance ^a	r _{DS(on)}	V _{GS} = 4.5 V, I _D = 30 A		0.0025	0.003	Ω
		V _{GS} = 4.5 V, I _D = 30 A, T _J = 125 °C			0.0042	
		V _{GS} = 4.5 V, I _D = 30 A, T _J = 175 °C			0.005	
		V _{GS} = 2.5 V, I _D = 30 A		0.0027	0.0034	
		V _{GS} = 1.8 V, I _D = 30 A		0.003	0.0038	
Forward Transconductance ^a	g _{fs}	V _{DS} = 5 V, I _D = 30 A	30			S
Dynamic ^b						
Input Capacitance	C _{iss}	V _{GS} = 0 V, V _{DS} = 20 V, f = 1 MHz		21250		pF
Output Capacitance	C _{oss}			2350		
Reversen Transfer Capacitance	C _{rss}			1520		
Total Gate Charge ^c	Q _g	V _{DS} = 10 V, V _{GS} = 4.5 V, I _D = 85 A		140	200	nC
Gate-Source Charge ^c	Q _{gs}			18		
Gate-Drain Charge ^c	Q _{gd}			24		
Turn-On Delay Time ^c	t _{d(on)}	V _{DD} = 10 V, R _L = 0.12 Ω I _D ≈ 85 A, V _{GEN} = 4.5 V, R _g = 2.5 Ω		20	30	ns
Rise Time ^c	t _r			200	300	
Turn-Off Delay Time ^c	t _{d(off)}			450	670	
Fall Time ^c	t _f			320	480	
Source-Drain Diode Ratings and Characteristics (T _C = 25 °C) ^b						
Pulsed Current	I _{SM}				240	A
Forward Voltage ^a	V _{SD}	I _F = 100 A, V _{GS} = 0 V		1.2	1.5	V
Reverse Recovery Time	t _{rr}	I _F = 50 A, di/dt = 100 A/μs		75	150	ns




Notes:

- a. Pulse test; pulse width $\leq 300\ \mu\text{s}$, duty cycle $\leq 2\%$.
b. Guaranteed by design, not subject to production testing.
c. Independent of operating temperature.

**TYPICAL CHARACTERISTICS (25 °C UNLESS NOTED)****Output Characteristics****Transfer Characteristics****Transconductance****On-Resistance vs. Drain Current****Capacitance****Gate Charge**

TYPICAL CHARACTERISTICS (25 °C UNLESS NOTED)



**THERMAL RATINGS****Maximum Drain Current vs.
Case Temperature****Safe Operating Area****Normalized Thermal Transient Impedance, Junction-to-Case**



Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.