

CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes



more than you expect



Midcom

ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	4-6 @20°C	2.4 ohms max.
D.C. RESISTANCE	1-3 @20°C	1.35 ohms max.
D.C. RESISTANCE	7-12 @20°C	0.06 ohms max.
INDUCTANCE	4-6 10kHz, 100mVAC, L _s	1.70mH ±10%
LEAKAGE INDUCTANCE	4-6 tie(1+3+12+7), 100kHz, 100mVAC, L _s	27uH typ., 45uH max.
DIELECTRIC	4-7 tie(4+1), 4800VAC, 1 second	4000VAC, 1 minute
DIELECTRIC	1-4 1875VAC, 1 second	1500VAC, 1 minute
TURNS RATIO	(4-6):(1-3)	5.19:1, ±2%
TURNS RATIO	(4-6):(12-7)	13.5:1, ±2%



REV.	DATE	Packaging Specifications	CONVENTION PLACEMENT	Tolerances unless otherwise specified:	DRAWING TITLE	PART NO.
6C	10/10	Method: Tray PKG-0736	6C	Angles: ±1° Fractions: ±1/64	TRANSFORMER	750871111
6B	1/09	www.we-online.com/midcom	6B	Decimals: ±.005 [1.3] Footprint: ±.001 [0.3]		
6A	10/08	SEE REVISION SHEET FOR	6A	This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750871111	SPECIFICATION SHEET 1 OF 1

