


MATERIALS

BODY	BRASS NICKEL PLATED
CONTACT	GOLD PLATED
INSULATOR	PTFE



SPECIFICATIONS

FREQUENCY RANGE: DC TO 4 GHz

ATTENUATION: 2dB

IMPEDANCE: 50 OHMS

ACCURACY: ± 4 dB MAXIMUM

VSWR: 1.25:1 MAXIMUM

AVG. POWER HANDLING CAPABILITY: 2 WATTS



PASTERNAK ENTERPRISES, INC.

P.O BOX 16759, IRVINE, CA 92623
PHONE (949) 261-1920 FAX (949) 261-7451

WEB ADDRESS: www.pasternack.com
E-MAIL ADDRESS: sales@pasternack.com

COAXIAL & FIBER OPTICS

DWG TITLE

PE7049-2

DES. BNC ATTENUATOR, FREQUENCY RANGE: DC
TO 4 GHz

SIZE A

FSCM NO. 53919

CAD FILE 080502

SCALE N/A

127

NOTES:

1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.