

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

62201-8603

Status:

Active

Description:

Press-In Tool for Vertical Header 11-Row, 10-Column

Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Application Tooling
Series	T3002
Comments	See Tooling Specification (PDF) Above, Press-In Tool
Function	Insertion
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Product Name	N/A
Survey	www.molex.com//review/apptool_survey.html
Tool Type	Handtool
UPC	822350334150

Material Info

Reference - Drawing Numbers

Application Tooling Documents

ATS-622018603, TM-622018699, TM-622022099




image - Reference only

Series

EU RoHS	China RoHS
Compliance Status	
Not Reviewed	
REACH SVHC	
Not Reviewed	
Low-Halogen Status	
Not Reviewed	

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

T3002Series

Use With

GbX I-Trac™ Backplane Signal Module, 75705 Series

Application Tooling Description	FAQ Product #
1.85mm by 3.70mm Pitch, GbX I-Trac™ Vertical Header Module, Unguided, Open Ends, 11 Rows, 10 Columns, 220 Circuits, Mating Pin Length 5.70mm	0757050104
1.85mm by 3.70mm Pitch, GbX I-Trac™ Vertical Header Module, Unguided, Left End Wall, 11 Rows, 10 Columns, 220 Circuits, Staggered Mating	0757050115

Pin Length 4.70mm & 5.70mm 1.85mm by 3.70mm Pitch, GbX I-Trac™ Vertical Header Module, Unguided, Open Ends, 11 Rows, 10 Columns, 220 Circuits, Mating	0757051103
Pin Length 4.70mm 1.85mm by 3.70mm Pitch, GbX I-Trac™ Vertical Header Module, Unguided, Open Ends, 11 Rows, 10 Columns, 220 Circuits, Mating	0757051104
Pin Length 5.70mm 1.85mm by 3.70mm Pitch, GbX I-Trac™ Vertical Header Module, Unguided, Open Ends, 11 Rows, 10 Columns, 220 Circuits, Mating	0757051113
Pin Length 4.70mm 1.85mm by 3.70mm Pitch, GbX I-Trac™ Vertical Header Module, Unguided, Left End Wall, 11 Rows, 10 Columns, 220 Circuits, Mating	0757051123
Pin Length 4.70mm 1.85mm by 3.70mm Pitch, GbX I-Trac™ Vertical Header Module, Unguided, Dual End Wall, 11 Rows, 10 Columns, 220 Circuits, Mating	0757051124
Pin Length 4.70mm 1.85mm by 3.70mm Pitch, GbX I-Trac™ Vertical Header Module, Unguided, Dual End Walls, 11 Rows, 10 Columns, 220 Circuits, Mating	0757051133
Pin Length 5.70mm 1.85mm by 3.70mm Pitch, GbX I-Trac™ Vertical Header Module, Unguided, Right End Wall, 11 Rows, 10 Columns, 220 Circuits, Mating	0757052103
Pin Length 4.70mm 1.85mm by 3.70mm Pitch, GbX I-Trac™ Vertical Header Module, Left Guide, Right Open, 11 Rows, 10 Columns, 200 Circuits, Mating	0757052104
Pin Length 4.70mm 1.85mm by 3.70mm Pitch, GbX I-Trac™ Vertical Header Module, Left Guide, Right Open, 11 Rows, 10 Columns,	

220 Circuits, Mating
Pin Length 5.70mm
1.85mm by 3.70mm 0757053104
Pitch, GbX I-Trac™
Vertical Header
Module, Left Guide,
Right Open, 11
Rows, 10 Columns,
220 Circuits, Mating
Pin Length 5.70mm
1.85mm by 3.70mm 0757054103
Pitch, GbX I-Trac™
Vertical Header
Module, Right Guide,
Left Open, 11 Rows,
10 Columns, 200
Circuits, Mating Pin
Length 4.70mm
1.85mm by 3.70mm 0757054104
Pitch, GbX I-Trac™
Vertical Header
Module, Right Guide,
Left Open, 11 Rows,
10 Columns, 200
Circuits, Mating Pin
Length 5.70mm
1.85mm by 3.70mm 0757055103
Pitch, GbX I-Trac™
Vertical Header
Module, Right Guide,
Left Open, 11 Rows,
10 Columns, 200
Circuits, Mating Pin
Length 4.70mm
1.85mm by 3.70mm 0757055104
Pitch, GbX I-Trac™
Vertical Header
Module, Right Guide,
Left Open, 11 Rows,
10 Columns, 200
Circuits, Mating Pin
Length 5.70mm
1.85mm by 3.70mm 0757057103
Pitch, GbX I-Trac™
Vertical Header
Module, Left Guide,
Right Endwall, 11
Rows, 10 Columns,
200 Circuits, Mating
Pin Length 4.70mm
1.85mm by 3.70mm 0757057104
Pitch, GbX I-Trac™
Vertical Header
Module, Left Guide,
Right Endwall, 11
Rows, 10 Columns,
200 Circuits, Mating
Pin Length 5.70mm
1.85mm by 3.70mm 0757059104
Pitch, GbX I-Trac™
Vertical Header
Module, Right Guide,
Left Endwall, 11
Rows, 10 Columns,

