

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0901512210

Status:

Active

Overview:

C-Grid® / SL™ Products

Description:

2.54mm (.100") Pitch C-Grid III™ PC Board Connector, Dual Row, Vertical, 10 Circuits

Documents:

3D Model

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Application

Overview

Product Name

PCB Receptacles

90151

Board-to-Board

C-Grid® / SL™ Products

C-Grid III™

Physical

Circuits (Loaded)

Color - Resin

Glow-Wire Compliant

Guide to Mating Part

Keying to Mating Part

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Number of Rows

Orientation

PC Tail Length (in)

PC Tail Length (mm)

PCB Locator

PCB Retention

PCB Thickness Recommended (in)

PCB Thickness Recommended (mm)

Packaging Type

Pitch - Mating Interface (in)

Pitch - Mating Interface (mm)

Plating min: Mating (µin)

Plating min: Mating (µm)

Plating min: Termination (µin)

Plating min: Termination (µm)

Polarized to PCB

Temperature Range - Operating

Termination Interface: Style

10

Black

No

No

None

No

Phosphor Bronze

Gold

Tin

Polyester

2

Vertical

0.114 In

2.90 mm

No

None

0.062 In

1.60 mm

Tube

0.100 In

2.54 mm

15.2

0.38

120

3

No

-55°C to +125°C

Through Hole

Electrical

Current - Maximum

Grounding to PCB

Voltage - Maximum

3A

No

350V

Solder Process Data

Lead-free Process Capability


Wave Capable (TH only)

Material Info

Reference - Drawing Numbers

Sales Drawing

SDA-90151



EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Halogen-Free

Status

Not Halogen-Free

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

90151 Series

Mates With

0.64mm (.025") square pins

This document was generated on 12/08/2009

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION