




PRODUCT NUMBER
SEE TABLE



mat'l. code				surface		tolerance		projection		product family					
				ISO 1302 ✓		ISO 406 ISO 1101				LATCH-N-LOK					
ltr ecn nodr date				tolerances unless otherwise specified						title					
P	ELX-N-008458	ZK	11/29/11	angles	linear	XX±.01/0.XX±0.3		INCH/MM		2X4 LNL RIGHT ANGLE HDR ASSM. ON .100" CTR.					
			XXX±.005/0.XX±0.13												
			XXXX±.0020/0.XXX±0.05												
J	M05-0023	MHT	2/18/05	0°±2°	XXXX±.0020/0.XXX±0.05		scale 1:1		dwg no sheet 1 of 2 size A3						
K	M05-0033	ERE	2/25/05	dr	S. ROYER	8/9/90									
L	M05-0052	MHT	3/16/05	engr	D. HORCHLER	8/9/90									
M	M06-0365	AGS	9/21/06	chr	D. HORCHLER	8/9/90									
N	M09-0048	MHT	3/12/09	appd	D. HORCHLER	8/9/90									
sheet revision				P	P										
index				sheet	1	2									

87316-XYYZLF

LEAD FREE OPTION NOTE 8,9

KEY POSITION

—	STANDARD PROD.	NOTE	7
1	KEY POS. 1	NOTE	6
2	KEY POS. 2	NOTE	6
3	KEY POS. 3	NOTE	6

COLOR


1	70343	LT GRAY	—	OBS
2	80166	OFF WHITE		
3	70634	DK GRAY	—	OBS
4	701	BLACK		
5	70511	SLATE GRAY	—	OBS
7	70455	SILVER GRAY		
8	80189	PEARL WHITE	—	OBS
9	70419	PEBBLE GRAY		

PLATING ③

0	30u" MIN OVER 50u"MIN Ni
3	30u" MIN OVER 50u"MIN Ni
5	50u" MIN OVER 50u"MIN Ni


PIN LENGTH KEY

	DIM L	± 0.10 ± 0.25
0	.200	[5.08]
1	.130	[3.30]



NOTES:

1. HEADER SHROUD:
HIGH TEMPERATURE THERMOPLASTIC.
UL-94V-0 RATED.
2. GROUND CONTACT:
MAT'L: COPPER ALLOY
PLATING: 100-160u"/2.54-4.06 TIN.
- ③ SIGNAL CONTACT:
MAT'L: COPPER ALLOY
PLATING: PERFORMANCE PLATING WILL BE EITHER GOLD OR GXT
ON CONTACT AREA OR TAIL, OPTIONALLY (78-295u") TIN ON TAIL.
- ④ NUMBERS SHOWN ARE FOR G.E. LEXAN AND ARE FOR REFERENCE ONLY
- 5 THIS ASSEMBLY U.L. RECOGNIZED PER FILE E66906VVOL. 1, SEC. 19 AND
CSA APPROVED PER MASTER FILE LR46923.
- ⑥ REQUIRES USE OF LNL PLUG OF SAME KEYED POSITION.
- ⑦ OMIT 4TH DASH DIGIT IF NO KEY (STANDARD PRODUCT) IS DESIRED.
- ⑧ ADD LF SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE OPTION.
9. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE
FOR 15 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.5mm
MINIMUM THICK CIRCUIT BOARD. SEE APPLICATION NOTES/PROCEDURES
IF THEY ARE AVAILABLE.
10. HIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER
COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
11. PRODUCT SPEC: GS-12-003



mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family LATCH-N-LOK			
ltr		ecn		nodr		date		tolerances unless otherwise specified				title	
P								angles $0^\circ \pm 2'$		line ar $0.004 \pm 0.005 / 0.004 \pm 0.005$		INCH/MM 2X4 LNL RIGHT ANGLE HDR ASSM. ON .100" CTR.	
								dr S. ROYER 8/9/90 engr D. HORCHLER 8/9/90 chr D. HORCHLER 8/9/90 app D. HORCHLER 8/9/90		scale 1:1 		dwg no 87316	
										sheet2 of 2 A3		type Product Customer Drawing	
sheet		revision											
index		sheet											