




Note:

* Material :

Insulation:

Nylon 46+40% G.F UL 94V-0

Color Nature(Ivory)

Contact : Phosphor Bronze

* Recommended mating part:

Housing : CI44**S0000

Terminal : CI44T011PP0

ORDERING CODE:

CI44 ** P 1 H 00
① ② ③ ④ ⑤ ⑥

① SERIES NO.:

② NO. OF CIRCUITS: 02 TO 15



③ CONTACTS TYPE: P= Plug

④ PLATING OPTION:


1= Tin over Nickel plated

⑤ TAIL STYLE: H= RIGHT ANGLE

⑥ OPTION: 00= STANDARD



Circuits	Dimension		
	A	B	C
2	1.25(.049)	4.35(.171)	3.15(.124)
3	2.50(.098)	5.6(.220)	4.40(.173)
4	3.75(.148)	6.85(.270)	5.65(.222)
5	5.00(.197)	8.1(.319)	6.90(.272)
6	6.25(.246)	9.35(.368)	8.15(.321)
7	7.50(.295)	10.6(.417)	9.40(.370)
8	8.75(.344)	11.85(.467)	10.65(.419)
9	10.00(.394)	13.1(.516)	11.90(.469)
10	11.25(.443)	14.35(.565)	13.15(.518)
11	12.50(.492)	15.6(.614)	14.40(.567)
12	13.75(.541)	16.85(.663)	15.65(.616)
13	15.00(.591)	18.1(.713)	16.90(.665)
14	16.25(.640)	19.35(.762)	18.15(.715)
15	17.50(.689)	20.6(.811)	19.40(.764)



Recommended P.C. Board Layout

Tin-Lead Process

RoHS Compliant

4				CIVILUX CORP 2007.03.06 ISSUED		DATE	UNIT: mm / inch		TITLE: 1.25MM(.049") RIGHT ANGLE HEADER	 瀚荃股份有限公司 CviLux Corporation
3					DRAWN BY: Eager	02/27-07'	TOLERANCE UNLESS OTHERWISE SPECIFIED			
2					ENGINEER: Eisley	03/01-07'	.X ± 0.25/.010	X.* ± 1"	MATERIAL:	
1	Eager	02/13-07'	ECR07015-0/ECN07050		CHECKED BY: David	03/01-07'	.XX ± 0.15/.006	.X.* ±	FINISH:	
SYM	NAME	DATE	REVISIONS	APPROVED BY: Alex	03/01-07'	.XXX ± 0.08/.003	.XX.* ±		DRAWING NO. CI4404SH	PART NO. CI44**P1H00
									SCALE 5 / 1	SHEET 1 OF 1



DRAWN BY: Eager
ENGINEER: Eisley
CHECKED BY: David
APPROVED BY: Alex

TOLERANCE
UNLESS OTHERWISE SPECIFIED
.X ± 0.25/.010 X' ± 1'
.XX ± 0.15/.006 X' ±
.XXX ± 0.08/.003 .XX ±

MATERIAL:
FINISH: