

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2014

© COPYRIGHT 2014

BY - TE CONNECTIVITY

ALL RIGHTS RESERVED.

LOC - -

DIST - -

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
NC		NEW RELEASE PER E.O. PI4915	04DEC1995	-	RDR
A		REVISED PER E.O. PI5908	05FEB1999	-	RDR
B		REVISED PER E.O. PI8134	23MAY2003	-	RDR
BI		REVISED AS PER ECO-15-001798	02SEP2014	VNB	DM

Ø 2.000
[50.8]

MAIN POLARIZING KEYWAY

1.875
[47.63]

(1.647) SHELL
[41.83]

1.030
[26.16]

.505
[12.83]

.100
[2.54]

Ø 1.579)
[40.11]

Ø 1.470)
[37.34]

RECEPTACLE HOUSING

1.6875-18 UNEF REF

6. MATERIAL:
RECEPTACLE HOUSING: AL 6000 SERIES

5. THIS PART MATES WITH HD36-24-XXXP/SX-XXXX

4. PART NUMBER INFO: XX= ARRANGEMENT: X= SEAL TYPE

3. TOTAL DIM. WITH EXTENDED WIRE SEAL (WITH CONTACTS
#4 OR #8 ONLY) = 1.870±.050 [47.50±1.27].

2. FOR ARRANGEMENT OF CONTACT LOCATION
SEE ENVELOPE DRAWING 0425-014-2400.

1. CONSULT THE FACTORY FOR ELECTRICAL AND MATERIAL SPECIFICATIONS.

NOTES:

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 30OCT2014 VIJETH BHARADWAJ	TE Connectivity	
DIMENSIONS: INCHES [mm]		CHK 31OCT2014 I. GRANTCHAROVA		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 31OCT2014 D. MEYER	NAME RECEPTACLE CONNECTOR SHELL SIZE 24 BAYONET COUPLING HD30 SERIES	
0 PLC ±-		PRODUCT SPEC 0425-016-0000	SIZE A3	CAGE CODE -
1 PLC ±-		APPLICATION SPEC 0425-015-0000	DRAWING NO C=HD34-24-XXP/SX	RESTRICTED TO -
2 PLC ±-		WEIGHT -		
3 PLC ±.010 [±.254]		Customer Drawing		
4 PLC ±-		SCALE NONE		
ANGLES ±° 30' 0"		SHEET 1 OF 1		
FINISH -		REV BI		

1470-19 (3/11)