


Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.


FCI

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT No.	ROWS		SIGNAL												POWER							
		E1	12	11	10	9	8	7	6	5	4	3	2	1	P7	P6	P5	P4	P3	P2	P1	E2
51602-XX001 NOTE: 2	D C B A		E	E	E	E	E	E	X	X	E	E	E	E			X					



CODE	CONTACT TYPE
E	SIGNAL
PA	POWER
HA	HOLD-DOWN
X	OMITTED

mat'l code				NOTE 1		tolerances unless otherwise specified		CUSTOMER		A FCI www.fciconnect.com	
lfr	ecn no.	dr	date	linear	.XX±.01/.X±.3		projection		COPY	title	7P + 48S VERTICAL SOLDER RECEPTACLE
A	V81897	DLW	10/30/98		.XXX±.005/.XX±.13						
B	V90098	DLW	01/22/99	angles	.XXX±.0020/.XXX±.051			INCH/MM	product family	PWRBLADE	code
C	V01363	LSS	06-05-00		0° ± 2°						
D	V10810	EKK	01-31-01	dr	D. WOLFORD	10/30/98	scale	1:1	size	dwg no	213
E	V11164	LSS	04/09/01	enrg	J. BROWN	10/30/98					
F	DG05-0363	GuoJM	09/29/05	chr	J. BROWN	10/30/98	A	51602	sheet	1 of 3	
				appd	J. BROWN	10/30/98					
sheet index		revision		F	F	F					
		sheet		1	2	3					

Pro/E

cage code 22526

PDM: Rev:F

STATUS: Released

Printed: Dec 20, 2010

Tous droits strictement réservés. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.





FCI

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.


PRODUCT NUMBER

51602-XX001--

NOTE: 2



RECOMMENDED PCB LAYOUT

mat'l code				NOTE 1		tolerances unless otherwise specified		CUSTOMER		A FCI www.fciconnect.com	
lfr	ecn no.	dr	date	linear	.XX±.01/.X±.3		COPY		projection 	title	
F					.XXX±.005/.XX±.13					7P + 48S	
					.XXX±.0020/.XXX±.051					VERTICAL SOLDER RECEPTACLE	
				angles	0° ± 2°		INCH/MM		product family		code
				dr	D. WOLFORD	10/30/98	scale		PWRBLADE		213
				enqr	J. BROWN	10/30/98	1:1		size		sheet
				chr	J. BROWN	10/30/98			dwg no		2
				appd	J. BROWN	10/30/98			A		
sheet index	revision										
	sheet										

cage code 22526

Pro/E

PDM: Rev:F

STATUS: Released

Printed: Dec 20, 2010

PRODUCT NUMBER
51602-XX001__
NOTE: 2

CONNECTOR NOTES:

- HOUSING MATERIAL: UL 94 V-0 GLASS FILLED HIGH TEMP THERMOPLASTIC
POWER CONTACT MATERIAL: COPPER ALLOY
SIGNAL CONTACT MATERIAL: COPPER ALLOY

2. PLATING:

51602-XX001 Singal Pin:30u"/0.76um Au OVER 50u"/1.27um Ni ON THE CONTACT AREA,
AND 100u"/2.54um SnPb PLATING OVER 50u"/1.27um Ni ON THE TERMINATION SECTION.
Power Pin:30u"/0.76um Au OVER 50u"/1.27um Ni ON THE CONTACT AREA,
AND 100u"/2.54um SnPb PLATING OVER 50u"/1.27um Ni ON THE TERMINATION SECTION.

51602-XX001LF Singal Pin:30u"/0.76um Au OVER 50u"/1.27um Ni ON THE CONTACT AREA,
AND 78u"/2.00um Sn PLATING OVER 50u"/1.27um Ni ON THE TERMINATION SECTION.
Power Pin:30u"/0.76um Au OVER 50u"/1.27um Ni ON THE CONTACT AREA,
AND 78u"/2.00um Sn PLATING OVER 50u"/1.27um Ni ON THE TERMINATION SECTION.

PART NUMBER 51602-XX001LF MEETS EUROPEAN UNION DIRECTIVE AND JOTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.

THE HOUSING WILL WITHSTAND EXPOSURE TO 260° PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION WITH A CIRCUIT BOARD.

- "MANUFACTURER" NAME, P/N, AND DATE CODE TO APPEAR ON THIS SURFACE

- PRODUCT SPECIFICATION GS-12-149

PCB NOTES:

- ALL DIMENSIONS ARE BASIC UNLESS OTHERWISE SPECIFIED.
- ALL THROUGH HOLES ARE LOCATED WITH A TRUE POSITION OF 0.004 [0.10]
- ALL HOLE DIAMETERS ARE FINISHED HOLE SIZE
- Ø0.079[2.01] THROUGH HOLES ARE UNPLATED.
- Ø0.0453±0.0010 [1.151±0.025] DRILLED HOLES PLATED WITH 0.0003 [0.008] MIN SnPb OVER 0.001 [0.03] TO 0.003 [0.08] Cu PLATING TO ACHIEVE A Ø0.040±0.003 [1.02±0.07] HOLE.

CONFIDENTIAL

mat'l code				NOTE 1		tolerances unless otherwise specified		CUSTOMER		FCI			
lfr	ecn no.	dr	date					COPY		www.fciconnect.com			
F				linear		.XX±.01/.X±.3		projection		title 7P + 48S			
						.XXX±.005/.XX±.13				VERTICAL SOLDER RECEPTACLE			
				angles		.XXX±.0020/.XXX±.051				product family PWRBLADE			
						0° ± 2°				code 213			
				dr	D. WOLFORD	10/30/98		INCH/MM		size dwg no			
				engr	J. BROWN	10/30/98				A 51602			
				chr	J. BROWN	10/30/98		scale		sheet 3			
				appd	J. BROWN	10/30/98		1:1					
sheet index		revision sheet											