


耐水ソレノイドロック(通電時解錠型)

WATERPROOF SOLENOID LOCKS (UNLOCKED WHEN TURNED ON)

特徴 Feature



LE-70-11



- ステンレス製(ソレノイド部はテフロンコーティング処理)で耐食性に優れています。
- 電源をONにして解錠するソレノイド型電気錠(通電時解錠型)
- ラッチ機構(自動施錠タイプ)
- 表面・裏面取付け穴はLE-30-11・LE-33-11と同じです。用納備(ラッチ高さは異なります。)
- 表面・裏面取付け専用(表面取付けの時はカバーを外して行ってください。)

- Corrosion-resistant stainless steel is used.
(solenoid section is coated with Teflon)
- Turn power ON to unlock solenoid electric lock.
(excitation unlocking type)
- The latch mechanism is incorporated.
(auto-locking type)
- The front and the rear surface installation hole are the same as LE-30-11/LE-33-11. (The height of the latch is different.)
- Both front and rear surface attachment. (remove the cover when choosing the front surface attachment)

- 仕様
- 定格電圧: DC24V±5%
 - 消費電力: 7.4W
 - 消費電流: 310mA
 - 通電率: 100% (連続定格)
 - 使用荷重: ラッチ引込み力(水平時)/1.76N
ラッチ押込み力(水平時)/1.27N
 - パスボックス・各種ケース
 - 標準在庫品
 - 本製品のラッチストローク及び、引込み力、押出しづらは水平取付け時の値です。
 - 周囲温度40°Cで、コイル温度上昇分が約65°Cとなる消費電力を定格電圧(連続定格)としています。
 - ソレノイドに連続通電すると高温(70°C前後)になります。手が触れる懸念がある場合は放熱を考慮の上、火傷防止の処置をしてください。
 - 通電動作時はラッチへの負荷を取り除いてください。
 - ソレノイドに極性(+・-)はありません。

仕 様 Specifi-cations

- Rated voltage: DC24V±5%
- Power consumption: 7.4W
- Current consumption: 310mA
- Duty cycle: 100% (continuous rating)
- Working load: Latch retraction force (at horizontal) / 1.76N
Latch pushing force (at horizontal) / 1.27N

- 用途考
Specific use
Remarks
- Pass boxes and various cases
 - The latch stroke, the retraction force and the extension force are value in the horizontal installation.
 - The rated voltage (continuous rating) is at a power consumption that causes the temperature of the coil to reach 65°C when the ambient temperature is 40°C.
 - When continuously energized, the solenoid becomes hot (around 70°C). If there is a risk of it being touched, measures should be taken to prevent burns with consideration given to heat radiation.
 - Remove the load on the latch when operating electrically.
 - Solenoid has no polarity (+/-).



商品番号 Product No.	RoHS 10 CAD	製品質量(g) Mass	コード Code	単価 Price	量販価格 Bulk Price
LE-70-11	2D	330	50210	¥8,500	5個～ ¥8,160

● : RoHS10指令対応品
▲ : RoHS10指令に対応可能です。
※大量のご注文は更にお安くなります。