


CH20M CH20M12 C TP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-2083
www.weidmueller.com



Superior efficiency, flexibility and design - the "standard tailor-made fit"

When selecting a housing design, flexibility is a key factor. Other important criteria are: scalability, customized design, innovative functionality and cost efficiency. You need a choice which offers the maximum performance with the minimum overhead.

The CH20M12 modular electronics housing is the "small" option amongst the "large" housing solutions for compact electronics applications.

The entire system is characterized by excellence: outstanding scalability and flexibility, a high security level, innovative application functionality and a variety of practical details.

- **Quicker installation** with features such as "Wire ready" the universal multi-tool screw head
- **User-friendly operations:** with clear and permanent labelling and extra marking possibilities, integrated release clip or transparent cover
- **Maximum interference immunity** with EMC-compliant construction featuring deeply overlapping module joint edges made from high-performance plastic
- **High operational reliability** with the unique Auto-Set coding system and featuring double-sided touch protection on the pin header and socket blocks

CH20M - a compact name for the most flexible system available on the market. It doesn't just stand for "Component Housing IP20 Modular".

CH20M also stands for efficiency and innovation throughout design, production and use.

Note: technical specifications are preliminary

General ordering data

Order No.	1104250000
Part designation	CH20M12 C TP
Version	Electronics housings, CH20M transparent, Tilt cover, Width: 12.5 mm
GTIN (EAN)	4032248878581
Qty.	70 pc(s).

CH20M CH20M12 C TP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-2083
www.weidmueller.com

Technical data

Dimensions (1)

Length	84.83 mm	Width	12.5 mm
Height	17 mm		

System parameters

Version	Tilt cover
---------	------------

Material data

Flammability class UL 94	V-0	Insulating material	PC
Colour	transparent	Highest continuous operating temperature, min.	-20 °C
Highest continuous operating temperature, max.	85 °C		

Approvals

Approvals institutes

Classifications

eClass 6.0	90-27-26-07
------------	-------------