

MATERIALS AND FINISHES







BODY, CRIMP TUBE BRASS
PLATED GOLD

OUTER CONTACT BERYLLIUM COPPER
PLATED GOLD

CENTER CONTACT BERYLLIUM COPPER
PLATED GOLD

INSULATOR TEFLON

CRIMP USING .128 HEX DIE



73415-5034	73415-5033 W/GOLD FLASH BODY / STANDARD TRAY
73415-5033	GOLD 8u" MIN. / STANDARD TRAY (80 CAV.)
73415-5032	73415-5030 / SMALL TRAY (20 CAV.)
73415-5031	73415-5030 X 1 PER BAG
73415-5030	GOLD 10u" MIN. / STANDARD TRAY (80 CAV.)
PART NO.	DESCRIPTION

MIL-STD-348A, FIG. 326.1	INTERFACE
SPECIFICATION	DESCRIPTION

CHG:ADDED -5034 PER PDR14011525 EC NO: URF2014-0441 DRWN:RYEH CHKD: JAPPR:HUANG 2014/01/27 2014/02/11	DESCRIPTION REV
B5	

QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)
▽=0	4 PLACES ± --- ± ---
▽=0	3 PLACES ± --- ± ---
▽=0	2 PLACES ± --- ± ---
	1 PLACE ± --- ± ---
	0 PLACE ± ±
	ANGULAR ± 2 °
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

DIMENSION STYLE	SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION
MM/IN	12:1	METRIC	
DRAWN BY	DATE	TITLE	
TEF	2004/06/10	SMP JACK R/A FOR RG316 50 OHMS EWR-2492 SMP-JC/RA	
CHECKED BY	DATE		
SSS	2004/06/10		
APPROVED BY	DATE		
GMH	2004/06/10		
MATERIAL NO.	DOCUMENT NO.		
SEE TABLE	SD-73415-503		
SIZE			
C			

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	SHEET NO. 1 OF 1
---	---------------------