



Product Data Sheet

143X124

Replace "x" with 1, 2, or 3 for number of poles

Power Terminal Block

255 Amps 600 Volts AC/DC

Wire Range

- Line: (1) 250 kcmil - #6 AWG
- Load: (1) 250 kcmil - #6 AWG

Electrical Ratings

- 255 Amps
- 600V per UL 1059 & CSA 22.2 No.158, class B & C requirements
- SCCR of 10,000 A (default for terminal blocks)..
- CU9AL - 90°C connector terminal rating with copper or aluminum wire
- Factory & Field Wiring

Agency Compliance

- UR - UL Recognized Terminal Block, Evaluated to UL 1059, File No.XCFR2.E62806
- CSA - certified to C22.2 No. 158, File No. LR19766 (wire classes B & C only)
- CE compliant to IEC 60947-7-1


Material Information

- Insulator base:
 - Phenolic
 - Flammability rating of insulator base UL94V0
 - Insulator base temperature rating: -40°C to 150°C (UL RTI)
- Connector: copper, tin plated
- Terminal set screws: brass, tin plated
- Connector mounting screws: steel, zinc plated
- RoHS compliant

A Regal Brand

REGAL

Termination Specifications

Line & load Side	Wire Size (CU Stranded)	Torque	Wires / Terminal	Wire Class (UL) ¹
	250 kcmil	42.4 N·m (375 lbf·in)	1	B, C
	4/0	42.4 N·m (375 lbf·in)	1	B, C, G, H
	3/0 - 2	42.4 N·m (375 lbf·in)	1	B, C, G, H, I (DLO)
	4 - 6	42.4 N·m (375 lbf·in)	1	B, C

- Aluminum wire range: 250 kcmil - #6 AWG
- Wire strip length:
 - line & load side taps: 1 3/16 in. (30mm)
- Terminal screw drive: 3/8 in. hex

¹ For information on copper stranded wire classes please reference:

<http://www.marathonsp.com/CatalogPDFs/Flexible-Stranded-Wire.pdf>

Installation & Accessories

- Mounting (Panel):
 - For use with #10 fastener.
 - Torque mounting fastener to 25-30 lbf·in (2.8 - 3.4 N·m).
- Covers:
 - Flat covers available upon request
 - Catalog Number: CH143x (replace "x" with number of poles)
 - Covers are clear polycarbonate
 - Accessory covers are not intended to provide insulation for electrical spacings.
- Marker Strip: white vinyl strip with mounting screws available.
- Printing options available, consult customer service for specifications.

Drawing

