







N=Number of poles



P.C.B. LAYOUT



SIGN	DATE	DESCRIPTION	APPROVER
		THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!	

Material

- Terminal body
(metal housing): Brass(CuZn)
- Terminal screw: Steel Zinc plating "-" slot type
- Wire guard: Stainless steel
- Surface of solder tail: Tin plated
- Insulator (housing): Thermoplastic (UL94V-0)

Electrical UL/CSA

- Voltage rating: 250VAC/250VAC
- Current rating: 16A/16A
- Wire range:
Solid wire(AWG): 14/14-22
Stranded wire(AWG): 14-22
- Torque: 2.6Lb-In/4Kgf.cm
- Screw: M3
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.5KV/1.5KV
- Operating temperature: -30°C to +105°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval:



RoHS Compliant

PART NUMBER:

OSTTBXX0161

No. of Poles
02 2 Poles
03 3 Poles
...
24 24 Poles

COLOR
0: Black
5: Green
6: Blue (Standard)
8: Grey



TITLE		OSTTB 5.0 series 2-Interlock			
PART NO.	OSTTBXX0161	DWG NO.	OSTTBXX0161.DWG	Tolerance	
APPROVED	Shi Jun 2006.10.19	CHECKED	Marvin 2006.10.19	DESIGNED	Marvin 2006.10.19
		DRAWN	Marvin 2006.10.19	CUST NO.	
				UNIT: mm	X. ±0.50
				SCALE: NONE	X.X ±0.30
				REV: D	X.XX ±0.10
				SHEET: 01/01	X° ±1°

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF ON-SHORE TECHNOLOGY, INC. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF ON-SHORE TECHNOLOGY, INC.