



PC BOARD VERSIONS		
PRODUCTNR:	PCB THICKNESS	DIM"A"
85789-X0Z	1.6	2.90
85789-X1Z	2.4	3.53

SEE NOTE 7



SEE NOTE 8



SEE NOTE 9




PLATING CONTACT AREA:	
DASH NR:	PERFORMANCE LEVEL
-1YY/1YYLF	TELCORDIA CO
-2YY/2YYLF	CUSTOMER SPECIAL
-3YY/3YYLF	CUSTOMER SPECIAL




PC BOARD THICKNESS ±0.20
SEE TABLE

PRODUCT AFTER HOT RIVETTING.



14.64 REF. SEE NOTE 6



RECOMMENDED HOLE PATTERN,
COMPONENT SIDE.

NOTES:

- 1 BODY MAT'L: LIQUID CRYSTAL POLYMER 30% GLASS FLAME RETARDANT ACC. UL 94-V0
- 2 TERMINAL MATERIAL: PHOSPHOR BRONZE.
- 3 PLATING SOLDER TAILS 2-8 um SnPb 90-97.
- 4 INDICATED HOLES ARE UNPLATED.
- 5 PRODUCT MARKING: PART NUMBER & BATCH ID.
- 6 SET BACK FOR PRESS BLOCK.
- 7 FOR CODE Z (SELECTIVE LOADING PATTERNS) SEE SHEET 2.
- 8 TOP SURFACE OF PRESS BLOCK MAY EXTEND UP TO 0.4MM HIGHER THAN HOUSING. THIS MAY AFFECT THE TAIL LENGTH BEFORE APPLICATION TO A BOARD
9. DIAMOND LOCATION PEG ARE ONLY EXISTED ON THE BOTH SIDES OF PRODUCT

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		FCI ELECTRONICS	
ltr	ecr no	dr	date	linear		projection		title	www.falconconnect.com
A	H70776	DOB	971112					RA RCP PRESSBLOCK	
B	V00862	LLA	000511					STB 48 mm SEL LOAD.	
C	V00847	LLA	000530	angles				product familMETRAL(tm)	code
D	D607-0189	Cent	05/15/07	dr	D. de Bli	971112		size	213
E	D609-0088	Cent	06/06/08	engr	P. Schalk	971112		dwg no	1 of 2
				chr	P. Schalk	971112	scale	A2	85789
				app	H. Coolmans	971112	5:1		
sheet	revision	E	E						
index	sheet	1	2						

PDM: Rev:E

STATUS: Released

Printed: May 19, 2011

Tous droits strictement réservés. Reproduction ou communication à des tiers
interdite sans autorisation écrite du propriétaire.
FCI B.V.

All rights strictly reserved. Reproduction or issue to third parties in any form
without prior written permission is not permitted without written authority from the proprietor.
FCI B.V.



LOADING CONFIGURATION	POSITION ROW	24	23	22	21	20	19	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1
85789-XY1	d	+	0	+	0	+	0	+	0	+	+	+	0	+	0	0	0	+	0	+	0	0	0	+	0
	c	0	+	0	+	0	+	0	+	0	+	0	+	0	+	0	+	0	0	0	+	0	0	0	+
	b	+	0	+	0	+	0	+	0	+	+	+	0	+	0	0	0	+	0	+	0	0	0	+	0
	a	0	+	0	+	0	+	0	+	0	+	0	+	0	+	0	+	0	0	0	+	0	+	0	+
85789-XY2	d	+	0	+	0	+	0	+	0	+	+	+	0	+	0	0	0	+	0	+	0	+	0	+	0
	c	0	+	0	+	0	+	0	+	0	+	0	+	0	+	0	+	0	0	0	+	+	0	0	+
	b	+	0	+	0	+	0	+	0	+	+	+	0	+	0	0	0	+	0	+	0	0	0	+	0
	a	0	+	0	+	0	+	0	+	0	+	0	+	0	+	0	+	0	0	0	+	0	+	0	+
+ =LOADED POSITION 0 =EMPTY POSITION																									

mat'l. code				tolerances unless otherwise specified			CUSTOMER COPY		ELECTRONICS www.fciconnect.com	
ltr	ecr	no	dr	date	Linear		projection		title RA RCP PRESSBLOCK STB 48 mm SEL LOAD.	
E										
					angles		mm		product familyMETRAL(tm)	
					dr	D. de Bil	971112			
					enr	P. Schalk	971112	scale	size dwg no	
					chr	P. Schalk	971112			
					app	H. Coorjmans	971112	A3		sheet 2 of -
sheet index	revision sheet									