

The 89 Series is a high-performance axial type resistor. These molded-construction metal-housed resistors are available in higher power ratings than standard axial resistors and are better suited to withstanding vibration, shock and harsh environmental conditions.

The 89 Series Metal-Mite® resistors are aluminum housed to maintain high stability during operation and to permit secure mounting to chassis surfaces.

The metal housing also provides heat-sinking capability.

FEATURES

- High Stability: $\pm 0.5\%$ ΔR .
- High power to size ratio.
- Metal housing allows chassis mounting and provides heat sink capability.

As of September 2006, the 89 Series is no longer offered as Mil. Spec.

SPECIFICATIONS

Material

Housing: Metal, anodized aluminum.

Internal Coating: Silicone.

Core: Ceramic.

Terminals: Solder-coated axial.

Derating: Linearly from 100% @ +25°C to 0% @ +275°C.

Electrical

Tolerance: $\pm 1\%$ and $\pm 5\%$ (other tolerances available).

Power rating: Rating is based on chassis mounting area and temperature stability. Proper heat sink as follows: 5W and 10W units, 4" x 6" x 2" x .040" Aluminum chassis; 25W units, 5" x 7" x 2" x .040" Aluminum chassis; 50W units, 12" x 12" x .059" Aluminum panel.

Maximum ohmic values:

See chart.

Overload: 5 times rated wattage for 5 seconds.

Temperature coefficient:

Under 1Ω: ± 90 ppm/°C
1 to 9.99Ω: ± 50 ppm/°C
10Ω and over: ± 20 ppm/°C.


Dielectric withstanding voltage:

5W and 10W rating, 1000 VAC;
25 and 50W ratings, 2250 VAC.



89 Series

Metal-Mite® Aluminum Housed Axial Term. Wirewound, 1% Tolerance



Series	Wattage	Ohms	Voltage
805	5	0.10-25K	210
810	10	0.10-50K	320
825	25	0.005-75K	520
850	50	0.005-100K	1170

Non-Inductive versions available. Insert "N" before tolerance code. Example: 850NF560

	5 watt	10 watt	25 watt	50 watt
Series (Industrial)	805	810	825	850
Dimensions				
Dim. A (in. ± 0.062 / mm ± 1.57)	1.125 / 28.59	1.375 / 34.93	1.938 / 49.23	2.781 / 70.64
Dim. B (in. ± 0.010 / mm ± 0.25)	0.490 / 12.45	0.625 / 15.88	0.781 / 19.84	0.844 / 21.44
Dim. C (in. ± 0.031 / mm ± 0.79)	0.078 / 1.98	0.094 / 2.39	0.172 / 4.37	0.188 / 4.78
Dim. D (in. ± 0.010 / mm ± 0.25)	0.444 / 11.28	0.562 / 14.28	0.719 / 18.26	1.562 / 39.68
Dim. E (in. ± 0.062 / mm ± 1.57)	0.600 / 15.24	0.750 / 19.05	1.062 / 26.98	1.938 / 49.23
Dim. F (in. ± 0.062 / mm ± 1.57)	0.266 / 6.76	0.312 / 7.93	0.438 / 11.13	0.438 / 11.13
Dim. G (in. ± 0.062 / mm ± 1.57)	0.334 / 8.48	0.438 / 11.13	0.531 / 13.49	0.594 / 15.09
Dim. H (in. ± 0.031 / mm ± 0.79)	0.245 / 6.22	0.312 / 7.93	0.391 / 9.93	0.422 / 10.72
Dim. J (in. ± 0.031 / mm ± 0.79)	0.646 / 16.41	0.812 / 20.63	1.094 / 27.79	1.156 / 29.36
Dim. K (in. ± 0.005 / mm ± 0.13)	0.093 / 2.36	0.094 / 2.39	0.125 / 3.18	0.125 / 3.18
Dim. L (in. ± 0.031 / mm ± 0.79)	0.320 / 8.13	0.406 / 10.31	0.562 / 14.28	0.625 / 15.88
Dim. M (in. ± 0.062 / mm ± 1.57)	0.133 / 3.38	0.203 / 5.16	0.281 / 7.14	0.312 / 7.92
Dim. N (in. ± 0.031 / mm ± 0.79)	0.065 / 1.65	0.094 / 2.39	0.094 / 2.39	0.094 / 2.39
Dim. P (in. ± 0.005 / mm ± 0.13)	0.050 / 1.27	0.085 / 2.16	0.085 / 2.16	0.085 / 2.16
Q min AWG	16	12	12	12
Dim. R (in., min/mm, min)	0.085/ 2.16	0.140/ 3.56	0.140/ 3.56	0.140/ 3.56

ORDERING INFORMATION

Non-Inductive Winding
Optional (blank = std. winding)

805NF5R0E

Series
805 = 5 Watt
810 = 10 watt
825 = 25 watt
850 = 50 watt

Tolerance
F = 1%
J = 5%

Ohms
R005 = 0.005Ω
R10 = 0.1Ω
1R0 = 1.0Ω
250 = 250Ω
1K0 = 1,000Ω
1K5 = 1,500Ω
25K = 25,000Ω

RoHS Compliant

STANDARD PART NUMBERS

Wattage						Wattage						Wattage					
Ohmic value	Part No.	5	10	25	50	Ohmic value	Part No.	5	10	25	50	Ohmic value	Part No.	5	10	25	50
	Prefix ▶ Suffix ▼	805F 810F	825F 850F	805F 810F	825F 850F		805F 810F	825F 850F	805F 810F	825F 850F	805F 810F		825F 850F	805F 810F	825F 850F		
0.005 — R005		✓	✓			20 — 20R		✓	✓			1,500 — 1K5		✓	✱	✱	✓
0.010 — R010			✓	✓		25 — 25R		✓	✓			2,000 — 2K0		✓	✓	✱	✱
0.025 — R025			✓	✓		30 — 30R		✱	✱			2,500 — 2K5		✱	✓		
0.1 — R10			✓	✓		40 — 40R		✱	✓	✓		3,000 — 3K0		✱	✓	✓	✱
0.3 — R30			✓	✱		50 — 50R		✓	✓	✓		3,500 — 3K5		✱	✱		
0.5 — R50			✓	✱		75 — 75R		✓	✱	✓		4,000 — 4K0		✱	✓		
0.7 — R70				✱	✱	100 — 100		✓	✓	✓		4,500 — 4K5		✱	✱		
1.0 — 1R0		✓	✓	✓		150 — 150		✓	✓	✓		5,000 — 5K0		✓	✓		✓
1.5 — 1R5		✱				200 — 200		✱	✱	✓		6,000 — 6K0		✱	✱		
2.0 — 2R0		✱	✓	✓	✓	250 — 250		✓	✓	✓		10,000 — 10K		✱	✱	✓	✓
3.0 — 3R0		✓	✓	✓	✓	300 — 300		✓	✱			15,000 — 15K		✓	✓	✱	✱
4.0 — 4R0		✱	✓	✓		400 — 400		✱	✱			20,000 — 20K		✱	✱		
5.0 — 5R0		✓	✓	✓	✓	500 — 500		✓	✱	✓		25,000 — 25K		✓		✱	✱
10.0 — 10R		✓	✓	✓	✓	750 — 750		✱	✱	✓		50,000 — 50K			✱		
15.0 — 15R		✓	✓	✓	✓	1,000 — 1K0		✱	✓	✓		75,000 — 75K			✱		
												100,000 — 100K				✱	

✓ = Standard values

✱ = Non-standard values subject to minimum handling charge per item

Shaded values involve very fine resistance wire and should not be used in critical applications without burn-in and/or thermal cycling.

Check product availability at www.ohmite.com