


# CUSTOMIZED SWITCHING POWER SUPPLIES & CUSTOMIZED DC-DC CONVERTERS



Following the production of its first switching power supply in 1974, FDK has produced these electronic components for over 25 years. The mainstay of production is customized switching power supplies and DC-DC converters. In this brochure, we shall introduce the production framework and product line of our switching power supplies, along with DC-DC converters.

### Contents

	Page
■ FDK production framework ······	2
■ FDK's power supply technologies ·······	7
■ Customized switching power supplies ········	14
■ Customized DC-DC converters······	20

### **FDK** production framework

### (1) Features

### **■** Global operation

FDK produces switching power supplies not only in Japan but also in Taiwan and China.

### **■** High-power-factor technology

FDK is a leading creator of technologies for high-power-factor switching power supplies, power-factor-correction (PFC) modules, and PFC hybrid modules.

### **■** High-efficiency technology

FDK has achieved high efficiency DC-DC converter by applying ASIC to synchronized rectification.

### ■ Intensive packaging technology


FDK has downsized its power supplies by using intensive component packaging techniques involving hybrid modules, metallic circuit boards and so on.

### **■** Redundancy technology


FDK answers the needs of redundant devices such as servers based on the technology of redundant parallel operation with current sharing, maintenance in active state and high reliability.

### (2) Production bases


### (In Japan)



### (Outside Japan)



### **3 Global sales operation**



### 4 FDK's power supply plants



### **FDK Kosai Plant**

- The main plant
- Backed by the FDK R&D Center
- One of the Center's task is to develop and design medium to large power supplies.



#### **XIAMEN FDK CORPORATION in Xiamen, China**

- Founded in 1994 to supply lower-priced products.
- The new plant completed in February 1998.
- Produces power supplies in large lots.
- FDK's central overseas plant, also produces motors and hybrid modules



#### Iwaki Plant of IWAKI ELECTRONICS CO.,LTD.

- IWAKI, a wholly owned subsidiary of FDK, manufactures power supplies, hybrid modules and other assembled products.
- The coordinator of FDK's entire power supply manufacturing operation.
- Develops and designs small to medium power supplies and DC-DC converters.
- Produces trial, small-lot, large-sized and high-reliability power supplies, along with DC-DC converters.
- Also produces control-use hybrid modules and highdensity DC-DC converters using metallic circuit boards.

### [Power supply producing plants]

In Japan, FDK power supplies are developed and produced by IWAKI ELECTRONICS CO.,LTD., which is a wholly owned subsidiary of FDK. Power supplies are also produced in FDK plants in Taiwan and China.

Plant	Power supply technology dept. of IWAKI ELECTRONICS (located inside FDK's Kosai Plant ground)	Iwaki Plant of IWAKI ELECTRONICS	XIAMEN FDK (China)
Capital			100% owned by FDK
Main role	Development and design of medium to large power supplies (PS)	Development and design of small PS and CV; production of intensively packaged PS and CV; production of small-lot and trial products	Production of large-lot power supplies

PS : Power supplies CV : DC - DC converters


4

### 5 Development and production systems

### 1 High-frequency power ferrite cores

FDK develops and produces ferrite cores for use in:

- TV deflection yokes
- VCR rotary transformers
- Switching power supply transformers/choke coils. Ferrite technology is fully utilized in FDK's switching power supplies.



### Design simplified and standardized by CAD

CAD and CAM systems play a crucial role in the design and production of switching power supplies.

- Development time is reduced.
- · Quality upgraded.
- Delivery periods are shortened.
- Product prices lowered.



### 3 Intensive packaging through Hybrid modules


The hybrid modules developed and produced by IWAKI ELECTRONICS are applied to the downsizing and intensive packaging of our switching power supplies.



### 4 Sufficiency in transformers/choke coils

The production capacity for switching power supplies is enhanced by:

- · Acquiring automatic winding machines
- Operating a specialized transformer/choke coil plant.



### 6 Automated helpers in circuit packaging

The mounting and packaging of components on circuit boards are automated to the highest degree in order to achieve:

- Higher quality
- Faster delivery
- Lower cost



### 6 Quality screening by aging tests

All new power supplies fresh off the assembly line undergo a high-temperature aging process to weed out defective products at an early stage.



### Quality assurance by measuring systems

Tuning, testing and inspections are performed by automated measuring systems to assure the quality of FDK's switching power supplies.



### 8 Reliability tests on engineering samples

Thorough reliability tests are performed on engineering samples of power supplies so that the end products will perform at their intended levels.

- Electric characteristics test
- Mechanical characteristics test
- Safety confirmation test, etc



#### Noise control through noise measurement

FDK operates advanced noise-measuring facilities to rule out noise problems not only from its switching power supplies but from equipment incorporating power supplies.

- Terminal noise control
- · Radiation noise control



### Meeting international standards

FDK can quickly meet UL, CSA, IEC and other international safety standards with respect to customized switching power supplies. In addition, all of its power supply plants are ISO-9002-approved. Thus these plants are internationally recognized as being capable of assuring quality.

### FDK's power supply technologies


### 1 Power factor correction (PFC) circuit technology

### Purpose of power factor correction


PFC circuits are intended to modify the input current waveform so as to resemble an input voltage waveform or, in other words, to achieve a power factor that is close to 1. There are three major purposes of power factor correction, as outlined below.

- Control of high-harmonic current Many countries regulate high-harmonic current, which adversely affects power facilities, in response to the IEC 1000-3 Standard.
- Reduction of peak input current
   Peak input current needs to be lowered so as to stay below the current
   capacities of power equipment and
   capacitors.
- Compatibility with world input voltages
   Automatic compatibility over a wide
   range of input voltages from 90V to
   264V is achieved by PFC circuits
   equipped with rising voltage capacitors


### PFC and conventional circuits



PFC characteristics



### PFC block diagram and operation waveform



### • Input current reduction effect of PFC

Because switching power supplies adopt the capacitor input rectification method, the input current peak is very high, thereby pushing down the power factor to 0.6 or 0.7.

As shown by the equation below, however, the input current can be reduced if the power factor is improved toward 1.

 $Input \ current = \frac{Output \ power}{Efficiency \times Power \ factor \times Input \ voltage}$ 

### Comparison of FDK switching power supplies with and without PFC (when using a 2kW output DC-DC converter)

	<u> </u>		
Circuit type	Conventional (without PFC)	With PFC	
Description	FDK's conventional switching power supplies without PFC are operated by pulse current, so that the peak current is 3 to 5 times higher than the effective input current (see Fig.A). This is accompanied by a drop in the input voltage due to the impedance of the input power supply line, thus causing distortions in the input voltage waveform (Fig.B). Moreover, since the input pulse current does not have a sine waveform, it contains many harmonic elements which are likely to generate noise.	FDK's new switching power supplies incorporating PFC enable the input current to have a sine waveform in proportion to the input voltage. The pulse current is thus eliminated, and the peak value of the input current is lowered (see Fig.C). Further, voltage drops and waveform distortions are also forestalled.	
Input voltage range	AC 85-132V or AC 170-264V	85VAC~264VAC	
Input current	21A (200VAC)	15A (200VAC)	
Input current waveform	Fig.A  **S5A**  **S5A	Fig.C	
Power factor	0.6~0.7 (200VAC)	0.95 or more (AC 200V)	
Input voltage waveform distortions  ( Line impedance: 0.1Ω	Fig.B \$\\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\	Fig.D 2.1V	
		(Waveform distortions eliminated)	


### 2 PFC Products

### PFC modules: PFCM300-03


Taking advantage of intensive packaging technology, these PFC modules incorporate an inrush current-limiting circuit (with an external resistor), an input rectifier, an inductor, and an auxiliary power supply circuit all in one compact unit. Using a PFC module, it is easy to enable switching power supplies to meet the harmonic wave regulations without the help of many external components.

### **Features**

- Variable switching frequency
- DIP [13.7(H) × 65(W) × 90(L) mm]
- Built-in protection circuits
  - \*Overvoltage protection
  - \*Overcurrent protection
  - \*Thermal protection
- Conformity with major safety standards
  - \*UL 1950
  - \*CSA 234
  - \*IEC 950/EN 60950




### Example of PFC module application (improving the power factor of a switching power supply)



### **Electrical characteristics of PFC modules**

Item	PFCM300-03	Remarks
Input voltage	AC85V~AC264V	Operation startup voltage : AC60-70V
Output voltage	DC360V±2%	
Output power	300Wmax./600Wmax.	100V/200V systems
Output voltage variation	±2%	Line regulation Load regulation
Output ripple	8V/16V	100V/200V systems
Efficiency	90%typ./94%typ.	100V/200V systems
Power factor	0.95Vmin.	
Overvoltage protection	390V±5V	
Thermal protection	100°C	Aluminum substrate surface temperature
Auxiliary power supply output	12V~18V 10mAmax.	
Isolation resistance	100MΩmin.	Terminal-to-casing when DC 500V
Isolation withstand voltage	AC1500V for 1 min.	Terminal-to-casing

### **Shape and dimensions**



### **Terminal name and function**

Pin No.	Terminal code	Function
1	AC IN (L)	AC input terminal (L)
2	R	Terminal for connecting an inrush prevention resistance
3	AC IN (R)	AC input terminal (N)
4	360V (+)	+360V output terminal
(5)	0V	+360V return
6	Remote	Remote control terminal
7	Vout Adj	Terminal for output voltage adjustment
8	Vcc Out	Output terminal of auxiliary power supply
9	PFD	Operation confirmation signal output terminal
10	GND	Grounding


Made to order

### PFC control hybrid modules


By adopting a continuous current formula, these PFC circuit control modules minimize the amount of the rated current required by peripheral circuit components, thereby enabling the host equipment to meet the harmonic wave regulations. They are designed for power supplies of up to several kW capacity.

### **Features**

- Compatible with a wide range of output power thanks to the large drive output current (Io = ±2A)
- ON/OFF control possible by using external signals



### **Example of PFC control hybrid modules application**




### Absolute maximum rating of PFC control hybrid modules

Item	Symbol	Min. value	Max. value	Unit
Supplied voltage	Vcc	_	18	٧
Comparator input voltage	Isense1,2	-0.3	20	٧
Control amplifier input	Vsense	-0.3	6	٧
Multiplier input current	I in sense	_	100	mA
Overvoltage protection input	Vovp	-0.3	7	V
Overcurrent protection input	Vocp	_	-1	V
Drive circuit output current	lo	_	±2	Α
Operating temperature	Topr	-25	85	°C
Non-operating temperature	Tsts	-30	105	°C

### **Recommended operating conditions**

Item	Symbol	Min. value	Max. value	Unit
Supplied voltage	Vcc	12	15	V
Comparator input	Isense1,2	0	3.5	V
Control amplifier input	V SENSE	0	3.5	V
Multiplier input	V in sense	0	1.6	V

### **Shape and dimensions**



### **Terminal name and function**

Pin No.	Name	Function
1	V in sense	Multiplier input
2	OCP	Overcurrent detection input
3	GND 1	Ground
4	Vcc	Auxiliary power supply input
(5)	OUT	Switching element drive output
6	I sense 1	Current comparator input 1
7	I sense 2	Current comparator input 2
8	GND 2	Ground
9	REMOTE	ON/OFF control input
10	V out adj.	Output voltage adjustment by external resistor
11)	V sense	Output voltage detection input
12	OVP	Overvoltage detection input


Made to order

### High-efficiency intensive-packaging technology


As electronic equipment is downsized, switching power supplies and DC-DC converters must be made more compact, lightweight and flat. Surface packaging technology is utilized for higher-density packaging. In addition, the internal loss and heat release of the switching power supply must be improved.

- 1) FDK adopts a synchronized rectification method so as to boost efficiency, which in turn improves the internal loss.
- ②FDK uses single-surface or double-surface metallic boards to enhance the heat release performance.


We recommend various combinations of these steps to our customers, so that the best overall balance is achieved as a total electronic system.



Example of intensive packaging by using a double-surface metallic circuit board



Example of high-efficiency packaging through the synchronized rectification method




Example of intensive packaging by using a single-surface metallic circuit board

### **Customized switching power supplies**

# ■Customized switching power supplies for personal computers

Designed for desk-top PCs that automatically adjust input voltage in order to meet the harmonic wave regulations, these power supplies have a 150W-4ch output and provide separate 100V and 200V input voltage options.




### **Characteristics (examples)**

	Item Rated value				
	Input voltage	AC 100V/200V (AC 90~132V or AC 187~276V)			
	Frequency	50/60Hz (48~62Hz)			
Input	Inrush current		42A	max.	
-	Efficiency		60%	min.	
	Power factor		IEC 1	00-3-2	
	Channels	ch1	ch2	ch3	ch4
	Output voltage	+5.0V	+12.0V	-12.0V	-5.0V
	Rated current	13A	3.5A	0.3A	0.3A
put	Current range	1.5~18A	0~4.2A	0~0.5A	0~0.5A
Output	Ripple/noise	150mV	360mV	360mV	150mV
	Overall regulation	+5%-4%	±5%	±10%	+10%-8%
	Overvoltage protection	+5.6~+6.8V	+13.6~+15.6V		
	Overcurrent protection	Short circuit protection	Short circuit protection	Short circuit protection	Short circuit protection
ions	Operating temp./humidity		0~+50°C, 20~80%R	RH (No dew deposit)	
condit	Non-operating temp./humidity		-10~+70°C, 10~90%	RH (No dew deposit)	
Ambient conditions	Vibration		0.5G, 1~100~1Hz/60sec, X	YZ directions, 10 min. each	
Amk	Shock		40G, 10msec, XYZ di	rections, 3 times each	
sions	Dimensions		150 × 140	0 × 86mm	
, dimer	Casing	Encased			
Construction, dimensions	Thermal radiation	Built-in fan			
1	Thermal protection		_		
Standards	Noise standards		VCCI class II,	FCC-B, VDE-B	
Stand	Safety standards	UL1950, IEC950, CSA C22.2 950, Denki Yohin (JAPAN)			

# ■Customized switching power supplies for work stations

These are 150W-3ch switching power supplies for work stations with built-in active filters, and conform to worldwide input voltage or harmonic wave regulations.




### **Characteristics (examples)**

Item Rated value					
	Input voltage	Input voltage AC 100V/200V (AC 87~264V)			
	Frequency		50/60Hz (47~66Hz)		
Input	Inrush current		60Amax.		
	Efficiency		65%min.		
	Power factor	0.	.95 or more (with a built-in active filte	er)	
	Channels	ch1	ch2	ch3	
	Output voltage	+5.0V	+12.0V	-12.0V	
	Rated current	25A	2.0A	0.1A	
Output	Current range	2.0~25A	0.2~3.5A	0~0.4A	
Out	Ripple/noise	50mV	100mV	100mV	
	Overall regulation	±3%	±5%	±5%	
	Overvoltage protection	6.0~7.0V	13.0~16.0V		
	Overcurrent protection	29.0~35.0A	8.0~12.0A	0.5~2.0A	
suo	Operating temp./humidity	0~+50°C, 10~90%RH (No dew deposit)			
Ambient conditions	Non-operating temp./humidity	-4	0~+70°C, 0~95%RH (No dew depos	sit)	
ient o	Vibration	1.0G,	5~300~5Hz, XYZ directions, 30 min	. each	
Amb	Shock	400	G, 11msec, XYZ directions, 3 times e	ach	
sions	Dimensions		200 × 100 × 70mm		
Construction, dimensions	Casing	Encased			
uction,	Thermal radiation	Built-in fan			
Constr	Thermal protection				
ards	Noise standards		VCCI class II, FCC-A, VDE-A		
Standards	Safety standards	UL1950, II	EC950, CSA C22.2 950, Denki Yohir	n (JAPAN)	

# ■Customized switching power supplies for fax machines

These switching power supplies are suited for compact fax machines using A4 thermo-sensitive papers. They provide separate 100V and 200V input voltage options, and they have +5V, +24V and  $\pm12$  output channels, a 30W rated output, and a 130W peak output.




### **Characteristics (examples)**

	Item	Rated value			
	Input voltage	AC 100V/200V (AC 90~132V or AC 180~264V)			
	Frequency 50/60Hz (48~62Hz)				
Input	Inrush current		40Aı	max.	
_	Efficiency		65%	smin.	
	Power factor		_		
	Channels	ch1	ch2	ch3	ch4
	Output voltage	+5.0V	+12.0V	-12.0V	+24.0V
	Rated current	0.6A	0.05A	0.05A	1.0A
Output	Current range	0.2~1.0A	0.01~0.1A	0.01~0.1A	5.0A
Out	Ripple/noise	200mV	300mV	300mV	700mV
	Overall regulation	±5%	±10%	±10%	±5%
	Overvoltage protection	<del></del>			
	Overcurrent protection	Short circuit protection			
suo	Operating temp./humidity	0~+50°C, 10~90%RH (No dew deposit)			
Ambient conditions	Non-operating temp./humidity		−20~+70°C, 0~95%F	RH (No dew deposit)	
ient o	Vibration		2G, 10~55~10Hz/min., XY	Z directions, 30 min. each	
Amb	Shock		30G, 11ms, XYZ dire	ections, 3 times each	
sions	Dimensions		60 × 175	5 × 39mm	
, dimer	Casing	Open frame			
Construction, dimensions	Thermal radiation	Natural cooling			
	Thermal protection		_		
Standards	Noise standards		VCCI class II,	FCC-B, VDE-B	
Stanc	Safety standards	UL1950, IEC950, CSA C22.2 950, Denki Yohin (JAPAN)			

# ■Customized switching power supplies for photocopiers

Intended for compact and medium to high-speed photocopiers, these switching power supplies have two output channels (+5V, +24V), a 160W rated power, and a 250W peak power. They provide 100V and 200V input voltage options.




### **Characteristics (examples)**

	Item	Rated	value	
	Input voltage	AC 100V/200V (AC 85~138V or AC 187~276V)		
	Frequency	50/60Hz (45~65Hz)		
Input	Inrush current	50Ar	max.	
-	Efficiency	70%	min.	
	Power factor		_	
	Channels	ch1	ch2	
	Output voltage	+5.0V	+24.0V	
	Rated current	0.5A~1.5A	0.05A~6.5A	
but	Current range	0.5~2.0A	0.05~10A	
Output	Ripple/noise	100mV	480mV	
	Overall regulation	±5%	±10%	
	Overvoltage protection	5.5~7.0V	27~33V	
	Overcurrent protection	1.7~5.0A	10.1~15.0A	
suo	Operating temp./humidity	0~+55°C, 10~95%R	RH (No dew deposit)	
Ambient conditions	Non-operating temp./humidity	-40~+70°C, 10~95%	RH (No dew deposit)	
oient o	Vibration	2mm amplitude, constant 16Hz	z, XYZ directions, 30 min. each	
Amk	Shock	30G, 11msec, XYZ di	rections, 3 times each	
sions	Dimensions	100 × 240 × 50mm		
Construction, dimensions	Casing	Open frame		
ruction	Thermal radiation	Natural cooling		
	Thermal protection	_		
Standards	Noise standards	VCCI class II, I	FCC-A, VDE-A	
Stand	Safety standards	UL114, IEC950, CSA C22.2 950, Denki Yohin No. 8 (JAPAN)		

# ■Customized switching power supplies for control equipment

We offer compact, highly reliable switching power supplies for programmable controllers. Input voltages come in 100V and 200V types, while their two-channel outputs are +5V and +24V (30W-2ch).



### **Characteristics (examples)**

	Item	Rated value					
	Input voltage	AC 100V/200V (AC 85~132V / AC 170~264V)					
l ts	Frequency	50/60Hz (47Hz~63Hz)					
Input	Inrush current	20Amax.					
	Efficiency	65%					
	Channels	ch1	ch2				
	Output voltage	+5.0V	+24.0V				
	Rated current	3.0A	0.6A				
	Current range	0~3.0A	0~0.6A				
Output	Ripple/noise	200mVp-p	500mVp-p				
	Overall regulation	±3%	±9%				
	Overvoltage protection	5.5~6.5V	<del></del>				
	Overcurrent protection	3.3~9.0A	0.66~1.88A				
	Remote control		<del></del>				
ions	Operating temp./humidity	0~+55°C, 10~90%RH (No dew deposit)					
Ambient conditions	Non-operating temp./humidity	-20~+80°C, 10~95%RH (No dew deposit)					
ojent o	Vibration	JIS C0911 10~55Hz 2G					
Amk	Shock	JIS C0912 15G XYZ directions, 3 times each					
Sions	Dimensions	88 × 125 × 47mm					
Construction, dimensions	Casing	Open frame					
ruction	Thermal radiation	Natural cooling					
	Thermal protection	<del></del>					
Standards	Noise terminal voltage	FCC	C-A				
Stand	Safety standards	UL508 CSA NO. 142/E.B.1402C					

### ■How to order customized switching power supplies

FDK designs and manufactures customized switching power supplies on the basis of the specifications provided by the customer. When placing orders, please consider the following recommendations:

- ① We are willing to shorten the development period for you. Please feel free to discuss your schedule with us.
- ② In order to indicate the specifications you desire, please enter all information in the righthand table.
- ③ Please explain the intended aim of the switching power supplies you are looking for and the conditions under which they will be used.
- 4 If you have any questions or requests before placing an order, we welcome your early contact.

### **Development steps**

Step	Flow chart	Customer	F D K	Ave. days Required
	Inquiry	Prepare rough specifications and design requests		rtoquilou
	Consulting	Consultation on sp	1 day	
Engineering sample production	Cost estimate		Draw up a circuit and parts plan, and produce a cost estimate:  • Engineering sample cost  • Mass product cost  • Development cost  circuit & system design engineering sample evaluation  PCB metal mold cost parts metal mold cost  • Safety approval acquisition cost  • Reliability evaluation cost	8 days
ngineerir	Development scheduling	Decide specifications, devel samples, mass production s	opment date, number of chedule, development cost, etc.	1 day
В	Circuit design; System design		1 Circuit design 2 System design 3 Assembly plan 4 Parts selection 5 Parts list 6 Parts procurement	20 days
	Consultation on samples	Production of sam • Engineering sam • Engineering sam • Pre-production sa	30 days	
Evaluation	Evaluation	Evaluation of actual operation in host equipment	Confirmation of characteristics, reliability, quality	60 days
Ш	Final consultation	Finalize specifications in	1 day	
Mass Production	Mass production			60 days from required

Note: The dates of engineering sample production, evaluation, and mass production sometimes overlap. Please check with our marketing divisionfor exact schedules.


### **Setting specifications**

<b>5</b> e	IJJ	ng specifica	itions				
		Input voltage	□V ±□% (V)				
		Frequency/phase	50/60 ± Hz				
		Power consumption	UVAmax. (UVUHz. rated load)				
		Power factor					
		Efficiency	─────────────────────────────────────				
		Inrush current	Amax.				
	'n						
	outk	Instantaneous shut time	1. None 2. msec. (LHz) max.				
	Rated output	Output voltage					
	Ra	Output current					
တ္က		Voltage regulation					
Electrical characteristics		Voltage variable range					
cter		Ripple/noise voltage					
Jara		Spike noise voltage					
ਕ ਹ		Total variation	□%         □%         □%         □%         □%				
tric		Over shoot					
Elec	io	Overvoltage protection					
-	Protection	Overcurrent protection					
	Pro	Thermal protection					
	u	Remote sensing					
	Noise Isolation Added function	Output sequence					
		Remote control	None 2. As per attached pape				
		Blackout sensing signal	None 2. As per attached pape				
		Withstand voltage	V AC/DC 1 min.				
		Isolation resistance	V DC MΩmin. at leak current mA max				
		External noise resistance	Pulse widthns, Peak valueV				
		Audible noise					
			☐dB max. ☐m distance				
g.		erating temp./humidity					
Ambience		n-operating temp./humidity					
dm\	Iе	mperature rise	☐°C max.  1. Natural cooling				
	Со	oling method	2. Forced cooling Wind direction, volume □ ℓ /min.				
Anti- vibration	Vik	pration resistance	☐Hz~ ☐Hz ☐G/mm ☐hr.				
vib A	Sh	ock resistance	☐m sec. ☐G ☐times				
	Su	rface treatment					
uo.	We	eight	□kg max.				
Construction	Dir	mensions	Mainframe □cm × □cm × □cm				
nst	Ins	tallation area/position					
ပ	Sa	fety regulation					
	Ca	sing	With casing, Open frame				
рg	Loa	ad electrostatic capacity					
Load	No	-load excitation					
ility	De	rating					
Reliability		MTBF/MTTR					
<u> </u>	Nο	ise regulation	VCCI I/II, FCC A/B, VDE A/B				
  -							
Other	Applications						
		. of samples/mass products					
	⊔a	te of mass production					

### **Customized DC-DC converters**

# ■Customized DC-DC converters for microprocessors

These onboard DC-DC converters designed for microprocessors have been remarkably downsized through the use of metallic circuit boards. They feature a free choice of a precise output voltage in the 4.7-5.3V range by attaching an external resistor.




### **Characteristics (examples)**

	Item	Rated value		
	Input voltage	DC+5.0V (DC+4.75V~DC5.25V)		
Input	Inrush current	<del></del>		
lnp	Efficiency	80% min (with rated input)		
	Input current	5.5Amax. ( " )		
	Channels	ch 1		
	Output voltage	+4.7V~+5.3V variable (using an external resistor)		
	Permissible output	22wmax.		
	Permissible current range	1.0~4.5A		
Output	Ripple/noise 50mV/150mV p-p			
Out	Output voltage regulation ±50mV			
	Overvoltage protection +5.7~6.5V			
	Overcurrent protection Short circuit protection			
	Rise time	100msec. or less		
	Remote ON/OFF	<del></del>		
ons	Operating temp./humidity	0~+45°C, 5~95%RH (No dew deposit)		
Ambient conditions	Non-operating temp./humidity	-40~+75°C, 0~95%RH (No dew deposit)		
ient c	Vibration	5G, 5~500~5Hz/min., XYZ directions, 10 min. each		
Amb	Shock 50G, 11ms, XYZ directions, 3 times each			
sions	Dimensions	72 × 25.4 × 12.7mm		
, dimen	Construction	Open frame		
Construction, dimensions	Thermal radiation	Forced air cooling (conditions specified separately)		
Const	Connection method Lead frame (flow-soldering)			

# ■Customized DC-DC converters for switchboards

These onboard DC-DC converters for switchboards feature compatibility with plug-in cards and an impressively compact size through the use of metallic circuit boards. Their input voltage is 48V, while their output is either 5V or 3.3V with a 8.0A current.




### **Characteristics (examples)**

	Item	Rated value		
	Input voltage	DC+48V (DC+38.4~72V)		
Input	Inrush current			
dul	Efficiency	75%min.		
	Input current	0.86		
	Channels	ch 1		
	Output voltage	5V or 3.3V		
	Rated current	7.5A		
	Current range	0~7.5A		
Output	Ripple/noise 50mV/120mVP-P			
Ont	Total variation	±5%		
	Overvoltage protection	3.8~4.6V (shut down)		
	Overcurrent protection	8.5~11.0A (self-resumption)		
	Rise time	<del></del>		
	Isolation withstand voltage	Input-to-output, DC500V, 60 sec.		
ons	Operating temp./humidity	0~+70°C, 10~90%RH (No dew deposit)		
Ambient conditions	Non-operating temp./humidity	-40~+70°C, 0~95%RH (No dew deposit)		
ient o	Vibration	5G, 5~500~5Hz/min., XYZ directions, 10 min. each		
Amk	Shock	50G, 11ms, XYZ directions, 3 times each		
sions	Dimensions	56.5 × 55.9 × 13.0mm		
, dimer	Construction	Open frame		
Construction, dimensions	Thermal radiation	Forced air cooling (90m/min.)		
Const	Connection method Lead frame (flow-soldering)			

## ■Customized DC-DC converters for notebook PCs

Intended for use in notebook PCs, these DC-DC converters provide a constant output current for recharging the PC's batteries. A constant output voltage is supplied by the main superb 90% efficiency rating, thus ensuring stable PC operation by battery power.



### **Characteristics (examples)**

Item		Rated value								
	Input voltage	DC+	7.2V (DC+6.0~+1	7.0V)	DC+3.6V (D0	DC15V				
Input	Efficiency (type load)		90%min.		60%	70%min.				
	Input current	2.7A (t	ype input, type loa	d) min.						
	Output current	Constant voltage output (main)			Constant voltage	ge output (sub)	Constant current output			
	Channels	ch1	ch2	ch3	ch4	ch5	ch6			
	Output voltage	+5.0V	+3.3V	+12V	+5.0V	+3.3V	5~10V			
	Rated current	0.6A	0.65A	0.05A	0.01A	0.001A	0.35A			
	Current range	0.003~2.0A	0.005~2.0A	0.0001~0.06A	0.003~0.015A		0.32~0.38A			
Output	Ripple	100mVp-p	100mVp-p	100mVp-p	100mVp-p	100mVp-p	100mVp-p			
	Total variation	±0.25V	±0.2V	±0.6V	±0.3V	±0.3V				
	Overvoltage protection	~6.5V	~4.5V	~14.0V						
	Overcurrent protection	Short circuit protection	Short circuit protection	Short circuit protection			Short circuit protection			
	Rise time	15ms	15ms	50ms	10ms	10ms				
	Remote ON/OFF	Provided	Provided	Provided			Provided			
ons	Operating temp./humidity	0~+50°C, 10~80%RH (No dew deposit)								
Ambient conditions	Non-operating temp./humidity	-20~+70°C, 0~95%RH (No dew deposit)								
ient c	Vibration	0.5G, 10~100~10Hz/min. XYZ directions, 10 min. each								
Amb	Shock		50G, 11ms, XYZ directions, 3 times each							
sions	Dimensions		80 × 48 × 14mm							
, dimen	Construction		Open frame							
Construction, dimensions	Thermal radiation			Forced a	ir cooling					
Consti	Connection method		Lead frame (flow or manual soldering)							

# ■General-purpose compact DC-DC converters (MX Series)

These DC-DC converters, which are very flat with a height of only 8.5mm, are packed inside metallic casing in order to prevent radiation noise from affecting the surrounding components. Their floating input-output system allows both single- and dual-output options, and are usable without attaching any external components.




### **Characteristics (examples)**

Model No.	MX0505S250	MX0506S210	MX0512S120	MX0509S150	MX0505F100	MX0512F060	MX0515F050	MX1205S300	MX2405S300	MX4805S300
Input voltage			ı	DC4.5V~6.0\	V			DC10.0V~16.0V	DC20.0V~30.0V	DC36.0V~56.0V
Output voltage	5V	6V	12V	9V	±5V	±12V	±15V	5V	5V	5V
Overall regulation	±5%	±5%	±5%	±5%	±5% each	±5% each	±5% each	±5%	±5%	±5%
Output current	0-250mA	0-210mA	0-120mA	0-150mA	0-100mA	(0-60) mA × 2	(0-50) mA $\times$ 2	0-300mA	0-300mA	0-300mA
Output capacity	1.25W	1.25W	1.44W	1.35W	1.00W	1.44W	1.5W	1.5W	1.5W	1.5W
Ripple/noise	120mVp-p	120mVp-p	120mVp-p	120mVp-p	120mVp-p	120mVp-p	120mVp-p	120mVp-p	120mVp-p	120mVp-p
Overcurrent protection				Sho	rt protection	(self-resump	tion)			
Efficiency		60	00/		45%	60	10/	700/		
(Typ. input, Max. load)	62%				45%	62% 70%				
Isolation				Primar	y-to-seconda	ry, AC 500V	, 1 min.			
Shielding				Metall	ic casing, fiv	e-surface shi	elding			
Operating temperature			-1	0°C~+70°C	(see the dera	ating curve fo	r 50°C or ove	er)		
Non-operating temp.					−20°C	~+85°C				
Humidity				95%m	nax. (MAX we	et-bulb temp.	38°C)			
Dimensions					33×2	2×8.5				
			10Hz~	56.7Hz Vibra	ation 1.5mmP	mmP-P No abnormality after 1 min.				
Vibration	56.8Hz~350Hz 10G intermittent vibrations for									
	351Hz~500Hz 20				00Hz 2G 2 2 hr. in each of XYZ directions					
Shock		100G, 6msec, XYZ directions, 3 times each								
Weight		15g								

Made to order

### **Derating curve**




### **Precautions**


- 1. The ripple and noise contained in the input voltage must not exceed +1%p-p of the rated input voltage.
- 2. Do not connect the output of the DC-DC converters in parallel to boost the output current or for any other purpose.
- 3. Because these DC-DC converters are packed in metallic casings, they should be insulated from the surrounding components and patterns.
- 4. We recommend that our customers install a protective fuse in the input line of their equipment.

### **Connection diagram**


(1) Single-output type



### (2) Dual-output type



### **Shape and dimensions**



### **■**How to order customized DC-DC converters

FDK always stand ready to receive orders for customdesign DC-DC converters. When placing orders, please enter your desired design in the specification table below.

### **Setting specifications**

		Input voltage	□V ±□% (V)								
		Efficiency	□%min.								
	ont	Output voltage	$\Box V$	□V	□V	□V	□V	□V	□V		
	Rated output	Output current	□A	□A	□A	□A	□A	□A	□A		
stics	ited	Voltage regulation	□%	□%	□%	□%	□%	□%	□%		
teri	Ra	Voltage variable range	□%	□%	□%	□%	□%	□%	□%		
Electrical characteristics		Ripple/noise voltage	$\Box$ V	□V	□V	□V	□V	□V	□V		
ıl ch		Spike noise voltage	$\Box$ V	□V	□V	□V	□V	□V	□V		
trica	Protection	Overvoltage protection									
∃lec		Overcurrent protection									
	Added function	Output sequence									
	Add	Remote control	None 2. As per attached paper								
	solation	Withstand voltage	□V AC/DC, 1 min.								
	Isola	Isolation resistance	V DC MΩmin. at leak current mA max.								
9	Operating temp./humidity		□°C~ □°C/ □%~→□%RH								
enc	Non-operating temp./humidity		□°C~ □°C/ □%~→□%RH								
Ambience	Cooling Method		<ol> <li>Natural Cooling</li> <li>Forced cooling</li> <li>Window direction</li> <li>Wind volume</li></ol>								
ti- ition	Vibration		□Hz~□Hz, □G/mm, □hr.								
Anti- vibration		Shock	☐m sec., ☐G, ☐times								
		Weight	□kg max.								
Construction	Dimensions		$\square$ cm $\times$ $\square$ cm								
stru	Installation area/position										
Con	Casing		Encased, None								
		Casing material									
١,		Applications									
Other	Nos	. of samples/mass products									
	Da	ate of mass production									

<sup>\*</sup> Please feel free to consult us for delivery of DC-DC converters in a very short period.

### **Precautions Before Use**

Switching power supplies and DC-DC converters are designed generally as components to be incorporated into equipment. FDK therefore recommends the use of its power supplies and DC-DC converters as components to be safely installed in relation to other components inside the host equipment.

### Safety

1. Rated input voltage A suitable input voltage range is designated for each model.

To prevent breakdown and other hazards, do not apply a voltage outside this range to power supplies and DC-DC converters; also, do not apply an inverse voltage to DC-DC converters.

2. Leakage current A leakage current within a designated safety limit flows in each power supply.

When more than one power supplies are used in the same system, their leakage currents are added on. The combined leakage current must not

exceed safety levels.

3. Grounding To prevent electric shocks and noise interferences, connect the grounding

terminal of the switching power supply or DC-DC converter with the host

equipment body, using a thick and short wire.

4. Wiring For the wiring of the switching power supply in the host equipment, use thick

wires that match the rated input and output currents of the power supply.

5. When the fuse has blown In most cases, the blowning of the fuse is accompanied by the breakdown of

an internal circuit. Because just replacing the fuse will not be sufficient, contact

FDK for repair.

6. Watch out for high voltage Each switching power supply has high-voltage areas inside. To avoid an

electric shock, do not touch it by bare hand.

### Operating environment

7. Temperature The service life of a power supply varies widely according to its ambient

temperature. For a longer life, keep the temperature inside the host equipment as low as possible. Users who operate power supplies continuously for a long

time are advised to overhaul their power supplies at intervals.

8. Water and humidity To prevent the breakdown of a circuit inside the power supply, do not operate in

an environment where the power supply is liable to be wetted by splash water

or by dew.

9. Dust The use of a power supply or a DC-DC converter often results in the

breakdown of the fan and/or the shorting of an internal circuit. For operation in

a dusty environment, take a dust blocking step.

10. Vibration and shock In case of using a power supply or a DC-DC converter in an environment with

continual vibrations and physical shocks, take an impact absorbing step.



### **FDK CORPORATION**

#### **Electronics sales Div.**

5-36-11, Shinbashi, Minato-ku, Tokyo 105-8677, Japan (Hamagomu Bldg.) TEL: (81)-3-5473-4673 FAX: (81)-3-3431-9436

#### U.S.A. FDK AMERICA, INC. CORPORATE OFFICE

2270 North First Street, San Jose, California 95131-2022, U.S.A.

TEL: (1)-408-432-8331 FAX: (1)-408-435-7478

#### FDK AMERICA, INC. BOSTON OFFICE

411 Waverley Oaks Road, Suite 324, Waltham, Massachusetts 02452-8437, U.S.A. TEL: (1)-781-899-7700 FAX: (1)-781-899-7701

#### FDK AMERICA, INC. SAN DIEGO OFFICE

6540 Lusk Blvd. Suite C274 San Diego, California 92121-2766, U.S.A. TEL: (1)-858-558-8368 FAX: (1)-858-558-6005

#### **Europe FDK ELECTRONICS GMBH**

Hansaallee 177C, 40549 Düsseldorf, Germany TEL: (49)-211-591574 FAX: (49)-211-593549

#### FDK ELECTRONICS UK LIMITED

Suite 4C Celect House 12A Fairbairn Road, Kirkton North Livingston EH54 6TS, Scotland, United Kingdom TEL: (44)-1506-467981 FAX: (44)-1506-467982

#### Asia FDK HONG KONG LTD.

Unit 18. 15/F., Chevalier Commercial Centre, 8 Wang Hoi Road, Kowloon Bay, Hong Kong

TEL: (852)-27999773 FAX: (852)-27554635

#### FDK SINGAPORE PTE., LTD.

4, Leng Kee Road, #06-07/08 SiS Building, Singapore. 159088, Republic of Singapore

TEL: (65)-472-2328 FAX: (65)-472-5761