

Datasheet for 76650-0086

General Information

Part Number:	76650-0086
Manufacturer:	Molex / Waldom
Title:	Mini-Fit Jr. Connector Kit
Description:	Vertical Header and Receptacle, 10 Circuit
Product Family:	Mini-Fit Jr.™
Certificates:	(Molex parts within this kit) - EU and China RoHS, UL, CSA and TUV
Country of Origin:	Kit assembled in U.S.A.

Specifications

Design	
Configuration:	Wire-to-Board
Pitch:	4.2mm (.165")
Connector Type:	Receptacles and Vertical Headers
Mounting	
Orientation:	Vertical
Circuit Sizes:	10
Current Rating:	6 Amps
Voltage:	600 Volts
Wire size:	24-18 AWG

Product Highlights

The Mini-Fit Jr. Series is designed for high current/high density applications. The Mini-Fit Jr. is appropriate for both power and signal applications. The Mini-Fit product family accepts the same terminals and application tooling, further reducing your design and qualification effort.

Features and Benefits

- Fully isolated terminals
- Positive housing locks
- Four point of contact for reliability
- Low engagement force terminals

Applications

- Security and Alarms
- Vending and Gaming Machines
- White Goods
- Production Equipment
- Broadcast Equipment
- Telecom Infrastructure

Datasheet for 76650-0086

Bill of Materials for Part No. 76650-0086

Molex Part No.	Country of Origin	Description	Quantity in Kit
39-00-0039	USA	Crimp Type Female Socket Terminals, 24-18 AWG	10
39-01-2100	USA	10 Circuit Free Hanging Receptacle, 4.20mm (.165") Pitch	1
39-28-1103	Mexico	10 Circuit Dual Row Vertical Header without Pegs	1

Recommended Molex Tool(s) for Part No. 76650-0086*

Molex Part No.	Country of Origin	Description
63819-0900 *	Sweden	Hand Crimp Tool
11-03-0044 *	Sweden	Extraction Tool

*Tool(s) not included in kit. Tool(s) ordered separately.