


PART NO SEE NOTE 3	PLATING
71363-102 71363-102LF	0.38um/15u" GOLD OR GXT ON CONTACT AREA OVER 1.27um/50u" Ni (SEE NOTE 7)
71363-202 71363-202LF	0.76um/30u" GOLD OR GXT ON CONTACT OVER 1.27um/50u" Ni (SEE NOTE 7)
71363-302 71363-302LF	2.54um/100u" MATTE TIN PLATING



NOTE:

1. MATERIAL

HOUSING : 30% GLASS FILLED POLYESTER
FLAME RETARDANT PER UL 94V-0
COLOR : BLACK

2. TERMINAL : PHOSPHOR BRONZE

PLATING : REFER TO CHART

③ PRODUCT DESCRIPTION CODE:

XXXXX - XXXLF

LEAD FREE (SEE NOTE 4 & 6)
EXTENSION NUMBER
CONTACT AREA PLATING
BASE NUMBER



④ 71363-XXXLF IS THE SAME AS 71363-XXX.
SUFFIX 'LF' IS ADDED FOR EASY LEAD FREE IDENTIFICATION.

5. THE HOUSING WILL WITHSTAND EXPOSURE TO 200°C PEAK
TEMPERATURE FOR 10 SECONDS IN A CONVECTION, INFRA-RED
OR VAPOR PHASE REFLOW OVEN.

⑥ THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER
COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.

7. PLATING OPTION:

MAY BE EITHER GOLD OR GXT PLATED AT MANUFACTURER'S OPTION.



spec ref	-	dr	Louis Ng	2010/10/11	projection	MM	size	A3	scale	6:1
tolerance std	ISO 406 ISO 1101	eng	Guo-Min Sun	2013/05/15	chr	-	ecn no	ELX-N-14400-1	rel level	Released
surface	✓	appr	Rick Bian	2013/05/26	product family	JUMPER	dwg no	71363	rev	K
linear	0.X ±0.35 0.XX ±0.25 0.XXX ±0.10	angular	0° ±2°	www.fci.com	cat. no.	-	Product - Customer Drw	sheet 1 of 1		