

Jumpers

for 0.6-0.64 mm wire wrap pins and Ø 0.6-0.7 mm

| art. no.         | no. of contacts | surface     | version                                  | grid |  |  |  |
|------------------|-----------------|-------------|------------------------------------------|------|--|--|--|
| CAB 4 G ...      | 2               | 0,1 μm gold | closed                                   | 2.54 |  |  |  |
| CAB 4 Z ...      | 2               | 5,0 μm tin  | closed                                   | 2.54 |  |  |  |
|                  |                 |             |                                          |      |  |  |  |
| CAB 5 05 G ...   | 2               | 0,5 μm gold | closed, hole for probe trip              | 5.08 |  |  |  |
| CAB 5 10 G ...   | 2               | 1,0 μm gold | closed, hole for probe trip              | 5.08 |  |  |  |
| CAB 5 Z ...      | 2               | 5,0 μm tin  | closed, hole for probe trip              | 5.08 |  |  |  |
|                  |                 |             |                                          |      |  |  |  |
| CAB 6 05 G ...   | 2               | 0,5 μm gold | open, suitable for miniature test probes | 2.54 |  |  |  |
| CAB 6 10 G ...   | 2               | 1,0 μm gold | open, suitable for miniature test probes | 2.54 |  |  |  |
| CAB 6 Z ...      | 2               | 5,0 μm tin  | open, suitable for miniature test probes | 2.54 |  |  |  |
|                  |                 |             |                                          |      |  |  |  |
| CAB 7 G ...      | 2               | 0,1 μm gold | engageable, closed                       | 2.54 |  |  |  |
| CAB 7 Z ...      | 2               | 5,0 μm tin  | engageable, closed                       | 2.54 |  |  |  |
|                  |                 |             |                                          |      |  |  |  |
| CAB 9 G ...      | 2               | 0,1 μm gold | tag, open                                | 2.54 |  |  |  |
| please indicate: |                 |             |                                          |      |  |  |  |

Colour "grey" except for CAB 9.

The flexible contacts are shorting two pins. The jumpers can be mounted behind and next to each other.

Male headers .1" SMD  
Male headers .1" solder  
Male headers .1" press-fit  
Male headers .079" SMD

→ G 35 - 39  
→ G 8 - 18  
→ G 45 - 46  
→ G 55 - 57

Male headers .079" solder  
Technical data  
Special male & female headers  
Jump. links .079" & .1" solder

→ G 51 - 53  
→ G 72 - 76  
→ G 19  
→ G 20

G 70

A

B

C

D

E

F

G

H

I

K

L

M

N