

© COPYRIGHT 1974 BY AMP INCORPORATED, HARRISBURG, PA.
ALL INTERNATIONAL RIGHTS RESERVED. AMP INCORPORATED PRODUCTS
COVERED BY U. S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.





3

2

1

Loc DIST
AA 20

REVISIONS				DATE	APPROVED
P	F	ZONE	LTR	DESCRIPTION	
H	V		H	-1 SUPERSEDED BY 2/1: EEN AA-4739	8/5/80 X5



1. THE CONTACT SURFACES OF THE TERMINALS ARE COATED WITH LUBRICANT.
2. ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY UNLESS OTHERWISE SPECIFIED.
3. MATERIAL: HOUSING - THERMOPLASTIC (BLK) TERMINALS - GOLD OVER NICKEL PLATED HIGH STRENGTH COPPER ALLOY.

4. WIRE SIZE: 26-27-28 AWG 7 STRANDS OF COPPER CONDUCTORS. MAX INSULATION DIA OF .045 IS ACCEPTABLE FOR MOST APPLICATIONS.
- △ COATING MAY OR MAY NOT APPEAR AND IS AT THE DISCRETION OF AMP INCORPORATED.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS ± .001 ANGLES ± .1°		CONTRACT NO		NAME	
MATERIAL		DR 1-2-80		AMP INCORPORATED Harrisburg, Pa.	
FINISH		CHK 1/3/80		ASSY, RCPT, 24 POSN, E SLOT (CHAMP-LOK, W/.187 DIA HOLES)	
APPD 8.6.27/80 1/1/80		APPD 1/3/80		SIZE CODE IDENT NO DRAWING NO	
DSGN APPD		OTHER APPD		C 00779 552474	
SCALE 2/1		SHEET 1 OF 1			