






THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION						
© COPYRIGHT — By —				ALL RIGHTS RESERVED.						
PART NO.	POS NO.	A	B	C	D	E	F	G	DATUM MARK 	TOOLING STATUS
2069716-3	40	19.5	21.3	26.25	24.47	24.3	20.6	28.2	WITHOUT DATUM MARK	AVAILABLE
2069716-2	30	14.5	16.3	21.25	19.47	19.3	15.6	23.2		NOT AVAILABLE
2069716-1	20	9.5	11.3	16.25	14.47	14.3	10.6	18.2		NOT AVAILABLE
5-2069716-3	40	19.5	21.3	26.25	24.47	24.3	20.6	28.2	WITH DATUM MARK	OBSOLETE
5-2069716-2	30	14.5	16.3	21.25	19.47	19.3	15.6	23.2		OBSOLETE
5-2069716-1	20	9.5	11.3	16.25	14.47	14.3	10.6	18.2		NOT AVAILABLE

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	REVISED (ECR-17-011570)	16AUG2017	C.H	A.K


5-2069716-3 AS SHOWN

H-H
(SCALE 10:1)MATED CONDITION
(REFERENCE)

- ① SOLDERING AREA
② RESIST OR GND AREA
③ PULL BAR MOVEMENT AREA
④ THE CONNECTOR SHOULD BE PLUGGED WITH 2069715-3.
5. COPLANARITY 0.1MAX
⑥ DATUM MARK
7. INSTRUCTION SHEET 411-78355



REFERENCE PWB LAYOUT



MATED CONDITION

③	SHELL	COPPER ALLOY, Au OVER Ni
②	CONTACT	COPPER ALLOY, Au OVER Ni
①	HOUSING	HIGH TEMP. THERMOPLASTIC, UL94V-0, BLACK
ITEM	PART NAME	MATERIAL & FINISH

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN Y.SHINO 18SEP2009			
DIMENSIONS: mm				CHK S.KAJINUMA 18SEP2009			
TOLERANCES UNLESS OTHERWISE SPECIFIED:				APVD S.KAJINUMA 18SEP2009			
0 RLC ± -				NAME			
1 PLC ± - ±0.2				PRODUCT SPEC			
2 PLC ± - ±0.2				108-78659			
3 PLC ± - ±2°				APPLICATION SPEC			
4 PLC ± - ± -				SIZE			
ANGLES ± -				CAGE CODE			
FINISH ± -				DRAWING NO			
MATERIAL				RESTRICTED TO			
				A300779C-2069716			
				CUSTOMER DRAWING			
				SCALE 5:1			
				SHEET 1 OF 2			
				REV B			

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

- , - .


© COPYRIGHT - By - ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-


EMBOSS PACKING CONDITION

DIRECTION OF TOP OF REEL




K-K


DETAIL L



J-J
SCALE 5:1




DETAIL L
SCALE 10:1



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



MATERIAL

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± 0.3
1 PLC ± 0.3
2 PLC ± 0.3
3 PLC ± 0.3
4 PLC ± 0.3
ANGLES ± 3°
FINISH

DWN	-
CHK	-
APVD	-
PRODUCT SPEC	-
APPLICATION SPEC	-
WEIGHT	-
CUSTOMER DRAWING	-



TE Connectivity

NAME
LCD COAXIAL EMBEDDED DISPLAY INTERFACE
(LCEDI) 0.5mm PITCH CONNECTOR
RECEPTACLE ASSEMBLY

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-2069716	-

SCALE 2:1 SHEET 2 of 2 REV B