



20 19 18 17 16 15 14 13 12 11 10 9 8 7 6 5 4 3 2 1




CARRIER VIEW




NOTES:

1. MATERIAL:
(0.20)/.008 THICK BRASS
2. FINISH:
122 - OVERALL TIN: (0.00381)/.000150 MIN. TIN OVER
(0.00076)/.000030 MIN NICKEL
154 - OVERALL TIN: (0.00254)/.000100 MIN. TIN OVER
(0.00127)/.000050 MIN NICKEL
P909 - OVERALL HOT TIN DIP: (0.00254)/.000100 MIN.
550 - SELECT GOLD: (0.000381)/.000015 MIN.
OVERALL GOLD FLASH: (0.00005)/.000002 MIN.
OVERALL NICKEL UNDERPLATE: (0.00076)/.000030 MIN.
555- SELECT GOLD (0.000381)/.000015 MIN.
OVERALL NICKEL UNDERPLATE: (0.00076)/.000030
558 - SELECT GOLD: (0.00076)/.000030 MIN.
OVERALL GOLD FLASH: (0.00005)/.000002 MIN.
OVERALL NICKEL UNDERPLATE: (0.00127)/.000050 MIN.
3. PRODUCT SPEC: PS-10-07
4. PACKAGING SPECIFICATION: LOOSE TERMINALS: PER PK-2759-001
CHAIN FORM TERMINALS: PER PK-2759-002
5. CRIMP IS FOR 22-30 GA WIRE WITH (1.57)/.062 DIA INSULATION MAX.
6. INSERTION FORCE OF TERMINAL INTO (2.54)/.100 CENTERLINE CONNECTOR IS 2.5 LBS. MAX
7. TERMINAL RETENTION IN HOUSING IS 26.7N / 6LBS MIN. WHEN PULLED AT THE RATE OF (25.4MM) / 1 INCH PER MINUTE.
8. DIMENSIONS GIVEN ACROSS CENTERLINES ARE SYMMETRICAL ABOUT THOSE CENTERLINES WITHIN HALF THE TOTAL TOLERANCE.
9. THIS PART CONFORMS TO CLASS B REQUIREMENTS OF COSMETIC SPECIFICATION PS-45499-002.


SELECT GOLD LOCATION



CRIMP DETAIL



CRIMPED TERMINAL 2759-(P909)C IS USED WITHOUT WIRE AND IS INSERTED INTO HOUSING TO PROVIDE TENSION WHEN ASSEMBLED TO HEADERS DURING SHIPMENT.



SECTION A-A
BACKGROUND OMITTED

SECTION B-B
BACKGROUND OMITTED

2759-(***)*

FORM

L=LOOSE

C=LOOSE CRIMPED

A=CHAIN, PER WINDING DETAIL "A"

B=CHAIN, PER WINDING DETAIL "B"

PLATING


SEE NOTE 2

ADD WINDING DETAIL EC NO: UCP2014-4131 DRAWN BY: CHYONGKUN 2014/04/08 APPROVED BY: FSMTH 2014/04/21	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE	DESIGN UNITS INCH	 THIRD ANGLE PROJECTION
		mm INCH		DRAWN BY	DATE	TITLE		
		4 PLACES ±--- ±---		SMIEC	07/28/87	CRIMP TERMINAL		
		3 PLACES ±--- ±.010		CHECKED BY	DATE	22-30 GA WIRE		
		2 PLACES ±0.25 ±.014		PAEEL	07/28/87	molex		
		1 PLACE ±0.36 ±---		APPROVED BY	DATE	DOCUMENT NO.		
		0 PLACE ±--- ±---		FSMTH	2012/03/20	SD-2759		SHEET NO.
		ANGULAR ±1/2°		MATERIAL NO.				1 OF 2
		DRAFT WHERE APPLICABLE		SEE CHART				
		MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				


20 19 18 17 16 15 14 13 12 11 10 9 8 7 6 5 4 3 2 1

2759-(***)*		
	PART NO.	ENG. NO.
	08-55-0101	2759-(555)B
	08-55-0102	2759-(555)L
	08-55-0126	2759-(555)A
	08-56-0109	2759-(550)B
	08-56-0110	2759-(550)L
	08-50-0113	2759-(P909)B
	08-50-0114	2759-(P909)L
	08-50-0124	2759-(P909)C
	08-51-0108	2759-(122)B
		2759-(122)L
	08-50-0274	2759-(P909)B
	08-50-0273	2759-(P909)A
	08-55-0130	2759-(558)B
	08-55-0131	2759-(558)L
	08-50-0160	2759-(154)L
	08-50-0159	2759-(154)B

WINDING DETAIL "A"



WINDING DETAIL "B"



SEE SHEET 1 SEC NO. UCP2014-431 DRAWN BY: IPFER 2014/04/08 CHKD BY: NGUYEN 2014/04/08 APPROVED BY: FSMITH 2014/04/21 REV	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	 THIRD ANGLE PROJECTION		
					MM/IN		1:1	INCH			
					DRAWN BY	DATE	TITLE				
					SAMEKH	07/28/87					
					CHECKED BY	DATE	CRIMP TERMINAL 22-30 GA WIRE				
					PATEL	07/28/87					
					APPROVED BY	DATE	molex				
					FSMITH	2012/03/20					
					MATERIAL NO.		DOCUMENT NO.			SHEET NO.	
					SEE CHART		SD-2759			2 OF 2	
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							

19 18 17 16 15 14 13 12 11 10 9 8 7 6 5 4 3 2 1