3 Amp Schottky Rectifier

MSP345



Dim.	Inches		Millimeter		
	Minimum	Maximum	Minimum	Maximum	Notes
A	.188	.260	4.78	6.50	Dia.
B	1.00	---	25.4	---	
C	.285	.375	7.24	9.52	
D	.046	.056	1.17	1.42	Dia.

PLASTIC D0201AD

Microsemi Catalog Number	Working Peak Reverse Voltage	Repetitive Peak Reverse Voltage
MSP345	45V	45V

- Schottky Barrier Rectifier
- Guard Ring Protection
- Low Forward Voltage
- 150°C Junction Temperature

Electrical Characteristics

Average forward current	$I_{F(AV)}$ 3.0 Amps	T_L = 82°C, Square wave, $R_{\theta JL}$ = 18°C/W, L = 3/8"
Maximum surge current	I_{FSM} 150 Amps	8.3ms, half sine, T_J = 150°C
Max peak forward voltage	V_{FM} .52 Volts	I_{FM} = 3.0A; T_J = 25°C*
Max peak reverse current	I_{RM} 1.5 mA	V_{RRM}, T_J = 25°C
Typical junction capacitance	C_J 265 pF	V_R = 5.0V, T_J = 25°C

*Pulse test: Pulse width 300 μsec, Duty cycle 2%

Thermal and Mechanical Characteristics

Storage temperature range	T_{STG}	−55°C to 175°C
Operating junction temp range	T_J	−55°C to 150°C
Maximum thermal resistance L = 3/8"	$R_{\theta JL}$	18°C/W Junction to lead
Weight		.032 ounces (1.0 grams) typical

SCOTTSDALE Microsemi
8700 East Thomas Road, P.O. Box 1390
Scottsdale, AZ 85252
PH: (480) 941-6300
FAX: (480) 947-1503
www.microsemi.com

05-25-07 Rev. 3

MSP345

Figure 1
Typical Forward Characteristics



Figure 2
Typical Reverse Characteristics



Figure 3
Typical Junction Capacitance