


**MCT2  
MCT2200**

**MCT2E  
MCT2201**


**MCT210  
MCT2202**

**MCT271**

## WHITE PACKAGE (-M SUFFIX)



## BLACK PACKAGE (NO -M SUFFIX)



## DESCRIPTION

The MCT2XXX series optoisolators consist of a gallium arsenide infrared emitting diode driving a silicon phototransistor in a 6-pin dual in-line package.


## FEATURES

- UL recognized (File # E90700)
- VDE recognized (File # 94766)
  - Add option V for white package (e.g., MCT2V-M)
  - Add option 300 for black package (e.g., MCT2.300)
- MCT2 and MCT2E are also available in white package by specifying -M suffix, eg. MCT2-M

## APPLICATIONS

- Power supply regulators
- Digital logic inputs
- Microprocessor inputs

## SCHEMATIC



PIN 1. ANODE  
2. CATHODE  
3. NO CONNECTION  
4. EMITTER  
5. COLLECTOR  
6. BASE

**MCT2**  
**MCT2200**

**MCT2E**  
**MCT2201**

**MCT210**  
**MCT2202**

**MCT271**

## ABSOLUTE MAXIMUM RATINGS

| Parameter                                                   | Symbol    | Device | Value          | Units |
|-------------------------------------------------------------|-----------|--------|----------------|-------|
| <b>TOTAL DEVICE</b><br>Storage Temperature                  | $T_{STG}$ | ALL    | -55 to +150    | °C    |
| Operating Temperature                                       | $T_{OPR}$ | ALL    | -55 to +100    | °C    |
| Lead Solder Temperature                                     | $T_{SOL}$ | ALL    | 260 for 10 sec | °C    |
| Total Device Power Dissipation @ $T_A = 25^{\circ}\text{C}$ | $P_D$     | -M     | 250            | mW    |
|                                                             |           | Non-M  | 260            |       |
| Derate above $25^{\circ}\text{C}$                           |           | -M     | 2.94           | mW/°C |
|                                                             |           | Non-M  | 3.3            |       |
| <b>EMITTER</b><br>DC/Average Forward Input Current          | $I_F$     | -M     | 60             | mA    |
|                                                             |           | Non-M  | 100            |       |
| Reverse Input Voltage                                       | $V_R$     | ALL    | 3              | V     |
| Forward Current - Peak (300 $\mu\text{s}$ , 2% Duty Cycle)  | $I_F(pk)$ | ALL    | 3              | A     |
| LED Power Dissipation @ $T_A = 25^{\circ}\text{C}$          | $P_D$     | -M     | 120            | mW    |
|                                                             |           | Non-M  | 150            |       |
| Derate above $25^{\circ}\text{C}$                           |           | -M     | 1.41           | mW/°C |
|                                                             |           | Non-M  | 2.0            |       |
| <b>DETECTOR</b><br>Collector Current                        | $I_C$     | ALL    | 50             | mA    |
| Collector-Emitter Voltage                                   | $V_{CEO}$ | ALL    | 30             | V     |
| Detector Power Dissipation @ $T_A = 25^{\circ}\text{C}$     | $P_D$     | ALL    | 150            | mW    |
| Derate above $25^{\circ}\text{C}$                           |           | -M     | 1.76           | mW/°C |
|                                                             |           | Non-M  | 2.0            |       |

**MCT2**  
**MCT2200**

**MCT2E**  
**MCT2201**

**MCT210**  
**MCT2202**

**MCT271**

**ELECTRICAL CHARACTERISTICS** ( $T_A = 25^\circ\text{C}$  Unless otherwise specified.)

**Individual Component Characteristics**

| Parameter                           | Test Conditions                                   | Symbol            | Device                                                         | Min | Typ** | Max  | Unit |
|-------------------------------------|---------------------------------------------------|-------------------|----------------------------------------------------------------|-----|-------|------|------|
| <b>EMITTER</b>                      |                                                   |                   |                                                                |     |       |      |      |
| Input Forward Voltage               | (I <sub>F</sub> = 20 mA)                          | V <sub>F</sub>    | MCT2/-M<br>MCT2E/-M<br>MCT271<br>MCT2200<br>MCT2201<br>MCT2202 |     | 1.25  | 1.50 | V    |
|                                     | (T <sub>A</sub> = 0-70°C, I <sub>F</sub> = 40 mA) |                   | MCT210                                                         |     | 1.33  |      |      |
| Reverse Leakage Current             | (V <sub>R</sub> = 3.0 V)                          | I <sub>R</sub>    | MCT2/-M<br>MCT2E/-M<br>MCT271<br>MCT2200<br>MCT2201<br>MCT2202 |     | 0.001 | 10   | μA   |
|                                     | (T <sub>A</sub> = 0-70°C, V <sub>R</sub> = 6.0 V) |                   | MCT210                                                         |     |       |      |      |
| <b>DETECTOR</b>                     |                                                   |                   |                                                                |     |       |      |      |
| Collector-Emitter Breakdown Voltage | (I <sub>C</sub> = 1.0 mA, I <sub>F</sub> = 0)     | BV <sub>CEO</sub> | ALL                                                            | 30  | 100   |      | V    |
|                                     | (T <sub>A</sub> = 0-70°C)                         |                   | MCT210                                                         |     |       |      |      |
| Collector-Base Breakdown Voltage    | (I <sub>C</sub> = 10 μA, I <sub>F</sub> = 0)      | BV <sub>CBO</sub> | MCT2/-M<br>MCT2E/-M<br>MCT271<br>MCT2200<br>MCT2201<br>MCT2202 | 70  | 120   |      | V    |
|                                     | (T <sub>A</sub> = 0-70°C)                         |                   | MCT210                                                         | 30  |       |      |      |
| Emitter-Collector Breakdown Voltage | (I <sub>E</sub> = 100 μA, I <sub>F</sub> = 0)     | BV <sub>ECO</sub> | MCT2/-M<br>MCT2E/-M<br>MCT271<br>MCT2200<br>MCT2201<br>MCT2202 | 7   | 10    |      | V    |
|                                     | (T <sub>A</sub> = 0-70°C)                         |                   | MCT210                                                         | 6   | 10    |      |      |
| Collector-Emitter Dark Current      | (V <sub>CE</sub> = 10 V, I <sub>F</sub> = 0)      | I <sub>CEO</sub>  | ALL                                                            |     | 1     | 50   | nA   |
|                                     | (V <sub>CE</sub> = 5 V, T <sub>A</sub> = 0-70°C)  |                   |                                                                |     |       | 30   | μA   |
| Collector-Base Dark Current         | (V <sub>CB</sub> = 10 V, I <sub>F</sub> = 0)      | I <sub>CBO</sub>  | ALL                                                            |     |       | 20   | nA   |
| Capacitance                         | (V <sub>CE</sub> = 0 V, f = 1 MHz)                | C <sub>CE</sub>   | ALL                                                            |     | 8     |      | pF   |

\*\* Typical values at  $T_A = 25^\circ\text{C}$

**MCT2**  
**MCT2200**

**MCT2E**  
**MCT2201**

**MCT210**  
**MCT2202**

**MCT271**

**TRANSFER CHARACTERISTICS** ( $T_A = 25^\circ\text{C}$  Unless otherwise specified.)

| DC Characteristic                                                                        | Test Conditions                                                                                               | Symbol                | Device                                       | Min | Typ** | Max | Unit |
|------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------|-----------------------|----------------------------------------------|-----|-------|-----|------|
| Output Collector Current                                                                 | (T <sub>A</sub> = 0-70°C)                                                                                     | CTR                   | MCT210                                       | 150 |       |     | %    |
|                                                                                          | (I <sub>F</sub> = 10 mA, V <sub>CE</sub> = 5 V)                                                               |                       | MCT2200                                      | 20  |       |     |      |
|                                                                                          |                                                                                                               |                       | MCT2201                                      | 100 |       |     |      |
|                                                                                          |                                                                                                               |                       | MCT2202                                      | 63  |       | 125 |      |
|                                                                                          | (I <sub>F</sub> = 10 mA, V <sub>CE</sub> = 10 V)                                                              |                       | MCT2<br>MCT2-M<br>MCT2E<br>MCT2E-M           | 20  |       |     |      |
|                                                                                          |                                                                                                               |                       | MCT271                                       | 45  |       | 90  |      |
| (I <sub>F</sub> = 3.2 mA to 32 mA, V <sub>CE</sub> = 0.4 V)<br>(T <sub>A</sub> = 0-70°C) | MCT210                                                                                                        | 50                    |                                              |     |       |     |      |
| Collector-Emitter Saturation Voltage                                                     | (I <sub>C</sub> = 2 mA, I <sub>F</sub> = 16 mA)                                                               | V <sub>CE (SAT)</sub> | MCT2<br>MCT2-M<br>MCT2E<br>MCT2E-M<br>MCT271 |     |       | 0.4 | V    |
|                                                                                          | MCT210                                                                                                        |                       |                                              |     |       |     |      |
|                                                                                          | MCT2200<br>MCT2201<br>MCT2202                                                                                 |                       |                                              |     |       |     |      |
| AC Characteristic Saturated Turn-on Time from 5 V to 0.8 V                               | (I <sub>F</sub> = 15 mA, V <sub>CC</sub> = 5 V, R <sub>L</sub> = 2 kΩ)<br>(R <sub>B</sub> = Open) (Fig. 20)   | t <sub>on</sub>       | MCT2                                         |     | 1.1   |     | μs   |
|                                                                                          | (I <sub>F</sub> = 20 mA, V <sub>CC</sub> = 5 V, R <sub>L</sub> = 2 kΩ)<br>(R <sub>B</sub> = 100 kΩ) (Fig. 20) |                       | MCT2E                                        |     | 1.1   |     |      |
|                                                                                          |                                                                                                               |                       | MCT2                                         |     | 1.3   |     |      |
|                                                                                          | MCT2E                                                                                                         |                       |                                              | 1.3 |       |     |      |
| Saturated Turn-off Time from SAT to 2.0 V                                                | (I <sub>F</sub> = 15 mA, V <sub>CC</sub> = 5 V, R <sub>L</sub> = 2 kΩ)<br>(R <sub>B</sub> = Open) (Fig. 20)   | t <sub>off</sub>      | MCT2                                         |     | 50    |     |      |
|                                                                                          |                                                                                                               |                       | MCT2E                                        |     | 50    |     |      |
|                                                                                          | (I <sub>F</sub> = 20 mA, V <sub>CC</sub> = 5 V, R <sub>L</sub> = 2 kΩ)<br>(R <sub>B</sub> = 100 kΩ) (Fig. 20) |                       | MCT2                                         |     | 20    |     |      |
|                                                                                          |                                                                                                               |                       | MCT2E                                        |     | 20    |     |      |
| Turn-on Time                                                                             | (I <sub>F</sub> = 10 mA, V <sub>CC</sub> = 10 V, R <sub>L</sub> = 100 Ω)                                      | t <sub>on</sub>       | MCT2-M<br>MCT2E-M                            |     | 2     |     |      |
| Turn-off Time                                                                            | (I <sub>F</sub> = 10 mA, V <sub>CC</sub> = 10 V, R <sub>L</sub> = 100 Ω)                                      | t <sub>off</sub>      | MCT2-M<br>MCT2E-M                            |     | 2     |     |      |
| Rise Time                                                                                | (I <sub>F</sub> = 10 mA, V <sub>CC</sub> = 10 V, R <sub>L</sub> = 100 Ω)                                      | t <sub>r</sub>        | MCT2-M<br>MCT2E-M                            |     | 2     |     |      |
| Fall Time                                                                                | (I <sub>F</sub> = 10 mA, V <sub>CC</sub> = 10 V, R <sub>L</sub> = 100 Ω)                                      | t <sub>f</sub>        | MCT2-M<br>MCT2E-M                            |     | 1.5   |     |      |

\*\* Typical values at  $T_A = 25^\circ\text{C}$

**MCT2**  
**MCT2200**

**MCT2E**  
**MCT2201**

**MCT210**  
**MCT2202**

**MCT271**

## TRANSFER CHARACTERISTICS (Cont.)

| AC Characteristic                                                           | Test Conditions                                                                     | Symbol                | Device                        | Min | Typ** | Max | Unit          |
|-----------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-----------------------|-------------------------------|-----|-------|-----|---------------|
| Saturated turn-on time                                                      | $(I_F = 16 \text{ mA}, R_L = 1.9\text{k}\Omega, V_{CC} = 5 \text{ V})$<br>(Fig. 20) | $t_{on}$              | MCT271                        |     | 1.0   |     | $\mu\text{s}$ |
| Saturated turn-off time<br>(Approximates a typical TTL interface)           |                                                                                     | $t_{off}$             |                               |     | 48    |     |               |
| Saturated turn-on time                                                      | $(I_F = 16 \text{ mA}, R_L = 4.7\text{k}\Omega, V_{CC} = 5 \text{ V})$<br>(Fig. 20) | $t_{on}$              |                               |     | 1.0   |     |               |
| Saturated turn-off time<br>(Approximates a typical low power TTL interface) |                                                                                     | $t_{off}$             |                               |     | 98    |     |               |
| Saturated rise time                                                         | $(I_F = 16 \text{ mA}, R_L = 560\Omega, V_{CC} = 5 \text{ V})$<br>(Fig. 20, 21)     | $t_r$                 | MCT210                        |     | 1.0   |     |               |
| Saturated fall time                                                         |                                                                                     | $t_f$                 |                               |     | 11    |     |               |
| Saturated propagation delay - high to low                                   | $(I_F = 16 \text{ mA}, R_L = 2.7\text{k}\Omega)$ (Fig. 20, 21)                      | $T_{PD} \text{ (HL)}$ |                               |     | 1.0   |     |               |
| Saturated propagation delay - low to high                                   |                                                                                     | $T_{PD} \text{ (LH)}$ |                               |     | 50    |     |               |
| Non-saturated turn on time                                                  | $(I_C = 2 \text{ mA}, V_{CC} = 10 \text{ V}, R_L = 100\Omega)$<br>(Fig. 20)         | $T_{ON}$              | MCT2200<br>MCT2201<br>MCT2202 |     | 2     | 10  |               |
| Non-saturated turn off time                                                 |                                                                                     | $T_{OFF}$             |                               |     | 2     | 10  |               |
| Non-saturated rise time                                                     | $(I_C = 2 \text{ mA}, V_{CC} = 5 \text{ V}, R_L = 100\Omega)$<br>(Fig. 20)          | $t_r$                 | MCT210                        |     | 2     |     |               |
| Non-saturated fall time                                                     |                                                                                     | $t_f$                 |                               |     | 2     |     |               |
| Non-saturated turn-on time                                                  | $(I_C = 2 \text{ mA}, V_{CC} = 5 \text{ V}, R_L = 100\Omega)$<br>(Fig. 20)          | $t_{on}$              | MCT271                        |     | 2     | 7   |               |
| Non-saturated turn-off time                                                 |                                                                                     | $t_{off}$             |                               |     | 2     | 7   |               |

\*\* Typical values at  $T_A = 25^\circ\text{C}$

## ISOLATION CHARACTERISTICS

| Characteristic                 | Test Conditions                                                      | Symbol    | Min       | Typ* | Max | Units    |
|--------------------------------|----------------------------------------------------------------------|-----------|-----------|------|-----|----------|
| Input-Output Isolation Voltage | (Non '-M', Black Package) ( $f = 60 \text{ Hz}, t = 1 \text{ min}$ ) | $V_{ISO}$ | 5300      |      |     | Vac(rms) |
|                                | (' -M', White Package) ( $f = 60 \text{ Hz}, t = 1 \text{ sec}$ )    |           | 7500      |      |     | Vac(pk)  |
| Isolation Resistance           | $(V_{I-O} = 500 \text{ VDC})$                                        | $R_{ISO}$ | $10^{11}$ |      |     | $\Omega$ |
| Isolation Capacitance          | $(V_{I-O} = \&, f = 1 \text{ MHz})$                                  | $C_{ISO}$ |           | 0.5  |     | pF       |
|                                | (' -M' White Package)                                                |           |           | 0.2  | 2   | pF       |

Note

\* Typical values at  $T_A = 25^\circ\text{C}$

**MCT2  
MCT2200**


**MCT2E  
MCT2201**

**MCT210  
MCT2202**


**MCT271**

**TYPICAL PERFORMANCE CURVES**


**Fig. 1 LED Forward Voltage vs. Forward Current  
(Black Package)**




**Fig. 2 LED Forward Voltage vs. Forward Current  
(White Package)**




**Fig.3 Normalized CTR vs. Forward Current  
(Black Package)**




**Fig.4 Normalized CTR vs. Forward Current  
(White Package)**



**Fig. 5 Normalized CTR vs. Ambient Temperature  
(Black Package)**



**Fig. 6 Normalized CTR vs. Ambient Temperature  
(White Package)**




**MCT2  
MCT2200**

**MCT2E  
MCT2201**


**MCT210  
MCT2202**

**MCT271**


**Fig. 7 CTR vs. RBE (Unsaturated)  
(Black Package)**




**Fig. 8 CTR vs. RBE (Unsaturated)  
(White Package)**




**Fig. 9 CTR vs. RBE (Saturated)  
(Black Package)**




**Fig. 10 CTR vs. RBE (Saturated)  
(White Package)**



**Fig. 11 Collector-Emitter Saturation Voltage vs. Collector Current  
(Black Package)**



**Fig. 12 Collector-Emitter Saturation Voltage vs. Collector Current  
(White Package)**




**MCT2**  
**MCT2200**

**MCT2E**  
**MCT2201**


**MCT210**  
**MCT2202**

**MCT271**


**Fig. 13 Switching Speed vs. Load Resistor**  
(Black Package)




**Fig. 14 Switching Speed vs. Load Resistor**  
(White Package)




**Fig. 15 Normalized  $t_{on}$  vs.  $R_{BE}$**   
(Black Package)




**Fig. 16 Normalized  $t_{on}$  vs.  $R_{BE}$**   
(White Package)



**Fig. 17 Normalized  $t_{off}$  vs.  $R_{BE}$**   
(Black Package)



**Fig. 18 Normalized  $t_{off}$  vs.  $R_{BE}$**   
(White Package)



**MCT2  
MCT2200**

**MCT2E  
MCT2201**

**MCT210  
MCT2202**

**MCT271**

Fig. 19 Dark Current vs. Ambient Temperature





Figure 20. Switching Time Test Circuit and Waveforms




Figure 21. Switching Time Waveforms (MCT210)

**MCT2  
MCT2200**


**MCT2E  
MCT2201**

**MCT210  
MCT2202**


**MCT271**

## Black Package (No -M Suffix)


### Package Dimensions (Through Hole)




### Package Dimensions (Surface Mount)



### Package Dimensions (0.4" Lead Spacing)



### Recommended Pad Layout for Surface Mount Leadform



## NOTE

All dimensions are in inches (millimeters)

**MCT2  
MCT2200**


**MCT2E  
MCT2201**

**MCT210  
MCT2202**


**MCT271**

## White Package (-M Suffix)


### Package Dimensions (Through Hole)




### Package Dimensions (Surface Mount)



### Package Dimensions (0.4" Lead Spacing)



### Recommended Pad Layout for Surface Mount Leadform



## NOTE

All dimensions are in inches (millimeters)

**MCT2**  
**MCT2200**

**MCT2E**  
**MCT2201**

**MCT210**  
**MCT2202**

**MCT271**

## ORDERING INFORMATION

| Order Entry Identifier    |                           |                                      |
|---------------------------|---------------------------|--------------------------------------|
| Black Package (No Suffix) | White Package (-M Suffix) | Description                          |
| .S                        | S                         | Surface Mount Lead Bend              |
| .SD                       | SR2                       | Surface Mount; Tape and reel         |
| .W                        | T                         | 0.4" Lead Spacing                    |
| .300                      | V                         | VDE 0884                             |
| .300W                     | TV                        | VDE 0884, 0.4" Lead Spacing          |
| .3S                       | SV                        | VDE 0884, Surface Mount              |
| .3SD                      | SR2V                      | VDE 0884, Surface Mount, Tape & Reel |

MCT271

[illegible]

---

**MCT2**  
**MCT2200**

**MCT2E**  
**MCT2201**

**MCT210**  
**MCT2202**

**MCT271**

---

## DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS.

## LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT OF FAIRCHILD SEMICONDUCTOR CORPORATION. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.