


5mm x 20mm FUSE HOLDERS

SLIM LINE



Mounting Detail

- Optional cover with window protects and insulates fuse
- Flame Retardant

CAT. NO. 4628 - Holder

CAT. NO. 4628C - Cover only (with window)

SPECIFICATIONS


Base & Cover: Nylon, UL Rated 94V-0

Clips: Brass, Tin Plate

Rated: 5 Amps @ 250V AC

Operating Temp. Range: -58°F to +292°F (-50°C to +145°C)

LOW PROFILE



Mounting Detail

- Low profile, space saving design
- Optional cover protects and insulates fuse
- Flame Retardant

CAT. NO. 4527 - Holder

CAT. NO. 4527C - Cover only

SPECIFICATIONS


Base & Cover: Nylon, UL Rated 94V-0

Clips: Brass, Tin Plate

Rated: 5 Amps @ 250V AC

Operating Temp. Range: -58°F to +292°F (-50°C to +145°C)

FULLY INSULATED



Mounting Detail

- Supplied unassembled
- Shock resistant
- Fuse can be accessed from board edge
- Fuse is completely enclosed, protecting use from shorting and breaking

CAT. NO. 4525

SPECIFICATIONS


Base: PBT

Contacts: Brass, Tin Plate

Rated: 10 Amps @ 250V AC

Operating Temp. Range: -58°F to +292°F (-50°C to +145°C)

PC SNAP-IN



Mounting Detail

- Snap-in design for wave soldering
- Flame Retardant
- Optional cover protects and insulates fuse - Cat. No. 3527C

CAT. NO. 3527 - Holder

SPECIFICATIONS

Base: .062 (1.57) G-10, UL Rated 94V-0


Clips: Brass, Tin Plate

Rated: 6.3 Amps @ 250V AC

Operating Temp. Range: -58°F to +292°F (-50°C to +145°C)

3AG FUSE HOLDERS

TERMINATION LUGS CAN BE USED WITH WIRES OR PC MOUNT



Mounting Detail

SPECIFICATIONS

Base: .062 (1.57) GPO-3, UL Rated 94V-0

Clips: Brass, Tin Plate


Rated: 15 Amps @ 500VAC

Operating Temp. Range: -58°F to +292°F (-50°C to +145°C)

CAT. NO. 3526

Optional cover available - Cat. No. 4245C

PRESS-FIT, IDEAL FOR WAVE SOLDERING



Mounting Detail

SPECIFICATIONS

Base: .062 (1.57) GPO-3, UL Rated 94V-0

Clips: Brass, Tin Plate


Rated: 15 Amps @ 500VAC

Operating Temp. Range: -58°F to +292°F (-50°C to +145°C)

CAT. NO. 4245

Optional cover available - Cat. No. 4245C

SNAP-IN DESIGN ASSURES STABILITY DURING WAVE SOLDERING



Mounting Detail

SPECIFICATIONS

Base: .032 (1.57) G-10, UL Rated 94V-0

Clips: Brass, Tin Plate


Rated: 15 Amps @ 500VAC

Operating Temp. Range: -58°F to +292°F (-50°C to +145°C)

CAT. NO. 4250

Optional cover available - Cat. No. 4245C

MOLDED BASE



SPECIFICATIONS

Base: LCP, UL Rated 94V-0

Clips: .020 (.51) Brass - Nickel Plated

Rated: 15 Amps @ 500 VAC

Operating Temp. Range: -58°F to +292°F (-50°C to +145°C)

CAT. NO. 3523

Optional cover available - Cat. No. 4245C