


SN54ALS2540, SN54ALS2541, SN74ALS2540, SN74ALS2541 OCTAL LINE DRIVERS/MOS DRIVERS WITH 3-STATE OUTPUTS

JUNE 1984—REVISED MAY 1986

- 3-State Outputs Drive Bus Lines or Buffer Memory Address Registers
- P-N-P Inputs Reduce DC Loading
- Outputs Have 25-Ω Series Resistor, So No External Resistors are Required
- Package Options Include Plastic "Small Outline" Packages, Plastic and Ceramic Chip Carriers, and Standard Plastic and Ceramic 300-mil DIPs
- Dependable Texas Instruments Quality and Reliability

SN54ALS2540, SN54ALS2541 . . . J PACKAGE
SN74ALS2540, SN74ALS2541 . . . DW OR N PACKAGE

(TOP VIEW)



description

These octal buffers and line drivers are designed to drive capacitive input characteristics of MOS devices and have the performance of the popular SN54ALS240A/SN74ALS240A series. At the same time, they offer a pinout with inputs and outputs on opposite sides of the package. This arrangement greatly enhances printed-circuit-board layout.


The three-state control gate is a 2-input AND with active-low inputs such that if either $\bar{G}1$ or $\bar{G}2$ is high, all eight outputs are in the high-impedance state.

The 'ALS2540 offers inverting data and the 'ALS2541 offers true data at the outputs.

The SN54ALS' is characterized for operation over the full military temperature range of -55°C to 125°C . The SN74ALS' is characterized for operation from 0°C to 70°C .

SN54ALS2540, SN54ALS2541 . . . FK PACKAGE


(TOP VIEW)



SN54ALS2540, SN54ALS2541, SN74ALS2540, SN74ALS2541 **OCTAL LINE DRIVERS/MOS DRIVERS WITH 3-STATE OUTPUTS**


JUNE 1984—REVISED MAY 1986

logic symbols[†]



[†]These symbols are in accordance with ANSI/IEEE Std 91-1984 and IEC Publication 617-12.

logic diagrams (positive logic)



All output resistors are 25 Ω.

SN54ALS2540, SN54ALS2541, SN74ALS2540, SN74ALS2541 OCTAL LINE DRIVERS/MOS DRIVERS WITH 3-STATE OUTPUTS

JUNE 1984—REVISED MAY 1986

absolute maximum ratings over operating free-air temperature range (unless otherwise noted)

Supply voltage, V_{CC}	7 V
Input voltage	7 V
Voltage applied to a disabled 3-state output	5.5 V
Operating free-air temperature range: SN54ALS2540, SN54ALS2541	–55°C to 125°C
SN74ALS2540, SN74ALS2541	0°C to 70°C
Storage temperature range	–65°C to 150°C

recommended operating conditions

		SN54ALS2540 SN54ALS2541			SN74ALS2540 SN74ALS2541			UNIT
		MIN	NOM	MAX	MIN	NOM	MAX	
V_{CC}	Supply voltage	4.5	5	5.5	4.5	5	5.5	V
V_{IH}	High-level input voltage	2			2			V
V_{IL}	Low-level input voltage			0.7			0.8	V
I_{OH}	High-level output current			–0.4			–0.4	mA
I_{OL}	Low-level output current			12			12	mA
T_A	Operating free-air temperature	–55		125	0		70	°C

electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

PARAMETER		TEST CONDITIONS		SN54ALS2540		SN74ALS2540		UNIT	
				SN54ALS2541		SN74ALS2541			
				MIN	TYP†	MAX	MIN	TYP†	MAX
V _{IK}		V _{CC} = 4.5 V, I _I = –18 mA		–1.2		–1.2		V	
V _{OH}		V _{CC} = 4.5 V to 5.5 V, I _{OH} = –0.4 mA		V _{CC} – 2		V _{CC} – 2		V	
V _{OL}		V _{CC} = 4.5 V, I _{OL} = 1 mA		0.15 0.5		0.15 0.5		V	
		V _{CC} = 4.5 V, I _{OL} = 12 mA		0.35 0.8		0.35 0.8			
I _{OZH}		V _{CC} = 5.5 V, V _O = 2.7 V		20		20		μA	
I _{OZL}		V _{CC} = 5.5 V, V _O = 0.4 V		–20		–20		μA	
I _{OH}		V _{CC} = 4.5 V, V _O = 2 V		–15		–15		mA	
I _{OL}		V _{CC} = 4.5 V, V _O = 2 V		30		30		mA	
I _I		V _{CC} = 5.5 V, V _I = 7 V		0.1		0.1		mA	
I _{IH}		V _{CC} = 5.5 V, V _I = 2.7 V		20		20		μA	
I _{IL}		V _{CC} = 5.5 V, V _I = 0.4 V		–0.1		–0.1		mA	
I _O ‡		V _{CC} = 5.5 V, V _O = 2.25 V		–15 –70		–15 –70		mA	
I _{CC}	‘ALS2540	V _{CC} = 5.5 V	Outputs high	5 10		5 10		mA	
			Outputs low	13 22		13 22			
			Outputs disabled	11 19		11 19			
	‘ALS2541	V _{CC} = 5.5 V	Outputs high	6 14		6 14		mA	
			Outputs low	15 25		15 25			
			Outputs disabled	13.5 22		13.5 22			

† All typical values are at $V_{CC} = 5$ V, $T_A = 25^\circ\text{C}$.

‡ The output conditions have been chosen to produce a current that closely approximates one half of the true short-circuit output current, I_{OS} .

SN54ALS2540, SN54ALS2541, SN74ALS2540, SN74ALS2541 **OCTAL LINE DRIVERS/MOS DRIVERS WITH 3-STATE OUTPUTS**

JUNE 1984 – REVISED MAY 1986

'ALS2540 switching characteristics (see Note 1)

PARAMETER	FROM (INPUT)	TO (OUTPUT)	V _{CC} = 5 V, C _L = 50 pF, R1 = 500 Ω, R2 = 500 Ω, T _A = 25 °C	V _{CC} = 4.5 V to 5.5 V, C _L = 50 pF, R1 = 500 Ω, R2 = 500 Ω, T _A = MIN to MAX				UNIT
			'ALS2540	SN54ALS2540		SN74ALS2540		
			TYP	MIN	MAX	MIN	MAX	
t _{PLH}	A	Y	7.5	2	14	2	12	ns
t _{PHL}			5.6	2	13	2	11	
t _{PZH}	$\overline{G}$	Y	9	5	18	5	15	ns
t _{PZL}			12.6	8	24	8	20	
t _{PHZ}	$\overline{G}$	Y	4	1	12	1	10	ns
t _{PLZ}			7	2	14	2	12	

'ALS2541 switching characteristics (see Note 1)

PARAMETER	FROM (INPUT)	TO (OUTPUT)	V _{CC} = 5 V, C _L = 50 pF, R1 = 500 Ω, R2 = 500 Ω, T _A = 25 °C	V _{CC} = 4.5 V to 5.5 V, C _L = 50 pF, R1 = 500 Ω, R2 = 500 Ω, T _A = MIN to MAX				UNIT
			'ALS2541	SN54ALS2541		SN74ALS2541		
			TYP	MIN	MAX	MIN	MAX	
t _{PLH}	A	Y	8.7	2	17	2	15	ns
t _{PHL}			7	2	14	2	12	
t _{PZH}	$\overline{G}$	Y	9	5	18	5	15	ns
t _{PZL}			12.6	8	24	8	20	
t _{PHZ}	$\overline{G}$	Y	4	1	12	1	10	ns
t _{PLZ}			7	2	14	2	12	

NOTE 1: Load circuit and voltage waveforms are shown in Section 1.

PACKAGING INFORMATION

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan (2)	Lead/Ball Finish	MSL Peak Temp (3)	Op Temp (°C)	Top-Side Markings (4)	Samples
SN74ALS2540N	OBSOLETE	PDIP	N	20		TBD	Call TI	Call TI	0 to 70		

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

(2) Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS), Pb-Free (RoHS Exempt), or Green (RoHS & no Sb/Br) - please check <http://www.ti.com/productcontent> for the latest availability information and additional product content details.

TBD: The Pb-Free/Green conversion plan has not been defined.

Pb-Free (RoHS): TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes.

Pb-Free (RoHS Exempt): This component has a RoHS exemption for either 1) lead-based flip-chip solder bumps used between the die and package, or 2) lead-based die adhesive used between the die and leadframe. The component is otherwise considered Pb-Free (RoHS compatible) as defined above.

Green (RoHS & no Sb/Br): TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

(3) MSL, Peak Temp. -- The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

(4) Multiple Top-Side Markings will be inside parentheses. Only one Top-Side Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Top-Side Marking for that device.


Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.


N (R-PDIP-T**)

16 PINS SHOWN

PLASTIC DUAL-IN-LINE PACKAGE



PINS ** DIM	14	16	18	20
A MAX	0.775 (19,69)	0.775 (19,69)	0.920 (23,37)	1.060 (26,92)
A MIN	0.745 (18,92)	0.745 (18,92)	0.850 (21,59)	0.940 (23,88)
MS-001 VARIATION	AA	BB	AC	AD



4040049/E 12/2002

NOTES:

- A. All linear dimensions are in inches (millimeters).
B. This drawing is subject to change without notice.
-  Falls within JEDEC MS-001, except 18 and 20 pin minimum body length (Dim A).
 The 20 pin end lead shoulder width is a vendor option, either half or full width.

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have **not** been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

Products

Audio	www.ti.com/audio
Amplifiers	amplifier.ti.com
Data Converters	dataconverter.ti.com
DLP® Products	www.dlp.com
DSP	dsp.ti.com
Clocks and Timers	www.ti.com/clocks
Interface	interface.ti.com
Logic	logic.ti.com
Power Mgmt	power.ti.com
Microcontrollers	microcontroller.ti.com
RFID	www.ti-rfid.com
OMAP Applications Processors	www.ti.com/omap
Wireless Connectivity	www.ti.com/wirelessconnectivity

Applications

Automotive and Transportation	www.ti.com/automotive
Communications and Telecom	www.ti.com/communications
Computers and Peripherals	www.ti.com/computers
Consumer Electronics	www.ti.com/consumer-apps
Energy and Lighting	www.ti.com/energy
Industrial	www.ti.com/industrial
Medical	www.ti.com/medical
Security	www.ti.com/security
Space, Avionics and Defense	www.ti.com/space-avionics-defense
Video and Imaging	www.ti.com/video

TI E2E Community

e2e.ti.com