


REV.	DATE	DESCRIPTION
NC	10/16/02	INITIAL RELEASE
A	05/01/04	UPDATE DRAWING FORMAT



8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020”	APPROVALS		DATE		Amphenol Connex					
7						DRAWN	G.R.S.	05/01/04							
6						CHECKED									
5						ISSUED				PART DESCRIPTION BNC ”T” ADAPTER / JACK–PLUG–JACK 75ohm					
4	CONTACT PIN	BRASS	GOLD	1		SHEET	1 OF 1								
3	CONTACT PIN	PHOS. BRONZE	GOLD	1		PART NO. 112462					DWG. NO. 112462.DWG REV. A SIZE A SCALE NA				
2	INSULATOR	DELIN	NATURAL	1											
1	BODY	DIE CAST	NICKEL	1											
	DESCRIPTION	MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING	C:/112/112462.DWG									