






- 1 POINT OF MEASUREMENT FOR PLATING THICKNESS.
- 2 RECOMMENDED DRILL SIZE 1.15mm .0452±.0010 INCHES.
- 3 DUPLEX PLATING: .000030 GOLD IN AREA F. .000100-.000200 BRIGHT TIN-LEAD ON COMPLIANT TAIL, ALL OVER .000050 NICKEL.
- 4 RECESSED DATE CODE AND CSA LOGO
- 5 PRELIMINARY PART - NOT RELEASED FOR PRODUCTION.
- 6 ROHS 2002/95/EC COMPLIANT
- 7 DUPLEX PLATING: .000030 GOLD IN AREA F, .000100-.0002000 MATTE TIN ON COMPLIANT TAIL, ALL OVER .000050 NICKEL

6	7	-	1	4.270	3.900	39	4.300	4.380	80	5-147792-5
6	7	-	36	4.270	3.900	39	4.300	4.380	80	5-147792-4
6	7	37	-	4.270	3.900	39	4.300	4.380	80	5-147792-3
6	7	40	-	4.270	3.900	39	4.300	4.380	80	5-147792-2
6	7	1	-	4.270	3.900	39	4.300	4.380	80	5-147792-1
6	3	-	1	4.270	3.900	39	4.300	4.380	80	147792-5
5	3	-	36	4.270	3.900	39	4.300	4.380	80	147792-4
	3	37	-	4.270	3.900	39	4.300	4.380	80	147792-3
	3	40	-	4.270	3.900	39	4.300	4.380	80	147792-2
	3	1	-	4.270	3.900	39	4.300	4.380	80	147792-1

ROW M	ROW N	E	D	C	B	A	NO. OF POSN	ASSEMBLY PART NO.					
PLATING	POSTS OMITTED												
THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN R BROWN	12APR01	TE Connectivity								
			CHK J GESFORD	12APR01									
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J GESFORD	12APR01	NAME							
		0 PLC ± -		PRODUCT SPEC									
		1 PLC ± -		—									
		2 PLC ± -		APPLICATION SPEC									
		3 PLC ± .005		—									
4 PLC ± -		—		SIZE				CAGE CODE	DRAWING NO	RESTRICTED TO			
MATERIAL		FINISH		WEIGHT		A2		00779	C=147792				
—		SEE TABLE		CUSTOMER DRAWING				SCALE	4:1	SHEET	1 of 1	REV	F1