

Part Number: 53319-0649

2.54 BtB RA Header Assy Metal Peg 64Ckt

Image not available

Status: **OBsolete**
Replacement: [Contact Molex](#)
Series: [53319](#)
Category: Molex Parts

 [CHECK DISTRIBUTOR INVENTORY](#) [Add to My Parts](#)[Go to Part Detail ▾](#)*Series image - Reference only***Specifications & Other Documents:***Documents not available online***Sales Drawings, 3D Models, and Brochures***Documents not available online*Note - Please disable browser pop-up blockers to view documents on www.molex.com**Product Environmental Compliance**Questions on Product Environmental Compliance? Email productcompliance@molex.com[EU RoHS](#): ELV and RoHS Compliant[China RoHS](#): [REACH SVHC](#): Contains SVHC: No[Low-Halogen Status](#): Not Low-Halogen**Application Tooling**[FAQ](#)

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling[Check our list of old tooling that used to be available for this part](#)**Part Detail**[COLLAPSE ALL](#)**▼ General**

Status	Obsolete
Category	Molex Parts
Series	53319
UPC	822348141036

▼ Physical

Flammability	94V-0
Net Weight	12793.688/mg

▼ Agency Certification

CSA	LR19980
UL	E29179

▼ Material Info**Molex Connectors**

Wire-to-Board

Board-to-Board

Wire-to-Wire

Input/Output (IO)

FFC/FPC

Sockets

Other Products

Fiber Optic Products

Antennas

Industrial Automation

Membrane Switches

Copper Flex

PCB Assemblies

Woodhead Electrical

Solid State Lighting

Resources

Catalog

Cross-Reference

Industries

Literature

Product Name

Company Info

About Us

Careers

Contact Us

ecocare

Investors

Press Room

Shows & Events

Other Info

Feedback

Help

Legal Disclaimer

Privacy Policy

Sitemap

Stay Connected with Molex: