




Dimensions (mm)

 tolerances according to DIN ISO 2768-m
 Toleranzen gem. DIN ISO 2768-m

Isometric

Scale 2:1
 Massstab 2:1



Mag. values DIN IEC 60404-8-	Conditions	Min	Typ	Max	Unit
Remanence Br		1.180	1.240		mT
Revers. temp. coeff. of Br			-0,1		%/K
Coercivity HcB		860	920		kA/m
Coercivity HcJ		1.750	1.900		kA/m
Revers. temp. coeff. of HcJ			-0,6		%/K
Density			7,6		g/cu cm
Max. operating temperature				160	°C
Magnetic moment	measured with MS150	29,6	31,8	34,1	E-6 Vs*cm
Magnet Material		NdFeB			
Direction of Magnetization		axial			

General data	Conditions	Min	Typ	Max	Unit
Remarks		All details according to manufacturers information			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Standex Electronics:](#)

[NDFEB 6X10MM](#)