

DIGITAST

Microminiature SPDT, Key Switches



Features/Benefits

- High reliability/long life
- Designed for low level switching
- Ready to implement on PCB
- Latching function available
- Several button options
- RoHS compliant and compatible

Typical Applications

- Medical
- Instrumentation
- Industrial electronics
- Audio electronics

Construction

FUNCTION: momentary or push-push
CONTACT ARRANGEMENT: 1 change over contact SPDT, NO
MODE OF SWITCHING: Non-shorting
DISTANCE BETWEEN BUTTON CENTERS:
HORIZONTAL MINIMUM 12,7 (0.500) or 17,78 (0.700)
VERTICAL MINIMUM 17,78 (0.700)
TERMINALS: PC pins
MOUNTING: Soldering, centering pins

Mechanical

TOTAL TRAVEL: ≤ 3 (0.118)
SWITCHING TRAVEL: 1,5 (0.0591)
LATCHING TRAVEL: 1,8 (0.0709)
OPERATING FORCE: 1.5 +/- 0.5 N (150 +/- 50 grams)

Process

SOLDERABILITY: Max. soldering time and temperature: 5 s at 260°C

Electrical

SWITCHING POWER MAX.: 240mW DC
SWITCHING VOLTAGE MAX.: 24 V DC
SWITCHING CURRENT MAX.: 10mA DC
CARRYING CURRENT AT 20°C (push-push version): 100mA
DIELECTRIC STRENGTH (50 Hz, 1 min): 500 V
OPERATING LIFE with or without max. switching power
Momentary: $\geq 5 \times 10^6$ operations
Push-push: $\geq 5 \times 10^6$ operations
CONTACT RESISTANCE: Initial $\leq 50 \text{ m}\Omega$
After 5×10^6 operations: $\leq 100 \text{ m}\Omega$
INSULATION RESISTANCE: $\geq 10^9 \Omega$
CAPACITANCE at $f = 10 \text{ kHz}$: $\leq 0.8 \text{ pF}$
BOUNCE TIME: $\leq 2.5 \text{ ms}$
Operating speed 400 mm/s (15.75/s)

Environmental

OPERATING TEMPERATURE: -25°C to 85°C.

How To Order

Our easy build-a-switch concept allows you to mix and match options to create the switch you need. To order, select desired option from each category and place it in the appropriate box.

Switch

Series	LED	1st LED Color	LED Spacing*	2nd LED Color	Function	Contact Material	Body Color
SER Narrow button SET Wide button SERU Switch body only (no button)	NONE No LED L 1 LED 2L 2 LED's	NONE No LED RD Red YE Yellow GN Green	NONE Narrow LED Spacing (TYP Europe) 7.62 Wide LED Spacing (TYP No. America)	NONE No LED RD Red YE Yellow GN Green	EE Latching OA Non-latching	AU Gold	NONE White (STD) BRN Brown
Button Color**							
NONE (SERU) BK Black GY Gray							

* LED spacing only applies when 1 LED requested

Button

Button Style	LED Holes	Button Color**	Latching
SR Narrow ST Wide	NONE No LED holes L 1 LED hole 2L 2 LED holes	BK Black GY Gray	None For use with momentary switch EE With "EE" staple for latching

** Additional button colors available by request




Dimensions are shown: mm (inch)
Specifications and dimensions subject to change




www.ck-components.com

DIGITAST Microminiature SPDT, Key Switches

DESIGNATION




SER NARROW BUTTON




Total travel
3 (0.118)
Switching travel 1.5 (0.0591)




SER



SERL






SER2L



1st LED
2nd LED


SET WIDE BUTTON




Total travel
3 (0.118)
Switching travel 1.5 (0.0591)




SET



SETL






SET2L



1st LED
2nd LED

SERU NO BUTTON




First Angle
Projection

Dimensions are shown: mm (inch)
Specifications and dimensions subject to change

Microminiature SPDT, Key Switches


LED

NONE NO LED




L 1 LEDs

7.62mm Spacing (TYP No. America)




NARROW SPACING (TYP EUROPE)



TOP VIEW OF PCB

2 2LEDs



$\varnothing 1.0 \pm 0.1 \quad (0.0394 \pm 0.00349)$

$\varnothing 1.1 \pm 0.05 \text{ (} 0.0433 \pm 0.00197 \text{)}$

BUTTON COLOR

BK BLACK

GY GRAY

Other button colors available by request [red (RD), green (GN), white (WH), yellow (YE), blue (BU), orange (OG)].

LED COLOR

OPTION CODE	COLOR
NONE	Models without LED
RD	Red
GN	Green
YE	Yellow

CONTACT MATERIAL

OPTION CODE	MATERIAL
AU	Gold

FUNCTION

OPTION CODE	COLOR	SCHEMATIC
OA	Momentary	
EE	Push-Push	



Dimensions are shown: mm (inch)
Specifications and dimensions subject to change